



CIRCUIT DIAGRAM



RECOMMENDED P.C.B. LAYOUT

安装尺寸图

规格 Specifications	
额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V/50~60HZ) 60S min.
操作力 Operation force	≤180±30gf ≤300±50gf
寿命试验 Operating Life	50,000 cycles 30,000 cycles
行程 Travels	0.25±0.1mm



PRODUCT NO. : 1TS002E*****

- 轻触开关
- 3X6系列
- 外形:
 - A=插脚
 - B=贴片
 - C=贴片带柱
 - D=贴片2.5高
 - K=贴片带柱8.8
 - L=贴片10.2
- 按钮颜色:
 - 底座颜色:
 - 盖板颜色:
- 操作力度:
 - 160=160±20gf
 - 180=180±30gf
 - 220=220±30gf
 - 250=250±50gf
 - 300=300±50gf
- 手感:
 - 0=常规(弹片)
 - 1=大手感(弹片)
 - 2=小手感(弹片)
 - 3=特殊手感(弹片)
- 有无贴膜:
 - 0=不贴膜
 - 1=贴膜
- 其它:
 - CT=编带(非编带,不启用)
- 产品高度(H):
 - 250=2.5mm

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	ACTUATOR	1	LCP	RED
4	COVER	1	STAINLESS STEEL	NATURAL
3	DOME	1	STAINLESS STEEL	Ag-PLATED
2	HOUSING	1	LCP	BLACK
1	TERMINAL	1	BRASS	Ag-PLATED

UNIT	MM	FINISH
X. ± 0.3	X' ± 3'	
X ± 0.2	X' ± 2'	MAT'L
.XX ± 0.1	.XX' ± 1'	
.XXX ± 0.05	.XXX' ± 0.5'	

NAME(INTENDED USE)	QUANTITY	MATERIAL	FINISH
3X6 T/H SERIES TACT SWITCH	1	LCP	RED
1TS002E*****Q	1	BRASS	Ag-PLATED

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.

APPD: ZO 8/08/2014 DWG NO.: 1TS002E

CHKD: M.H.LI 8/08/2014

DR: WP.LU 8/07/2014

SCALE SHEET REV. 10/1 2/2 D