







RoHS

MAPX

MODIFICATION

DRW

DATE



1. 材料

- A. 主体: LCP, 黑色, 白色, UL 94-V0;
- B. 端子: 铜合金, 电镀刷金;
- C. 外壳: 不锈钢, 镀全镍;

2. 主要特性

- A. 电压等级: 20V AC;
- B. 电流: 3A;
- C. 工作温度: -40°C~85°C;

3. 电气要求:

- A. 接触电阻: 4mΩ Max.(初始), 5mΩ Max.(最后);
- B. 电压: 100V AC 1分钟;
- C. 绝缘电阻: 100MΩ/min. DC 500v;

4. 机械性能:

- A. 插入力: 5~20N. (从1~10,000次);
- B. 拔出力: 8~20N. (从1~1,000次);
- 6~20N. (从1,001~10,000次);
- C. 耐久性寿命: 5,000次;

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

产品图

PRODUCT CHART DWG

公差一览表

TOLERANCE UNLESS OTHERWISE

X.	±0.25	X.	±5°
.X	±0.20	.XX	±2°
.XX	±0.15	.XXX	±1°
.XXX	±0.10	.XXX	±0.5°

深圳市精拓金电子有限公司  
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

单位 UNITS	MM	制图 DRAWING	Z-Y-B	制图料号 PRODUCT PART NO.	918-418K2023S40001
比例 SCALE	1:1	审核 CHKD	郭志富	产品名称 PRODUCT NO.	TYPE-C3.1母座板上型7.35四脚 1.2带钢片单排SMT有柱 16PIN/3A
日期 DATE	2016-09-09	核准 APPD	黄国荣	角法 VIEW	版本 VER
					AO