





MAPX	MODIFICATION	DATE



P. C. B. LAYOUT

特性:Specifications:

电器:Electrical:

1. 接触阻抗: Contact Resistance  
30 milliohms MAX
2. 耐电压: Dielectnic Withstanding Voitage:  
500 V AC AT Sea Level
3. 绝缘抗阻: Lnsulation Resistance  
1000MEGA ohms MIN

材料:Matorial:

1. 塑胶: Housing:Hing Temperature Tnermaplastic
2. 端子: Contact:Coppre Alloy 铜合金
3. 铁壳: Shell:Copper Aiioy铜/铁合金

电镀: Finish:

1. 端子: Contact: Piated Golg in Mating Area:  
Tin On Solder Talls  
接触点镀金. 脚镀锡
2. 铁壳: Shell:

Nickel Plating

镀镍

产品图 PRODUCT CHART DWG				深圳市精拓金电子有限公司						
公差一览表 TOLERANCE UNLESS OTHERWISE				单位 UNITS	MM	制图 DRAWING	邱建辉	制图料号 PRODUCT PART NO.	921-112A1010D10200	
X.	±0.25	X.	±5.°	比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NO.	BF 90度弯脚铜壳/白胶	
.X	±0.20	.X	±2.°	日期 DATE	2016.05.11	核准 APPD	黄国荣	角法 VIEW	版本 VER	AD
.XX	±0.15	.XX	±1.°							
.XXX	±0.05	.XXX	±0.5°							