



PCB Layout(Pattern side)

NOTE:  
Operating Force:  
lever portion 4-180 ± 50 gf  
Push portion 250 ± 50 gf

1	2	3	4	5	6	7	8	9	10
F1	F1								
F2									
F3									
F4									
F5									

⑥	Contact	—	6	Fg/SUS	Natural	—
⑤	Terminal	—	10	Brass(Q.20)	Plating silver	—
④	Base	—	1	LCP	Black	—
③	Cover	—	1	SUS	Natural	—
②	Axle sleeve	—	1	LCP	Black	—
①	Keystroke	—	1	LCP	Black	—

DRAWN J.X.Zhong 2013/8/22

**HRP**  
ELECTRONICS CO.,LTD

CHECKED TITLE: MULTIFUNCTIONAL SWITCHES

APPROVALS PART NO. K1-1507SA-03

TOLERANCES ARE 30~125 ± ±0.30 ANGLE UNIT: mm SCALE: 1:1 PROJ: SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			