



Note:

1. Rating : DC 12V 50mA
2. Contact Resistance : ≤50mΩ
3. Insulation Resistance: DC500V 1Minute
4. Operating Temperature Range: -25℃+80℃
5. Ambient Humidity Used: ≤85%RH
6. Operating Force : 150±80gf
7. Operating Life : 50,000Cycles

PCB Layout(Pattern side)

ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Beryloy	Ag Plated	—
④	Terminal	—	5	Phosphor Bronze	Ag Plated	—
③	Base	—	1	LCP	Black	—
②	Cover	—	1	SUS	Natural	—
①	Knob	—	1	PA46	RED	—

APPROVALS		DATE	TITLE:	
DRAWN	JKUNLU	2013/10/8	TOGGLE SWITCHES	
CHECKED			ELECTRONICS CO.,LTD	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	PROJ:	SHEET
	A		NEW				30~0.1±	±0.30	mm	1:1	K3-1288S	1 of 1
							10~0.30	±0.20				
							5~10	±0.15	±2°			
							~5	±0.10				