



NOTE:
 Rating: DC 20V 50mA
 Operating Force: 20 ± 10 gf
 Lifetime: 100,000 Cycles

⑤	Spring	—	1	SUS	Ag Plated	—
④	Terminal	—	4	Phosphor Bronze	Ag Plated	—
③	Cover	—	1	PA46	Black	—
②	Base	—	1	PA46	Black	—
①	Slider	—	1	PA46	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD		
DRAWN	J.X.Zhang	2013/9/22				
CHECKED				TITLE:	DETECTOR SWITCHES	
APPROVALS				PART NO.	K5-1616SA-02	
TOLERANCES ARE	30~以上	± 0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	10~30	± 0.20		DRAWING NO.	—	SHEET 1 OF 1
	5~10	± 0.15				
	~ 5	± 0.10				

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.