




Circuit Diagram



NOTE:
 Rating: DC 5V 10mA
 Operating Force: 25±10gf
 Lifetime: 100,000 Cycles

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑥	Terminal	—	6	Phosphor Bronze	Ag Plated	—
⑤	Housing	—	1	PA46	Black	—
④	Contact Spring	—	1	Be Alloy	Ag Plated	—
③	Frisket	—	1	PA46	Black	—
②	Cover	—	1	SUS	Natural	—
①	Slider	—	1	PA46	Black	—

APPROVALS		DATE	TITLE:	
DRAWN	J.X.Zhang	2013/9/2	ELECTRONICS CO.,LTD	
CHECKED			DETECTOR SWITCHS	
APPROVALS			PART NO.	K5-1640DN-01

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE: 30~12.5 ±0.30 ANGLE ±2° UNIT: mm SCALE: 1:1 PROJ: SHEET 1 OF 1 10~30 ±0.20 5~10 ±0.15 DRAWING NO.						