

深圳市连线电子有限公司




客户承认图

CUSTOMER (客户): 立创

Customer Part NO.(客户物品号): **C122343**

Part Description (物品规格): 0.5*20*110*B (44/88) (0.035*0.3)

Item	项目	Specification	规格值
NO. of conductors	导体芯数 N	20	
Pitch	间距 P	0.5±0.05	
Total Pitch	全间距 PT	9.5±0.05	
Total Length	总长度 L	110±3	
Insulation Length	绝缘长度 IL	L-8±2	
Margin Width	边缘宽度 M	0.5±0.07	
Total Width	总宽度 W	10.5±0.08	
Strip Length	线口长度 S1	4±1	
Strip Length	线口长度 S2	4±1	
Reinforcing tape length	补强板长度B1	8±2	
Reinforcing tape length	补强板长度B2	8±2	
Slanting	线口倾斜度 A	≤0.3	
Over lap	冲孔	/	
Terminal thickness	插入厚度 t1	0.303±0.05	
Thickness insulation	线身厚度 t	0.121±0.05	
Conductor thickness	导体厚度 Ct	0.035±0.005	
Conductor width	导体宽度 Cw	0.3±0.03	
Supporting Tapc Color	补强板颜色	(Blue) 蓝色	
PET(Supporting Tapc Color)	补强板规格	0.225mm	
PET (Insulation)	绝缘胶规格	0.043mm (有印字)	
PET (Insulation)	绝缘胶规格	0.043mm (无印字白色)	
Rev	版本	A1	



印字内容: **AWM 20624 80C 60V VW-1 颜色: 蓝色**

Storage condition:(储存条件) Recommended (推荐)

Temp: 15°C~25°C(温度)15°C~25°C)Humidity: 30~60RH%(湿度30~60RH%)

Drawing Not To Scale
Hidden Lines Not Shown
图规不能以其线材比来
衡量, 隐藏线不显示

Unit (单位): mm

Discharge Date	Review Date	Drawing NO
2018.05.31	2018053109	图纸编号
Drawing by lilyen	Checked by 核对	Approved by 确认