



**SPECIFICATIONS**  
 Current rating: 2A AC/DC  
 Voltage rating: 250V AC/DC  
 Contact resistance: 30mΩ max.  
 Withstand voltage: 800V AC/min  
 Insulation resistance: 1000MΩ/min.  
 Temperature range: -25°C~+85°C  
 Applicable PC board thickness:  
 0.031"~0.063"(0.8~1.6)

**Material:**  
 Part No: 8-44  
 Insulator: PA66 UL94V-2  
 Contact: Brass  
 Finish: Tin Plated

Poles	Part No.	A	B	C
8	2008R-2*4P-1K	6.0	9.0	10.0
10	2008R-2*6P-1K	8.0	11.0	12.0
12	2008R-2*6P-1K	10.0	13.0	14.0
14	2008R-2*7P-1K	12.0	15.0	16.0
16	2008R-2*8P-1K	14.0	17.0	18.0
18	2008R-2*8P-1K	16.0	19.0	20.0
20	2008R-2*10P-1K	18.0	21.0	22.0
22	2008R-2*11P-1K	20.0	23.0	24.0
24	2008R-2*12P-1K	22.0	25.0	26.0
26	2008R-2*13P-1K	24.0	27.0	28.0
28	2008R-2*14P-1K	26.0	29.0	30.0
30	2008R-2*15P-1K	28.0	31.0	32.0
32	2008R-2*16P-1K	30.0	33.0	34.0
34	2008R-2*17P-1K	32.0	35.0	36.0
36	2008R-2*18P-1K	34.0	37.0	38.0
38	2008R-2*19P-1K	36.0	39.0	40.0
40	2008R-2*20P-1K	38.0	41.0	42.0

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED: \_\_\_\_\_ DATE: \_\_\_\_\_  
 CHECKED: \_\_\_\_\_ DATE: \_\_\_\_\_  
 DRAWN: LYP

TITLE: 2008R-2\*9P 带扣  
 PROD. P/N C155411  
 UNIT mm SCALE free

DATE: 2014-06-26  
 FILE NO. W-2006R18P-B000 REV. A KLD0

深圳市灿科盟实业有限公司  
 Ckmit CHANKLEMENT INDUSTRY CO., LTD