



**适用线路板**

RECOMMENDED PCB LAYOUT

- 技术指标:**
- 1、塑件表面应光洁、无毛刺、明显收缩、缺陷、裂纹等现象;
  - 2、温度范围: -25° C~85° C;
  - 3、额定电压: 50V, AC, DC(等效);
  - 4、接触电阻: ≤0.03Ω;
  - 5、绝缘电阻: ≥500MΩ;
  - 6、耐压: 500V, AC/minute.

**适用PPC寸法**

APPLICABLE FPC

4	100-0200-004	耐引箔料	精磷 Phosphor Bronze	2	镀层 镀层厚度50μm, 镀层 20μm.
3	100-0400-003	物 Actuator	PPS(UL94V-0)	1	材料
2	100-0100-002	籽 Contact	精磷 Phosphor Bronze	no1	镀层 镀层厚度50μm, 镀层 20μm.
1	100-0300-001	插 Flushing	PA66(DLH,UL94V-0)	1	材料
序号	图	号名	材料	数量	备注

**TOLERANCE TABLE**

	.0	±0.20
	.00	±0.10
	.000	±0.05

Pin#	Type	A	B	C	Pin#	Type	A	B	C
4	0.5A-4PMS	1.5	2.6	7.7	33	0.5A-33PMS	16	17.1	22.2
5	0.5A-5PMS	2	3.1	8.2	34	0.5A-34PMS	16.5	17.6	22.7
6	0.5A-6PMS	2.5	3.6	8.7	35	0.5A-35PMS	17	18.1	23.2
7	0.5A-7PMS	3	4.1	9.2	36	0.5A-36PMS	17.5	18.6	23.7
8	0.5A-8PMS	3.5	4.6	9.7	37	0.5A-37PMS	18	19.1	24.2
9	0.5A-9PMS	4	5.1	10.2	38	0.5A-38PMS	18.5	19.6	24.7
10	0.5A-10PMS	4.5	5.6	10.7	39	0.5A-39PMS	19	20.1	25.2
11	0.5A-11PMS	5	6.1	11.2	40	0.5A-40PMS	19.5	20.6	25.7
12	0.5A-12PMS	5.5	6.6	11.7	41	0.5A-41PMS	20	21.1	26.2
13	0.5A-13PMS	6	7.1	12.2	42	0.5A-42PMS	20.5	21.6	26.7
14	0.5A-14PMS	6.5	7.6	12.7	43	0.5A-43PMS	21	22.1	27.2
15	0.5A-15PMS	7	8.1	13.2	44	0.5A-44PMS	21.5	22.6	27.7
16	0.5A-16PMS	7.5	8.6	13.7	45	0.5A-45PMS	22	23.1	28.2
17	0.5A-17PMS	8	9.1	14.2	46	0.5A-46PMS	22.5	23.6	28.7
18	0.5A-18PMS	8.5	9.6	14.7	47	0.5A-47PMS	23	24.1	29.2
19	0.5A-19PMS	9	10.1	15.2	48	0.5A-48PMS	23.5	24.6	29.7
20	0.5A-20PMS	9.5	10.6	15.7	49	0.5A-49PMS	24	25.1	30.2
21	0.5A-21PMS	10	11.1	16.2	50	0.5A-50PMS	24.5	25.6	30.7
22	0.5A-22PMS	10.5	11.6	16.7	51	0.5A-51PMS	25	26.1	31.2
23	0.5A-23PMS	11	12.1	17.2	52	0.5A-52PMS	25.5	26.6	31.7
24	0.5A-24PMS	11.5	12.6	17.7	53	0.5A-53PMS	26	27.1	32.2
25	0.5A-25PMS	12	13.1	18.2	54	0.5A-54PMS	26.5	27.6	32.7
26	0.5A-26PMS	12.5	13.6	18.7	55	0.5A-55PMS	27	28.1	33.2
27	0.5A-27PMS	13	14.1	19.2	56	0.5A-56PMS	27.5	28.6	33.7
28	0.5A-28PMS	13.5	14.6	19.7	57	0.5A-57PMS	28	29.1	34.2
29	0.5A-29PMS	14	15.1	20.2	58	0.5A-58PMS	28.5	29.6	34.7
30	0.5A-30PMS	14.5	15.6	20.7	59	0.5A-59PMS	29	30.1	35.2
31	0.5A-31PMS	15	16.1	21.2	60	0.5A-60PMS	29.5	30.6	35.7
32	0.5A-32PMS	15.5	16.6	21.7					

APPROVED: DATE:

CHECKED: DATE:

DRAWN: DATE:

LYP 2009-11-28

深圳市灿科盟实业有限公司  
CKIMT W CHANKLEMENT INDUSTRY CO., LTD

TITLE: PPC0.5-XXP 下接抽接式

P/N	/
UNIT	mm
SCALE	free
FILE NO.	CKimtw-PPC-0034
REV.	A