


REVISONS			
REV/	NUMBER	DESCRIPTION	DATE
A		DESIGN	



三個配件出貨時另外附配件出貨(2个华司, 1个螺母)

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管, OD:2.0MM	AS
③	端子	高仿I-PEX, 1.13端子, 镀金	1
②	接头	SMA母头内孔, 分体, 11牙, 镀金	1
①	同轴线	RF 1.13灰色线, OD:1.13mm	AS

金航标电子有限公司

- NOTES:
- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE:3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPENS/SHORT, MISWIRING AND INTERMITTENT FAILURES
 - MATERIAL:
 - SEE TABLE
 - MECHANICAL:
 - SMA PULL FORCE: 12.0KGS.
 - ALL COMPONENTS ARE ROHS COMPLIANT.

ALL DIMENSION ARE IN MM	DRAWN	DATE	TITLE
ARE IN MM	Janny	2018/05/04	RF CABLE I-PEX 1.13 TO SMA / F L=80 MM
COMPUTER GENERATED IN SOLIDWORKS	ENG.		
DO NOT SCALE THIS DRAWING	MFG.		
	Q.A.		
PROJECTION	GENERAL TOLERANCE FOR ANGLES XX XXX XXXX ± 1° ± 0.3 ± 0.25 ± 0.150		
CUSTOMER PIN:	SCALE: Free TYPE SHEET 1 OF 1		

4
3
2
1

A
B
C
D

4
3
2
1

A
B
C
D