



35mm Size ABC Switch Type EC35AH/EC35CH Series

Actuator length			25mm	
Detent torque			30±15mN·m	
Number of detent			30	
Number of pulse			10	
Operating tempera	ature range		-40℃ to +85℃	
Electrical performance	Ratings			10mA 5V DC
	Output signal			Three phase A,B and C
	Max./min. operating current(Resistive load)			10mA/1mA
	Insulation resistance			100MΩ min. 250V DC
	Voltage proof			300V AC for 1 minute or 360V AC for 2s
Mechanical performance	Actuator strength		Pushing direction	100N
			Pulling direction	100N
Durability	Operating life			50,000 cycles
Minimum order unit (pcs.)		Japan		350
		Export		700

Dimensions




Mounting Hole Dimensions




Viewed from mounting side

Output Wave



Sliding Noise



V1=V2=2.5V max.

At $R = 5k\Omega$ Chattering : 5ms max. Bounce : 5ms max.

Packing Specifications

-	-		
	-	-	
		•	ıv

Number of package (pcs.)	s 1 case / Japan	350
(1-1-7)	1 case / export packing	700
Export package measurements (mm)		540×360×380

Soldering Conditions

Reference for Dip Soldering

Preheating	Soldering surfacetemperature	100℃ max.
	Heating time	2 min. max.
Dip soldering	Soldering temperature	260±5℃
	Soldering time	5±1s
No. of solders		2 time max.
Reference for Hand Soldering		
Tip temperature		350℃ max.
Soldering time		3s max.
No. of solders		1 time

Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. Please place purchase orders per minimum order unit (integer).
- 3. This products can be used in vehicles.

Although these products are designed to perform over a wide operating temperature range, please ensure that you receive and read the formal delivery specifications before use.