## The Quicksilver

## Yagi Directional Cellular Antenna



BT512389

Not all Yagi Antennas are created equal. The Quicksilver - a Yagi designed for the modern era. Compact, efficient, and high gain.

- Wide band, 698-2700 MHz, N-Female
- Built for 50 Ohm Signal Boosters
- High efficiency and compact design
- Stable performance proving high gain up to +11 dBi



ELECTRICAL STUFF			Product Specifications may change without prior notice.	
Item No.		BT512389		
Frequency Range		MHz	698-960	1710-2700
Gain		dBi	10	11
Polarization			Vertical & Horizontal	
Beam width	Horizontal	deg	60	55
	Vertical		65	45
VSWR			≤1.8	1.5
Maximum Input Power		watt	50	
Impedance		ohm	50	
PIM, 3rd Order, 2 x 20W		dBc	≤-150	
MECHANICAL S	TUFF			
Connector Type			N-Female	
Connector Position			Bottom	
Size		mm, in	440 x 210 x 60, 17.32 x 8.25 x 2.36	
Antenna Weight		kg, lb	1.20, 2.65	
Rated Wind Velocity		m/s, F/s	36.90, 121	
Operational Temperature		°C, °F	-40 to 55, -40 to 131	
Mounting hardware		mm, in	Ø35 to Ø50, 1.40 to 2.00	
Radome Material, Color			ABS, White	
Ingression Protection Rating			IP65	





















