


		1		
Part Number:		DRAWN	10/7/2016	
TD144	1009-1	CJ	10/7/2016	
IP1 <del>4</del> 4		CHECKED	10/7/2016	
		P.D.		
Description:	ansducer	APPROVED	10/7/2016	
Plezo III	aiisuucei	J.S.	10/7/2016	


This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.


## Top View



## Side View



## **Bottom View**



Items	Specifications	Conditions						
Sound Pressure Level	80	dB (@ 10cm)						
Resonant Frequency	4,000	Hz						
Rated Voltage	9	V	REVISION HISTORY					
Voltage Range	1 ~ 20	V	REV	DESCRIPTION	DATE	APPROVED		
Capacitance	13,000	pF		Released from Engineering	10/21/2013	J.S		
Max. Rated Current	7	mA	1	Updated to new template	10/7/2016	J.S.		
Storage Temperature	-20 ~ +70	°C		NOTES				
Operating Temperature	-20 ~ +70	°C		1) All dimensions are in mm unless otherwise noted				
Connection Method	PC Pins			2) All tolerances are ± 0.5 mm unless otherwise noted				
Mount Type	Thru Hole			3) All parts meet RoHS				
Housing Material	Noryl			4) Subject to change or redrawn without notice				
Moight	1	0						