

# Motor Run Capacitor

## HCK Series

440 Volt • 50/60 Hz



### Description

The HCK Series capacitors are used in single phase motor applications when there is a need for improved torque and efficiency. These run capacitors provide a phase shift to the secondary winding of the motor thereby increasing the torque and power factor.

### Features & Benefits

FEATURES	BENEFITS
<b>Single and dual rated values</b>	To meet a broad range of applications
<b>Round or oval case options</b>	To maximize product footprint
<b>Aluminum oil filled construction</b>	To help cool and extend the life of the capacitor
<b>Designed &amp; manufactured in accordance with UL 810 and EIA standard RS-456</b>	To ensure product meets quality benchmarks
<b>Movable contacts with heavy duty silver alloy</b>	Helps extend the life of the product

### Applications

- HVAC/R
- Food & Beverage
- Pool & Spa
- Motors
- Electronics

### Specifications

<b>Coil Terminal Connections</b>	.0250" x 0.032" quick connect terminals
<b>Rated AC Voltage</b>	370 and 440 V ac (contact factory for alternative voltages)
<b>Operating Temperature</b>	-40 °C to 70 °C; -40 °F to 158 °F (70 °C Maximum)
<b>Dissipation Factor</b>	0.1% max.
<b>Internal Protection</b>	0.1% max.; UL recognized internal protection bridge capable of interrupting up to 10k amp
<b>Capacitance Tolerance</b>	3 % available
<b>Leakage Current</b>	30 uA max.
<b>Frequency</b>	50/60 Hz
<b>Operating Life</b>	22,000 hours with 94 % survival; 60,000 hours available
<b>Case Material/Finish</b>	Unpainted aluminum construction
<b>Mounting Method</b>	Strap Mount

# Motor Run Capacitor

## HCK Series

### Certification & Compliance

<b>RU, cRU</b>	File No. E223457
<b>UL/cUL Recognized 5085</b>	File No. E223730 (Class 2 and 3) File No. E243953 (General Purpose)

### Ordering Information

LITTELFUSE CATALOG NUMBER	CONTACTOR FORM PER CIRCUIT	FULL LOAD CURRENT INDUCTIVE	FULL LOAD CURRENT RESISTIVE	LOCKED ROTOR CURRENT	LOCKED ROTOR CURRENT	LOCKED ROTOR WEIGHT
CAP-3/440R	Single	3	440 Volt	3 Microfarad	50/60 Hz	0.5 Lb
CAP-3/440	Single	3	440 Volt	3 Microfarad	50/60 Hz	0.5 Lb
CAP-4/440R	Single	3	440 Volt	4 Microfarad	50/60 Hz	0.5 Lb
CAP-4/440	Single	3	440 Volt	4 Microfarad	50/60 Hz	0.5 Lb
CAP-5/440R	Single	3	440 Volt	5 Microfarad	50/60 Hz	0.5 Lb
CAP-5/440	Single	3	440 Volt	5 Microfarad	50/60 Hz	0.5 Lb
CAP-6/440	Single	3	440 Volt	6 Microfarad	50/60 Hz	0.5 Lb
CAP-7.5/440R	Single	3	440 Volt	7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-7.5/440	Single	3	440 Volt	7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-10/10/440R	Dual	3	440 Volt	10+10 Microfarad	50/60 Hz	0.5 Lb
CAP-10/440R	Single	3	440 Volt	10 Microfarad	50/60 Hz	0.5 Lb
CAP-10/440	Single	3	440 Volt	10 Microfarad	50/60 Hz	0.5 Lb
CAP-12.5/440R	Single	3	440 Volt	12 Microfarad	50/60 Hz	0.5 Lb
CAP-12.5/440	Single	3	440 Volt	12.5 Microfarad	50/60 Hz	0.5 Lb
CAP-15/3/440R	Dual	3	440 Volt	15+3 Microfarad	50/60 Hz	.04 Lb
CAP-15/5/440R	Dual	3	440 Volt	15+5 Microfarad	50/60 Hz	0.5 Lb
CAP-15/5/440	Dual	3	440 Volt	15+5 Microfarad	50/60 Hz	.04 Lb
CAP-15/7.5/440R	Dual	3	440 Volt	15+7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-15/10/440R	Dual	3	440 Volt	15+10 Microfarad	50/60 Hz	.04 Lb
CAP-15/440R	Single	3	440 Volt	15 Microfarad	50/60 Hz	0.5 Lb
CAP-15/440	Single	3	440 Volt	15 Microfarad	50/60 Hz	0.5 Lb
CAP-17.5/440	Single	3	440 Volt	17.5 Microfarad	50/60 Hz	0.5 Lb
CAP-20/5/440R	Dual	3	440 Volt	20+5 Microfarad	50/60 Hz	0.5 Lb
CAP-20/5/440	Dual	3	440 Volt	20+5 Microfarad	50/60 Hz	0.5 Lb
CAP-20/7.5/440R	Dual	3	440 Volt	20+7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-20/10/440R	Dual	3	440 Volt	20+10 Microfarad	50/60 Hz	.04 Lb
CAP-20/440R	Single	3	440 Volt	20 Microfarad	50/60 Hz	0.5 Lb
CAP-20/440	Single	3	440 Volt	20 Microfarad	50/60 Hz	0.5 Lb
CAP-25/5/440R	Single	3	440 Volt	25+5 Microfarad	50/60 Hz	0.5 Lb
CAP-25/5/440	Dual	3	440 Volt	25+5 Microfarad	50/60 Hz	0.5 Lb
CAP-25/7.5/440R	Dual	3	440 Volt	25+7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-25/7.5/440	Dual	3	440 Volt	25+7.5 Microfarad	50/60 Hz	.04 Lb
CAP-25/10/440R	Dual	3	440 Volt	25+10 Microfarad	50/60 Hz	0.5 Lb

# Motor Run Capacitor

## HCK Series

### Ordering Information (cont.)

LITTELFUSE CATALOG NUMBER	CONTACTOR FORM PER CIRCUIT	FULL LOAD CURRENT INDUCTIVE	FULL LOAD CURRENT RESISTIVE	LOCKED ROTOR CURRENT	LOCKED ROTOR CURRENT	LOCKED ROTOR WEIGHT
CAP-25/15/440	Dual	3	440 Volt	25+15 Microfarad	50/60 Hz	.04 Lb
CAP-25/440R	Single	3	440 Volt	25 Microfarad	50/60 Hz	0.39 Lb
CAP-25/440	Single	3	440 Volt	25 Microfarad	50/60 Hz	0.39 Lb
CAP-30/3/440R	Dual	3	440 Volt	30+3 Microfarad	50/60 Hz	0.4 Lb
CAP-30/5/440R	Dual	3	440 Volt	30+5 Microfarad	50/60 Hz	0.4 Lb
CAP-30/5/440	Dual	3	440 Volt	30+5 Microfarad	50/60 Hz	0.4 Lb
CAP-30/7.5/440R	Dual	3	440 Volt	30+7.5 Microfarad	50/60 Hz	0.4 Lb
CAP-30/7.5/440	Dual	3	440 Volt	30+7.5 Microfarad	50/60 Hz	0.4 Lb
CAP-30/10/440R	Dual	3	440 Volt	30+10 Microfarad	50/60 Hz	0.5 Lb
CAP-30/15/440R	Dual	3	440 Volt	30+15 Microfarad	50/60 Hz	0.5 Lb
CAP-30/440R	Single	3	440 Volt	30 Microfarad	50/60 Hz	0.4 Lb
CAP-30/440	Single	3	440 Volt	30 Microfarad	50/60 Hz	0.4 Lb
CAP-35/1/440R	Dual	3	440 Volt	35+1 Microfarad	50/60 Hz	.04 Lb
CAP-35/3/440R	Dual	3	440 Volt	35+3 Microfarad	50/60 Hz	0.5 Lb
CAP-35/3/440	Dual	3	440 Volt	35+3 Microfarad	50/60 Hz	0.5 Lb
CAP-35/5/440R	Dual	3	440 Volt	35+5 Microfarad	50/60 Hz	0.5 Lb
CAP-35/5/440	Dual	3	440 Volt	35+5 Microfarad	50/60 Hz	0.5 Lb
CAP-35/7.5/440R	Dual	3	440 Volt	35+7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-35/7.5/440	Dual	3	440 Volt	35+7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-35/10/440R	Dual	3	440 Volt	35+10 Microfarad	50/60 Hz	0.5 Lb
CAP-35/10/440	Dual	3	440 Volt	35+10 Microfarad	50/60 Hz	.04 Lb
CAP-35/15/440R	Dual	3	440 Volt	35+15 Microfarad	50/60 Hz	0.5 Lb
CAP-35/440R	Single	3	440 Volt	35 Microfarad	50/60 Hz	0.5 Lb
CAP-35/440	Single	3	440 Volt	35 Microfarad	50/60 Hz	0.5 Lb
CAP-40/1/440R	Dual	3	440 Volt	40+1 Microfarad	50/60 Hz	.04 Lb
CAP-40/3/440R	Dual	3	440 Volt	40+3 Microfarad	50/60 Hz	.04 Lb
CAP-40/4/440R	Dual	3	440 Volt	40+4 Microfarad	50/60 Hz	.04 Lb
CAP-40/5/440R	Dual	3	440 Volt	40+5 Microfarad	50/60 Hz	0.5 Lb
CAP-40/5/440	Dual	3	440 Volt	40+5 Microfarad	50/60 Hz	0.5 Lb
CAP-40/7.5/440R	Dual	3	440 Volt	40+7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-40/7.5/440	Dual	3	440 Volt	40+7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-40/10/440R	Dual	3	440 Volt	40+10 Microfarad	50/60 Hz	0.5 Lb
CAP-40/10/440	Dual	3	440 Volt	40+10 Microfarad	50/60 Hz	.04 Lb
CAP-40/440R	Single	3	440 Volt	40 Microfarad	50/60 Hz	.04 Lb
CAP-40/440	Single	3	440 Volt	40 Microfarad	50/60 Hz	0.5 Lb
CAP-45/3/440R	Dual	3	440 Volt	45+3 Microfarad	50/60 Hz	0.5 Lb
CAP-45/5/440R	Dual	3	440 Volt	45+5 Microfarad	50/60 Hz	0.5 Lb
CAP-45/5/440	Dual	3	440 Volt	45+5 Microfarad	50/60 Hz	0.5 Lb

# Motor Run Capacitor

## HCK Series

### Ordering Information (cont.)

LITTELFUSE CATALOG NUMBER	CONTACTOR FORM PER CIRCUIT	FULL LOAD CURRENT INDUCTIVE	FULL LOAD CURRENT RESISTIVE	LOCKED ROTOR CURRENT	LOCKED ROTOR CURRENT	LOCKED ROTOR WEIGHT
CAP-45/7.5/440R	Dual	3	440 Volt	45+7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-45/7.5/440	Dual	3	440 Volt	45+7.5 Microfarad	50/60 Hz	0.5 Lb
CAP-45/10/440R	Dual	3	440 Volt	45+10 Microfarad	50/60 Hz	0.5 Lb
CAP-45/440R	Single	3	440 Volt	45 Microfarad	50/60 Hz	.04 Lb
CAP-45/440	Single	3	440 Volt	45 Microfarad	50/60 Hz	0.5 Lb
CAP-50/5/440R	Dual	3	440 Volt	50+5 Microfarad	50/60 Hz	0.6 Lb2 Lb
CAP-50/5/440	Dual	3	440 Volt	50+5 Microfarad	50/60 Hz	0.6 Lb2 Lb
CAP-50/7.5/440R	Dual	3	440 Volt	50+7.5 Microfarad	50/60 Hz	0.6 Lb2 Lb
CAP-50/7.5/440	Dual	3	440 Volt	50+7.5 Microfarad	50/60 Hz	0.6 Lb2 Lb
CAP-50/10/440R	Dual	3	440 Volt	50+10 Microfarad	50/60 Hz	0.6 Lb2 Lb
CAP-50/440R	Single	3	440 Volt	50 Microfarad	50/60 Hz	0.6 Lb1 Lb
CAP-50/440	Single	3	440 Volt	50 Microfarad	50/60 Hz	0.6 Lb1 Lb
CAP-55/4/440R	Dual	3	440 Volt	55+4 Microfarad	50/60 Hz	0.6 Lb2 Lb
CAP-55/5/440R	Dual	3	440 Volt	55+5 Microfarad	50/60 Hz	0.6 Lb2 Lb
CAP-55/5/440	Dual	3	440 Volt	55+5 Microfarad	50/60 Hz	0.6 Lb2 Lb
CAP-55/7.5/440R	Dual	3	440 Volt	55+7.5 Microfarad	50/60 Hz	0.6 Lb2 Lb
CAP-55/7.5/440	Dual	3	440 Volt	55+7.5 Microfarad	50/60 Hz	0.6 Lb2 Lb
CAP-55/10/440R	Dual	3	440 Volt	55+10 Microfarad	50/60 Hz	0.6 Lb
CAP-55/15/440R	Dual	3	440 Volt	55+15 Microfarad	50/60 Hz	0.6 Lb
CAP-55/440R	Single	3	440 Volt	55 Microfarad	50/60 Hz	0.6 Lb
CAP-55/440	Single	3	440 Volt	55 Microfarad	50/60 Hz	0.6 Lb
CAP-60/5/440R	Dual	3	440 Volt	60+5 Microfarad	50/60 Hz	0.77 Lb
CAP-60/5/440	Dual	3	440 Volt	60+5 Microfarad	50/60 Hz	0.77 Lb
CAP-60/7.5/440R	Dual	3	440 Volt	60+7.5 Microfarad	50/60 Hz	0.77 Lb
CAP-60/10/440R	Dual	3	440 Volt	60+10 Microfarad	50/60 Hz	0.88 Lb
CAP-60/10/440	Dual	3	440 Volt	60+10 Microfarad	50/60 Hz	0.88 Lb
CAP-60/440R	Single	3	440 Volt	60 Microfarad	50/60 Hz	0.6 Lb
CAP-60/440	Single	3	440 Volt	60 Microfarad	50/60 Hz	0.6 Lb
CAP-65/7.5/440R	Dual	3	440 Volt	65+7.5 Microfarad	50/60 Hz	0.77 Lb
CAP-70/5/440R	Dual	3	440 Volt	70+5 Microfarad	50/60 Hz	0.85 Lb
CAP-70/5/440	Dual	3	440 Volt	70+5 Microfarad	50/60 Hz	0.85 Lb
CAP-70/7.5/440R	Dual	3	440 Volt	70+7.5 Microfarad	50/60 Hz	0.85 Lb
CAP-70/10/440R	Dual	3	440 Volt	70+10 Microfarad	50/60 Hz	0.85 Lb
CAP-70/440R	Single	3	440 Volt	70 Microfarad	50/60 Hz	0.85 Lb
CAP-70/440	Single	3	440 Volt	70 Microfarad	50/60 Hz	1.03 Lb
CAP-80/5/440R	Dual	3	440 Volt	80+5 Microfarad	50/60 Hz	0.71 Lb
CAP-80/5/440	Dual	3	440 Volt	80+7.5 Microfarad	50/60 Hz	0.71 Lb
CAP-80/7.5/440R	Dual	3	440 Volt	80+7.5 Microfarad	50/60 Hz	0.71 Lb

# Motor Run Capacitor

## HCK Series

### Ordering Information (cont.)

LITTELFUSE CATALOG NUMBER	CONTACTOR FORM PER CIRCUIT	FULL LOAD CURRENT INDUCTIVE	FULL LOAD CURRENT RESISTIVE	LOCKED ROTOR CURRENT	LOCKED ROTOR CURRENT	LOCKED ROTOR WEIGHT
CAP-80/7.5/440	Dual	3	440 Volt	80+7.5 Microfarad	50/60 Hz	0.71 Lb
CAP-80/10/440R	Dual	3	440 Volt	80+10 Microfarad	50/60 Hz	0.71 Lb
CAP-80/440R	Single	3	440 Volt	80 Microfarad	50/60 Hz	0.85 Lb
CAP-80/440	Single	3	440 Volt	80 Microfarad	50/60 Hz	0.85 Lb

### Dimensions

LITTELFUSE CATALOG NUMBER	HEIGHT - IN.(MM)	LENGTH - IN. (MM)	WIDTH - IN. (MM)
CAP-3/440R	3 (76.2)	2 (50.8)	2 (50.8)
CAP-3/440	2.13 (54.1)	2.64 (67.06)	2.13 (54.1)
CAP-4/440R	2.13 (54.1)	2.64 (67.06)	2.13 (54.1)
CAP-4/440	2.13 (54.1)	2.64 (67.06)	2.13 (54.1)
CAP-5/440R	2.13 (54.1)	2.64 (67.06)	2.13 (54.1)
CAP-5/440	2.13 (54.1)	2.64 (67.06)	2.13 (54.1)
CAP-6/440	2.5 (63.5)	2 (50.8)	2.2 (55.88)
CAP-7.5/440R	2.13 (54.1)	2.64 (67.06)	2.13 (54.1)
CAP-7.5/440	2.13 (54.1)	2.64 (67.06)	2.13 (54.1)
CAP-10/10/440R	3 (76.2)	2 (50.8)	2 (50.8)
CAP-10/440R	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-10/440	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-12.5/440R	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-12.5/440	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-15/3/440R	3 (76.2)	2 (50.8)	2 (50.8)
CAP-15/5/440R	3.5 (88.9)	2 (50.8)	2 (50.8)
CAP-15/5/440	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-15/7.5/440R	3 (76.2)	2 (50.8)	2 (50.8)
CAP-15/10/440R	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-15/440R	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-15/440	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-17.5/440	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-20/5/440R	3.5 (88.9)	2 (50.8)	2 (50.8)
CAP-20/5/440	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-20/7.5/440R	2.07 (52.58)	3.82 (97.03)	2.07 (52.58)
CAP-20/10/440R	2.13 (54.1)	3.4 (86.87)	2.13 (54.1)
CAP-20/440R	3 (76.2)	2 (50.8)	2 (50.8)
CAP-20/440	2.9 (73.66)	3.4 (86.87)	2.9 (73.66)
CAP-25/5/440R	2.07 (52.58)	3.82 (97.03)	2.07 (52.58)
CAP-25/5/440	2.07 (52.58)	3.82 (97.03)	2.07 (52.58)

# Motor Run Capacitor

## HCK Series

### Dimensions (cont.)

LITTELFUSE CATALOG NUMBER	HEIGHT - IN.(MM)	LENGTH - IN. (MM)	WIDTH - IN. (MM)
CAP-25/7.5/440R	2.07 (52.58)	3.82 (97.03)	2.07 (52.58)
CAP-25/7.5/440	2.07 (52.58)	3.82 (97.03)	2.07 (52.58)
CAP-25/10/440R	2.07 (52.58)	3.82 (97.03)	2.07 (52.58)
CAP-25/15/440	2.9 (73.66)	1.9 (48.26)	4.6 (116.84)
CAP-25/440R	2.5 (63.5)	2 (50.8)	2 (50.8)
CAP-25/440	2.9 (73.66)	3.4 ( 86.87)	2.9 (73.66)
CAP-30/3/440R	3 (76.2)	2 (50.8)	2 (50.8)
CAP-30/5/440R	2.07 (52.58)	3.82 (97.03)	2.07 (52.58)
CAP-30/5/440	2.9 (73.66)	4.6 (116.84)	2.9 (73.66)
CAP-30/7.5/440R	2.07 (52.58)	4.6 (116.84)	2.07 (52.58)
CAP-30/7.5/440	4 (101.6)	2 (50.8)	2 (50.8)
CAP-30/10/440R	4 (101.6)	2 (50.8)	2 (50.8)
CAP-30/15/440R	3 (76.2)	2.3 (58.42)	2.3 (58.42)
CAP-30/440R	2.07 (52.58)	3.82 (97.03)	2.07 (52.58)
CAP-30/440	2.9 (73.66)	3.82 (97.03)	2.9 (73.66)
CAP-35/1/440R	2.07 (52.58)	4.6 (116.84)	2.07 (52.58)
CAP-35/3/440R	2.07 (52.58)	4.41 (112.01)	2.07 (52.58)
CAP-35/3/440	2.07 (52.58)	4.41 (112.01)	2.07 (52.58)
CAP-35/5/440R	2.07 (52.58)	4.41 (112.01)	2.07 (52.58)
CAP-35/5/440	2.07 (52.58)	4.41 (112.01)	2.07 (52.58)
CAP-35/7.5/440R	2.07 (52.58)	4.8 (121.92)	2.07 (52.58)
CAP-35/7.5/440	2.07 (52.58)	4.6 (116.84)	2.07 (52.58)
CAP-35/10/440R	4 (101.6)	2 (50.8)	2 (50.8)
CAP-35/10/440	2.07 (52.58)	4.6 (116.84)	2.07 (52.58)
CAP-35/15/440R	3.2 (81.28)	2.3 (58.42)	2.3 (58.42)
CAP-35/440R	2.07 (52.58)	4.41 (112.01)	2.07 (52.58)
CAP-35/440	2.9 (73.66)	4.41 (112.01)	2.9 (73.66)
CAP-40/1/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-40/3/440R	2.07 (52.58)	4.8 (121.92)	2.07 (52.58)
CAP-40/4/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-40/5/440R	2.07 (52.58)	4.8 (121.92)	2.07 (52.58)
CAP-40/5/440	2.9 (73.66)	4.41 (112.01)	2.9 (73.66)
CAP-40/7.5/440R	2.07 (52.58)	4.8 (121.92)	2.07 (52.58)
CAP-40/7.5/440	3.4 ( 86.36)	2.4 (60.96)	2.6 (66.04)
CAP-40/10/440R	4 (101.6)	2 (50.8)	2 (50.8)
CAP-40/10/440	3.4 ( 86.36)	2.4 (60.96)	2.6 (66.04)
CAP-40/440R	2.07 (52.58)	4.8 (121.92)	2.07 (52.58)
CAP-40/440	2.9 (73.66)	4.8 (121.92)	2.9 (73.66)
CAP-45/3/440R	3.5 (88.9)	2 (50.8)	2 (50.8)

# Motor Run Capacitor

## HCK Series

### Dimensions (cont.)

LITTELFUSE CATALOG NUMBER	HEIGHT - IN.(MM)	LENGTH - IN. (MM)	WIDTH - IN. (MM)
CAP-45/5/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-45/5/440	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-45/7.5/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-45/7.5/440	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-45/10/440R	4.25 (107.95)	2 (50.8)	2.5 (63.5)
CAP-45/440R	2.07 (52.58)	4.8 (121.92)	2.07 (52.58)
CAP-45/440	2.9 (73.66)	4.8 (121.92)	2.9 (73.66)
CAP-50/5/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-50/5/440	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-50/7.5/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-50/7.5/440	3.8 (96.52)	2.4 (60.96)	2.6 (66.04)
CAP-50/10/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-50/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-50/440	2.9 (73.66)	5.39 (136.91)	2.9 (73.66)
CAP-55/4/440R	3.8 (96.52)	2.4 (60.96)	2.4 (60.96)
CAP-55/5/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-55/5/440	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-55/7.5/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-55/7.5/440	2.46 (62.48)	4.8 (121.92)	2.46 (62.48)
CAP-55/10/440R	3.8 (96.52)	2.4 (60.96)	2.4 (60.96)
CAP-55/15/440R	3.8 (96.52)	2.4 (60.96)	2.4 (60.96)
CAP-55/440R	2.46 (62.48)	4.41 (112.01)	2.46 (62.48)
CAP-55/440	3.64 (92.46)	4.01 (101.85)	3.64 (92.46)
CAP-60/5/440R	2.46 (62.48)	4.8 (121.92)	2.46 (62.48)
CAP-60/5/440	2.46 (62.48)	4.8 (121.92)	2.46 (62.48)
CAP-60/7.5/440R	2.46 (62.48)	4.8 (121.92)	2.46 (62.48)
CAP-60/10/440R	2.46 (62.48)	5.39 (136.91)	2.46 (62.48)
CAP-60/10/440	2.46 (62.48)	5.39 (136.91)	2.46 (62.48)
CAP-60/440R	2.46 (62.48)	4.33 (109.98)	2.46 (62.48)
CAP-60/440	3.64 (92.46)	4.33 (109.98)	3.64 (92.46)
CAP-65/7.5/440R	2.46 (62.48)	4.8 (121.92)	2.46 (62.48)
CAP-70/5/440R	3.64 (92.46)	4.8 (121.92)	3.64 (92.46)
CAP-70/5/440	3.64 (92.46)	4.8 (121.92)	3.64 (92.46)
CAP-70/7.5/440R	4.1 (104.14)	2.5 (63.5)	2.5 (63.5)
CAP-70/10/440R	4.25 (107.95)	2 (50.8)	2.5 (63.5)
CAP-70/440R	4 (101.6)	2 (50.8)	2 (50.8)
CAP-70/440	3.64 (92.46)	4.8 (121.92)	3.64 (92.46)
CAP-80/5/440R	2.46 (62.48)	5.39 (136.91)	2.46 (62.48)
CAP-80/5/440	2.46 (62.48)	5.39 (136.91)	2.46 (62.48)

# Motor Run Capacitor

## HCK Series

### Dimensions (cont.)

LITTELFUSE CATALOG NUMBER	HEIGHT - IN.(MM)	LENGTH - IN. (MM)	WIDTH - IN. (MM)
CAP-80/7.5/440R	2.46 (62.48)	5.39 (136.91)	2.46 (62.48)
CAP-80/7.5/440	2.46 (62.48)	5.39 (136.91)	2.46 (62.48)
CAP-80/10/440R	2.58 (65.53)	5.39 (136.91)	2.58 (65.53)
CAP-80/440R	2.58 (65.53)	4.8 (121.92)	2.58 (65.53)
CAP-80/440	4.8 (121.92)	2 (50.8)	2 (50.8)

**Disclaimer Notice** – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/product-disclaimer](http://www.littelfuse.com/product-disclaimer).