Type PMA-KB-03-Q2S (formerly PKA-02) Panel Mount Fuse Holder 1/4" x 11/4" (6.3 x 32mm) Fuses Knob / Bayonet



www.optifuse.com

(619) 593-5050

Electrical Rating: 10A, 250V AC **Fuse Style:** 1/4" x 11/4" (6.3 x 32mm)

Material:

Frame and Cap: Phenolic (UL flame: 94V-1)

Terminals: Nickel-plated brass **Cap:** Knob type, Bayonet type

Max. Operating Temperature: 150°C


Mounting: by nut

Terminal: Solder/Quick-Connect 6.4mm / 0.250"

Panel Thickness: 0.5 ~ 6.5mm **Agency Standards and Listings:**



Product Dimensions: Inches [mm]



Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



- -Fuse Holders are not intended for circuit disconnect. All power should be disconnected before removing fuse.
- -Avoid contact of Fuse Holder with chemical solvent. Prolonged contact will damage the device performance.

Note: All specifications subject to change without notice.

Rev C 08/2021 - Page: 1/1 Code S02