



		1		
Part Number:		DRAWN	0/0/2016	
CC400	0408-1	CJ	8/9/2016	
SC400		CHECKED	8/9/2016	
		P.D.		
Description:	c Speaker	APPROVED	8/9/2016	
Dynamic		J.S.	0/3/2010	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


## Top View



## Side View



## **Bottom View**



Items	Specifications	Conditions					
Sound Pressure Level	89±3	dB (@ 10cm)					
Resonant Frequency	450	Hz	REVISION HISTORY				
Frequency Range	450 ~ 20,000	Hz	REV	DESCRIPTION	DATE	APPROVED	
Nominal Power	1	W		Released from Engineering	2/5/2014	J.S.	
Max. Power	2	W	1	Updated to new template	8/9/2016	J.S.	
Impedance	8	Ω	NOTES				
Cone Material	Cloth		All dimensions are in mm unless otherwise noted				
Mount Type	Flush Mount		2) All tolerances are ± 0.5 mm unless otherwise noted				
Storage Temperature	-40 ~ +80	℃	3) All parts meet RoHS				
Operating Temperature	-40 ~ +70	∘C	4) Subject to change or redrawn without notice				
Weight	7.6	g					