#### **Power Transistors**

TO-220 Case





Standard

Optional

TYPE	TYPE NO.		PD	BVCBO	BVCEO	h	FE	@ lc	V <sub>CE(SAT)</sub>	@ l <sub>C</sub>	fT
NPN	PNP	(A) MAX	(W)	(V) MIN	(V) MIN	MIN	MAX	(A)	(V) MAX	(A)	(MHz) MIN
2N5294		4.0	36	80	70	30	120	0.5	1.0	0.5	0.8
2N5296		4.0	36	60	40	30	120	1.0	1.0	1.0	0.8
2N5298		4.0	36	80	60	20	80	1.5	1.0	1.5	0.8
2N5490		7.0	50	60	40	20	100	2.0	1.0	2.0	0.8
2N5492		7.0	50	75	55	20	100	2.5	1.0	2.5	0.8
2N5494		7.0	50	60	40	20	100	3.0	1.0	3.0	0.8
2N5496		7.0	50	90	70	20	100	3.5	1.0	35	0.8
2N6043	2N6040	10	75	60	60	1,000	20,000	4.0	2.0	4.0	4.0
2N6044	2N6041	10	75	80	80	1,000	20,000	4.0	2.0	4.0	4.0
2N6045	2N6042	10	75	100	100	1,000	20,000	3.0	2.0	3.0	4.0
2N6099		10	75	70	60	20	80	4.0	2.5	10	5.0
2N6101		10	75	80	70	20	80	5.0	2.5	10	5.0
2N6103		16	75	45	40	15	80	8.0	2.5	16	5.0
2N6121	2N6124	4.0	40	45	45	25	100	1.5	0.6	1.5	2.5
2N6122	2N6125	4.0	40	60	60	25	100	1.5	0.6	1.5	2.5
2N6123	2N6126	4.0	40	80	80	20	80	1.5	0.6	1.5	2.5
2N6129	2N6132	7.0	50	40	40	20	100	2.5	1.4	7.0	2.5
2N6130	2N6133	7.0	50	60	60	20	100	2.5	1.4	7.0	2.5
2N6131	2N6134	7.0	50	80	80	20	100	2.5	1.8	7.0	2.5
2N6288	2N6111	7.0	40	40	30	30	150	2.0	3.5	7.0	4.0
2N6290	2N6109	7.0	40	60	50	30	150	2.5	3.5	7.0	4.0
2N6292	2N6107	7.0	40	80	70	30	150	3.0	3.5	7.0	4.0
2N6386	2N6666	8.0	65	40	40	1,000	20,000	3.0	2.0	3.0	20
2N6387	2N6667	10	65	60	60	1,000	20,000	5.0	2.0	5.0	20
2N6388	2N6668	10	65	80	80	1,000	20,000	5.0	2.0	5.0	20
2N6473	2N6475	4.0	40	110	100	15	150	1.5	1.2	1.5	4.0
2N6474	2N6476	4.0	40	130	120	15	150	1.5	1.2	1.5	4.0
2N6486	2N6489	15	75	50	40	20	150	5.0	1.3	5.0	5.0
2N6487	2N6490	15	75	70	60	20	150	5.0	1.3	5.0	5.0
2N6488	2N6491	15	75	90	80	20	150	5.0	1.3	5.0	5.0
	4	TM		1				1	Shaded are	as indicate	Darlington

**Central semiconductor corp.**www.centralsemi.com

Shaded areas indicate Darlington.

(6-December 2004)

#### **OUTSTANDING SUPPORT AND SUPERIOR SERVICES**



#### PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- · Inventory bonding
- · Consolidated shipping options

- · Custom bar coding for shipments
- · Custom product packing

#### **DESIGNER SUPPORT/SERVICES**

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free guick ship samples (2<sup>nd</sup> day air)
- Online technical data and parametric search
- SPICE models
- · Custom electrical curves
- · Environmental regulation compliance
- · Customer specific screening
- Up-screening capabilities

- · Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- · Application and design sample kits
- Custom product and package development

#### REQUESTING PRODUCT PLATING

- 1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
- 2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

#### **CONTACT US**

#### Corporate Headquarters & Customer Support Team

Central Semiconductor Corp. 145 Adams Avenue Hauppauge, NY 11788 USA

Main Tel: (631) 435-1110 Main Fax: (631) 435-1824

Support Team Fax: (631) 435-3388

www.centralsemi.com

Worldwide Field Representatives: www.centralsemi.com/wwreps

**Worldwide Distributors:** 

www.centralsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: <a href="https://www.centralsemi.com/terms">www.centralsemi.com/terms</a>

www.centralsemi.com (001)



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	
Last Shipment Date	Stock Only

Please be advised that Central Semiconductor must immediately discontinue the product(s) listed in the attached PDN notice. Orders can only be accepted for products with available inventory on hand.

You may have purchased one or more of the products listed. Please do not hesitate to contact your local Central Semiconductor sales representative with any questions or needs you may have. Central regrets any inconvenience this may cause.

Sincerely,

Central Semiconductor Corp.

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	
Last Shipment Date	Stock Only

Summary: The following power transistors are discontinued and now classified as of End of Life (EOL). NOTE: If inventory has been depleted, some devices may be available on special order; please contact your Central salesperson, manufacturer's rep, franchised distributor, or inquiry@centralsemi.com.

Although Central Semiconductor Corp. makes every effort to continue to produce devices that have been proclaimed EOL (End of Life) by other manufacturers, it is an accepted industry practice to discontinue certain devices when customer demand falls below a minimum level of sustainability. Accordingly, the following product(s) have been transitioned to End of Life status as part of Central's ongoing Product Portfolio Management. Any replacement products are noted below. The effective date for placing last purchase orders will be six (6) months from the date of this notice and twelve (12) months from the notice date for final shipments, and minimum order quantities may apply. The last purchase and shipment dates may be extended if inventory is available.

#### \* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement
BDW51	N/A
BDW51A	N/A
BDW51B	N/A
BDW51C	N/A
BDW52	N/A
BDW52A	N/A
BDW52B	N/A
BDW52C	N/A
BDW94B	N/A
BDX20	N/A
BDX54	N/A
BDX54B	N/A
BDX54C	N/A
BDX54E	N/A
BDX85	N/A
BDX85A	N/A
BDX85B	N/A
BDX85C	N/A
BDX87	N/A
BDX87A	N/A
BDX87B	N/A
BDX87C	N/A
BDY90	N/A
BD135	N/A
BD135 SL	N/A
BD135-10 SL	N/A
BD135-16	N/A
BD135-16 SL	N/A
BD136	N/A
BD136-10	N/A
BD136-10 SL	N/A
BD136-16	N/A
BD136-16 SL	N/A
BD137	N/A
*** CONTINUED ***	

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

\* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement	
BD137-10	N/A	
BD137-10 SL	N/A	
BD137-16	N/A	
BD138	N/A	
BD138-10	N/A	
BD138-10 SL	N/A	
BD138-16	N/A	
BD138-16 SL	N/A	
BD139	N/A	
BD139-10	N/A	
BD139-10 SL	N/A	
BD139-16	N/A	
BD139-16 SL	N/A	
BD140	N/A	
BD140-10	N/A	
BD140-10 SL	N/A	
BD140-16	N/A	
BD140-16 SL	N/A	
BD157	N/A	
BD158	N/A	
BD159	N/A	
BD175	N/A	
BD176	N/A	
BD177	N/A	
BD178	N/A	
BD179	N/A	
BD180	N/A	
BD201	N/A	
BD204	N/A	
BD233	N/A	
BD234	N/A	
BD235	N/A	
BD236	N/A	
BD237	N/A	
BD238	N/A	
BD238 SL	N/A	
BD433	N/A	
BD434		
BD437	N/A	
	N/A	
BD438	N/A	
BD439	N/A	
BD440	N/A	
BD441 * CONTINUED ***	N/A	

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

\* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement	
BD442	N/A	
BD537	N/A	
BD538	N/A	
BD675	N/A	
BD675A	N/A	
BD676	N/A	
BD676A	N/A	
BD676A SL	N/A	
BD677	N/A	
BD677A	N/A	
BD678	N/A	
BD678A	N/A	
BD679	N/A	
BD679A	N/A	
BD679A SL	N/A	
BD680	N/A	
BD680A	N/A	
BD680A SL	N/A	
BD681	N/A	
BD681 SL	N/A	
BD682	N/A	
BD682 SL	N/A	
BD683	N/A	
BD683 SL	N/A	
BD908	N/A	
BF457	N/A	
BF458	N/A	
BF459	N/A	
BF459 SL	N/A	
BF469	N/A N/A	
BF471	N/A N/A	
BF472	N/A N/A	
BUW34	N/A N/A	
BUW35	N/A	
BUW36	N/A	
BUW44	N/A	
BUW45	N/A	
BUW46	N/A	
BUX43	N/A	
BUX44	N/A	
BUX47	N/A	
BUX48	N/A	
BUX80	N/A	

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

\* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement
BUY69A	N/A
BUY69B	N/A
BUY69C	N/A
BU408	N/A
BU409	N/A
CEN1025	N/A
CEN1037	N/A
CEN1063	N/A
CEN1092	N/A
CEN1102	N/A
CEN1111	N/A
CEN1177	N/A
CEN1247	N/A
CEN1306	N/A
CEN1323	N/A
CEN1328	N/A
CEN1364 SL	N/A
CEN1378 SL	N/A
CEN1391	N/A
CEN1396	N/A
CEN1406	N/A
CEN1416	N/A
CEN1439	N/A
CEN1450	N/A
CEN496	N/A
CEN537	N/A
CEN591	N/A
CEN596	N/A
CEN644	N/A
CEN671	N/A
CEN698-1	N/A
CEN698-2	N/A
CEN774	N/A
CEN821	N/A
CEN844	N/A
CEN925	N/A
CEN951	N/A
CEN961	N/A
CEN972	N/A
CEN992	N/A
CM3441	N/A
CP166-BUP54-WN	N/A
CP230-CZT122-CT	CP260-TIP122-CT
* CONTINUED ***	

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

\* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

An I lating types (I DF REE, I II (I LEAD) for each item isted are included in this notice.				
Central Part Number	Suggested Replacement			
CP230-HTIP122-CM	N/A			
CP230-H2N6039-CM	N/A			
CP230-TIP122-CM	CP260-TIP122-CM			
CP230-TIP122-CT	CP260-TIP122-CT			
CP230-TIP122-CT20	N/A			
CP230-2N6039-CM	N/A			
CP230-2N6039-CT	N/A			
CP230-2N6039-WN	N/A			
CP630-CEN1263-WN	CP660-TIP127-WN			
CP630-CZT127-CT	CP660-TIP127-CT			
CP630-HTIP127-CM	N/A			
CP630-TIP127-CT	CP660-TIP127-CT			
CP630-TIP127-WN	CP660-TIP127-WN			
CP630-2N6036-CT	N/A			
CZT122 BK	N/A			
CZT122 DR CZT122 TR	N/A			
CZT122 TK CZT127 BK	N/A			
CZT127 TR	N/A			
CZT31C BK	N/A			
CZT31C TR	N/A			
D44C12	N/A			
D44E1	N/A			
D44E3	N/A			
D45E3	N/A			
D45H8	N/A			
MJE13003	N/A			
MJE13003 SL	N/A			
MJE13005	N/A			
MJE13005 SL	N/A			
MJE13006	N/A			
MJE13008	N/A			
MJE13009	N/A			
MJE15030	N/A			
MJE15031	N/A			
MJE170	N/A			
MJE171	N/A			
MJE172	N/A			
MJE180	N/A			
MJE181	N/A			
MJE182	N/A			
MJE200	N/A			
MJE210	N/A			
MJE220	N/A			
*** CONTINUED ***				

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

\* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement	
MJE221	N/A	
MJE222	N/A	
MJE223	N/A	
MJE224	N/A	
MJE225	N/A	
MJE230	N/A	
MJE231	N/A	
MJE232	N/A	
MJE233	N/A	
MJE234	N/A	
MJE235	N/A	
MJE2360T	N/A	
MJE240	N/A	
MJE241	N/A	
MJE242	N/A	
MJE243	N/A	
MJE244	N/A	
MJE250	N/A	
MJE250 MJE251	N/A	
MJE251 MJE252	N/A	
MJE253	N/A	
MJE254	N/A	
MJE2801T	N/A	
MJE2901T	N/A	
MJE2955T	N/A	
MJE340	N/A	
MJE341	N/A	
MJE344	N/A	
MJE344 SL	N/A	
MJE3440	N/A	
MJE350	N/A	
MJE370	N/A	
MJE371	N/A	
MJE520	N/A	
MJE521	N/A	
MJE700	N/A	
MJE701	N/A	
MJE702	N/A	
MJE703	N/A	
MJE710	N/A	
MJE711	N/A	
MJE712	N/A	
MJE720	N/A	
** CONTINUED ***		

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	Stock Only
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

<sup>\*</sup> All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement	
MJE721	N/A	
MJE722	N/A	
MJE800	N/A	
MJE800T	N/A	
MJE801	N/A	
MJE801T	N/A	
MJE802	N/A	
MJE802T	N/A	
MJE803	N/A	
MJE803T	N/A	
MJ1000	N/A	
MJ1001	N/A	
MJ10012	N/A	
MJ11011	N/A	
MJ11011 MJ11012	N/A	
MJ11012 MJ11013	N/A N/A	
MJ11013		
	N/A	
MJ11015	N/A	
MJ11016	N/A	
MJ2501	N/A	
MJ2955	N/A	
MJ3000	N/A	
MJ3001	N/A	
MJ4033	N/A	
MJ4035	N/A	
MJ410	N/A	
MJ802	N/A	
MJ901	N/A	
PMD10K100	N/A	
PMD10K40	N/A	
PMD10K60	N/A	
PMD10K80	N/A	
PMD12K100	N/A	
PMD12K40	N/A	
PMD12K60	N/A	
PMD12K80	N/A	
PMD13K100	N/A	
PMD16K100	N/A	
PMD16K60	N/A	
PMD16K80	N/A	
PMD1601K	N/A N/A	
PMD1602K	N/A N/A	
PMD1603K	N/A N/A	
* CONTINUED ***	1 <b>V/</b> /1	

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	Stock Only
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

<sup>\*</sup> All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement	
PMD17K100	N/A	
PMD17K60	N/A	
PMD17K80	N/A	
PMD1701K	N/A	
PMD1702K	N/A	
PMD1703K	N/A	
PMD18K100	N/A	
PMD18K60	N/A	
PMD18K80	N/A	
PMD19K100	N/A	
PMD19K60	N/A	
PMD19K80	N/A	
SE9303	N/A	
SE9304	N/A	
SE9305	N/A	
TIP102	N/A	
TIP107	N/A	
TIP107 SL	N/A	
TIP117	N/A	
TIP117 SL	N/A	
TIP122	N/A	
TIP122 SL	N/A	
TIP127	N/A	
TIP127 SL	N/A	
TIP132	N/A	
TIP137	N/A	
TIP140T	N/A	
TIP141T	N/A	
TIP1411 TIP142T	N/A N/A	
TIP1421 TIP145T	N/A N/A	
TIP146T	N/A	
TIP147T	N/A	
TIP29	N/A	
TIP29A	N/A	
TIP29A SL	N/A	
TIP29B	N/A	
TIP29C	N/A	
TIP31	N/A	
TIP31 SL	N/A	
TIP31A	N/A	
TIP31B	N/A	
TIP31C SL	N/A	
TIP32	N/A	

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	Stock Only
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

\* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement	
TIP32A	N/A	
TIP32A SL	N/A	
TIP32B	N/A	
TIP32C	N/A	
TIP41	N/A	
TIP41A	N/A	
TIP41B	N/A	
TIP41C	N/A	
TIP41C SL	N/A	
TIP42	N/A	
TIP42A	N/A	
TIP42B	N/A	
TIP42C	N/A	
TIP42C SL	N/A	
TIP42D	N/A	
2N3054	N/A	
2N3055	N/A	
2N3442	N/A	
2N3448	N/A	
2N3713	N/A	
2N3714	N/A	
2N3715	N/A	
2N3716	N/A	
2N3766	N/A	
2N3767	N/A	
2N3771	N/A	
2N3772	N/A	
2N3773	N/A	
2N3789	N/A	
2N3790	N/A	
2N3791	N/A	
2N3792	N/A	
2N3902	N/A	
2N4231	N/A	
2N4232	N/A	
2N4233	N/A	
2N4233 2N4347	N/A	
2N4348	N/A	
2N4348 2N4398	N/A N/A	
2N4398 2N4399	N/A N/A	
2N4991	N/A N/A	
2N4901 2N4902	N/A N/A	
2N4903 * CONTINUED ***	N/A	

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	_
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

\* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement	
2N4904	N/A	
2N4905	N/A	
2N4906	N/A	
2N4910	N/A	
2N4911	N/A	
2N4912	N/A	
2N4913	N/A	
2N4914	N/A	
2N4915	N/A	
2N4918	N/A	
2N4919	N/A	
2N4920	N/A	
2N4921	N/A	
2N4922	N/A	
2N4923	N/A	
2N4923 SL	N/A	
2N5067	N/A	
2N5068	N/A	
2N5069	N/A	
2N5192	N/A	
2N5192 SL	N/A	
2N5195	N/A	
2N5195 SL	N/A	
2N5240	N/A	
2N5294	N/A	
2N5294 2N5296	N/A	
2N5290 2N5297	N/A	
2N5297 SL	N/A	
2N5298	N/A	
2N5301	N/A	
2N5302	N/A	
2N5303	N/A	
2N5490	N/A	
2N5492	N/A	
2N5494	N/A	
2N5496	N/A	
2N5629	N/A	
2N5632	N/A	
2N5655	N/A	
2N5656	N/A	
2N5657	N/A	
2N5745	N/A	
2N5760	N/A	

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



DDN ID.	PDN01250
PUN IU:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	Stock Only
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

\* All Plating types (PBFREE.TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement	
2N5838	N/A	
2N5873	N/A	
2N5875	N/A	
2N5876	N/A	
2N5877	N/A	
2N5878	N/A	
2N5879	N/A	
2N5880	N/A	
2N5881	N/A	
2N5882	N/A	
2N5883	N/A	
2N5884	N/A	
2N5885	N/A	
2N5886	N/A	
2N6029	N/A	
2N6031	N/A	
2N6034	N/A	
2N6035	N/A	
2N6036	N/A	
2N6037	N/A	
2N6038	N/A	
2N6039 SL	N/A	
2N6040	N/A	
2N6042	N/A	
2N6043	N/A N/A	
2N6044	N/A N/A	
2N6045	N/A	
2N6050	N/A	
2N6051	N/A	
2N6052	N/A	
2N6055	N/A	
2N6056	N/A	
2N6057	N/A	
2N6058	N/A	
2N6059	N/A	
2N6099	N/A	
2N6107	N/A	
2N6109	N/A	
2N6111	N/A	
2N6121	N/A	
2N6122	N/A	
2N6123	N/A	
2N6124	N/A	

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	•
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

\* All Plating types (PBFREE.TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement	
2N6125	N/A	
2N6126	N/A	
2N6129	N/A	
2N6130	N/A	
2N6131	N/A	
2N6132	N/A	
2N6133	N/A	
2N6134	N/A	
2N6226	N/A	
2N6229	N/A	
2N6230	N/A	
2N6246	N/A	
2N6247	N/A	
2N6248	N/A	
2N6249	N/A	
2N6250	N/A	
2N6251	N/A	
2N6253	N/A	
2N6254	N/A	
2N6259	N/A	
2N6260	N/A	
2N6263	N/A	
2N6282	N/A	
2N6283	N/A	
2N6284	N/A	
2N6285	N/A	
2N6286	N/A	
2N6287	N/A	
2N6288	N/A	
2N6290	N/A	
2N6292	N/A	
2N6306	N/A	
2N6307	N/A	
2N6308	N/A	
2N6312	N/A	
2N6371	N/A	
2N6383	N/A	
2N6384	N/A	
2N6385	N/A	
2N6386	N/A	
2N6387	N/A	
2N6388	N/A N/A	
2N6465	N/A N/A	

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	Stock Only
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

\* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement	
2N6466	N/A	
2N6469	N/A	
2N6470	N/A	
2N6471	N/A	
2N6472	N/A	
2N6475	N/A	
2N6476	N/A	
2N6489	N/A	
2N6489 SL	N/A	
2N6490	N/A	
2N6491	N/A	
2N6497	N/A	
2N6498	N/A	
2N6498 SL	N/A	
2N6499	N/A	
2N6499 SL	N/A	
2N6530	N/A	
2N6531	N/A	
2N6532	N/A	
2N6543	N/A	
2N6544	N/A	
2N6545	N/A	
2N6546	N/A	
2N6547	N/A	
2N6569	N/A	
2N6576	N/A	
2N6577	N/A	
2N6578	N/A	
2N6594	N/A	
2N6609	N/A	
	N/A	
2N6666		
2N6667	N/A	
2N6668	N/A	
2N6671	N/A	
2N6672	N/A	
2N6673	N/A	
2N6674	N/A	
2N6675	N/A	
2N6677	N/A	
2N6678	N/A	
40250	N/A	
40312	N/A	

\*\*\* CONTINUED \*\*\*

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



submit an online inquiry.

opportunities/additional information.

## Product End of Life Notification

PDN ID:	PDN01250
Notification Date:	2/10/23
Last Buy Date:	Stock Only
Last Shipment Date	Stock Only

\*\*\* CONTINUED FROM PRIOR PAGE \*\*\*

<u>Central Part Number</u> <u>Suggested Replacement</u>

Central would be happy to assist you by providing additional information or technical data to help locate an alternate source if we have no replacement available. If you would like assistance, please visit https://my.centralsemi.com/submit-inquiry?type=ER to

\* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB



PDN ID:	PDN01192
Notification Date:	10/19/21
Last Buy Date:	4/19/22
Last Shipment Date	10/19/22

Summary: The following through-hole transistors are discontinued and now classified as of End of Life (EOL).

Although Central Semiconductor Corp. makes every effort to continue to produce devices that have been proclaimed EOL (End of Life) by other manufacturers, it is an accepted industry practice to discontinue certain devices when customer demand falls below a minimum level of sustainability. Accordingly, the following product(s) have been transitioned to End of Life status as part of Central's ongoing Product Management Process. Any replacement products are noted below. The effective date for placing last purchase orders will be six (6) months from the date of this notice and twelve (12) months from the notice date for final shipments, and minimum order quantities may apply. The last purchase and shipment dates may be extended if inventory is available.

#### \* All Plating types (PBFREE,TIN/LEAD) for each item listed are included in this notice.

Central Part Number	Suggested Replacement
BU911	N/A
CEN597	N/A
MJE3055T	N/A
MJ4034	N/A
2N2483	N/A
2N2540	N/A
2N3735	N/A
2N4407	N/A
2N5154	N/A
2N5337	N/A
2N6101	N/A
2N6488	N/A

Central would be happy to assist you by providing additional information or technical data to help locate an alternate source if we have no replacement available. If you would like assistance, please visit https://my.centralsemi.com/submit-inquiry?type=ER to submit an online inquiry.

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.