

TABLE OF CONTENTS	
SHEET NO.	SHEET DESCRIPTION
1	NOTES AND BOM
2	CONFIGURATIONS
3-4	KEY CONFIGURATIONS
5	BLADE SEALED ASSEMBLY
6	SYSTEM PACKAGING
7	BACKSHELL NOTES
8	BACKSHELL
9	BACKSHELL CONFIGURATIONS

NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:
a. APPLICATION SPECIFICATION SEE: AS-33472-100
-CONTAINS: PRODUCT INTRODUCTION, PRODUCT SUMMARY, CONNECTOR ASSEMBLY, PACKAGING INFORMATION, CONNECTOR MATING, SERVICE INSTRUCTIONS, ELECTRICAL CONTINUITY CHECKING, CRIMPING, AND TROUBLESHOOTING.
-DESIGNED TO MATE WITH RECEPTACLE SEALED ASSEMBLY AS SPECIFIED IN THE MATING CONNECTOR DRAWINGS CHART.
*DENOTES DRAWINGS THAT CAN BE ACCESSED AT <http://ewcap.uscarteams.org/>.
-ASSEMBLY SHIPPED WITH PLR IN PRE-LOCK POSITION (SEE PLR PRE-LOCK VIEW SHEET 5).

b. PRODUCT SPECIFICATION SEE:
-STANDARD CONFIGURATION: PS-33472-000
-UL V0 CONFIGURATION: TBD
CONTAINS: PRODUCT INTRODUCTION, PRODUCT SUMMARY, RATINGS (CURRENT, TEMPERATURE, SEALING, AND FLAMMABILITY), TERMINALS, WIRE DIAMETER RANGE, PRODUCT VALIDATION, AND PRODUCT DEVIATIONS.

c. PACKAGING SPECIFICATION PER MOLEX DRAWING: PK-31300-635


d. PARTS MUST BE IN COMPLIANCE TO MOLEX CHEMICAL SUBSTANCES FOR PRODUCTS AND PACKAGING SPECIFICATION: QEHS-699000-300

e. DATA MUST BE SUBMITTED UNDER THE MOLEX PART NUMBER TO IMDS (COMPANY ID#13255)


2. DESIGN - MATERIALS:
a. FOR BILL OF MATERIALS SEE:
-STANDARD CONFIGURATION: SD-33482-0002
-UL V0 CONFIGURATION: SD-160084-0002

3. DESIGN - GEOMETRY:
a. THE 3-D CAD DATA IS BASIC (WITHOUT TOLERANCE) AND MASTER FOR THIS PART WITH THE EXCEPTION OF UNDERLINED DIMENSIONS. DIMENSIONAL INFORMATION NOT SHOWN ON THIS DRAWING IS DEFINED BY THE DATA FILE AT ITS LATEST REVISION.
b. GEOMETRIC DIMENSIONS AND TOLERANCES PER ASME Y14.5M-2009
c. EDGES AND UNDIMENSIONED DETAILS PER ISO13715
d. CORNERS SHOWN AS SHARP TO BE R 0.2 MAX.
e. LETTERING SHALL BE 0.15 MAX RAISED IN 0.25 MAX RECESS PAD. THIS INCLUDES RECYCLING CODE, CAVITY ID, VENDOR IDENTIFICATION, AND CUSTOMER MATERIAL NUMBER.
f. VISUAL DEFECTS SHALL MEET COSMETIC STANDARD PS-45499-002 (Class B).
g. LASER MARKING:
1. PART NUMBER
2. DAY OF THE YEAR
3. SHIFT
4. YEAR
FOR ADDITIONAL INFORMATION SEE SECTION 5 UNDER PROCEDURES IN ES-34735-008.


MATING CONNECTOR DRAWINGS	
DESCRIPTION	MOLEX INLINE
2X2	SD-33472-0001
2X3	SD-33472-0001
2X4	SD-33472-0001
2X6	SD-33472-0001
2X8	SD-33472-0001
2X10	SD-33472-0001




2X2




2X3




2X4




2X6



2X8



2X10




REV	REV DESCRIPTION
E2	ADDED MOLEX BACKSHELL DETAILS
E1	MIGRATED FROM COCREATE AND IMPORTED DXF FILES
E	ADDED CHARTED DIMENSIONS FOR 2X2, 2X4, 2X6 AND 2X8 WITH CLIPSLLOT
D	MINOR GEOMETRY CHANGE FOR UL V0
C3	ADD 2X4
C2	ADD 2X3
C1	ADD UL V0 CONFIGURATIONS
C	ADD 2X8
B1	ADD 2X6 BACKSHELL INFO
B	ADD 2X6
A	INITIAL RELEASE
REV	REV DESCRIPTION


INSPECTION NUMBER LOG	
LAST NUMBER:	9
ADDED:	
REMOVED:	

SYMBOLS = 0 mm = 0 GENERAL TOLERANCES (UNLESS SPECIFIED) = 0 ANGULAR TOL ± 1.0° = 0 4 PLACES ± = 0 3 PLACES ± = 0 2 PLACES ± 0.1 = 0 1 PLACE ± 0.2 = 0 0 PLACES ± = 0 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16		 MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL	
	INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14		DOCUMENT NUMBER: SD-33482-0001			
	THIRD ANGLE PROJECTION		DRAWING: A1-SIZE		SERIES: 33482	
	MATERIAL NUMBER:		CUSTOMER: GENERAL MARKET		SHEET NUMBER: 1 OF 11	


SHEET DESCRIPTION
CONFIGURATIONS




2X2 - STANDARD (STD)




2X2 - UL V0*




2X3 - STANDARD (STD)




2X3 - LENGTHENED




2X4 - STANDARD (STD)




2X6 - STANDARD (STD)




2X8 - STANDARD (STD)



2X10 - STANDARD (STD)



2X10 - UL V0*



UL V0 UNIQUE FEATURE





Partial1
SCALE 10:1

* MINOR GEOMETRY CHANGE THAN STANDARD CONFIGURATION.
SEE NOTE 2a FOR MORE INFORMATION





SYMBOLS = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DIMENSION UNITS mm		SCALE 1.5:1		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16										
	GENERAL TOLERANCES (UNLESS SPECIFIED)		ANGULAR TOL ± 1.0°		4 PLACES ±		3 PLACES ±		2 PLACES ± 0.1					INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14		DOCUMENT NUMBER SD-33482-0001	
	1 PLACE ± 0.2		0 PLACES ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION 		DRAWING A1-SIZE		SERIES 33482		MATERIAL NUMBER CUSTOMER GENERAL MARKET		SHEET NUMBER 2 OF 11		

SHEET DESCRIPTION
KEY CONFIGURATIONS





2X2



2X3



2X4



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

SYMBOLS	DIMENSION UNITS	SCALE
	mm	3:1
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	ANGULAR TOL ± 1.0°	
	4 PLACES	±
	3 PLACES	±
	2 PLACES	± 0.1
	1 PLACE	± 0.2
	0 PLACES	±
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

CURRENT REV DESC:		
EC NO:	171650	
DRWN:	PMANJUNATHAC	2018/01/03
CHK'D:	MVANSLAMBROU	2018/02/16
APPR:	MVANSLAMBROU	2018/02/16
INITIAL REVISION:		
DRWN:	APROFFITT	2014/04/28
APPR:	VKOSHY	2014/05/14
THIRD ANGLE PROJECTION	DRAWING	SERIES
	A1-SIZE	33482


MX150 BLADE
DUAL ROW SEALED ASSEMBLY MAT SEAL

PRODUCT CUSTOMER DRAWING


DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-33482-0001	PSD	001	E2
MATERIAL NUMBER	CUSTOMER	SHEET NUMBER	
	GENERAL MARKET	3 OF 11	

SHEET DESCRIPTION
KEY CONFIGURATIONS CONT.


2X6




KEY A



KEY B




KEY C




KEY D


2X8




KEY A



KEY B




KEY C




KEY D


2X10




KEY A



KEY B



KEY C










KEY D

SYMBOLS = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	DIMENSION UNITS: mm SCALE: 3:1	CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16	 MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL		
	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 1.0° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.1 1 PLACE ± 0.2 0 PLACES ±	INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14	PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER: SD-33482-0001 DOC TYPE: PSD DOC PART: 001 REVISION: E2			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION 	DRAWING: A1-SIZE SERIES: 33482	MATERIAL NUMBER: GENERAL MARKET CUSTOMER: GENERAL MARKET	SHEET NUMBER: 4 OF 11		

SHEET DESCRIPTION
BLADE SEALED ASSEMBLY


DESCRIPTION	CHARTED DIMENSION				
	A	B	C	D	E
2X2	15.54	1.75	24.40	54.45	22.23
2X3 STANDARD	19.04	3.50	26.21	54.45	22.23
2X3 LENGTHENED	19.04	3.50	26.21	56.45	22.23
2X4	22.54	1.75	27.21	54.45	22.23
2X6	29.54	1.75	32.27	54.45	22.23
2X8	36.54	1.75	38.88	54.45	22.23
2X10	43.64	1.75	45.65	54.45	22.05

OPTIONAL LASER MARKING ON THIS SURFACE SEE NOTE 3g.



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN IN PRE-STAGED POSITION

SECTION W-W





PRIMARY LOCK REINFORCEMENT (PLR) SHOWN IN FINAL-LOCK POSITION

SECTION V-V

SYMBOLS THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION DIMENSION UNITS: mm SCALE: 3:1 GENERAL TOLERANCES (UNLESS SPECIFIED): ANGULAR TOL: ± 1.0° 4 PLACES: ± 3 PLACES: ± 2 PLACES: ± 0.1 1 PLACE: ± 0.2 0 PLACES: ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14		molex MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL		
DOCUMENT STATUS: P1 RELEASE DATE: 2018/02/16 22:02:26		PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER: SD-33482-0001 DOC TYPE: PSD DOC PART: 001 REVISION: E2		MATERIAL NUMBER: A1-SIZE CUSTOMER: GENERAL MARKET SHEET NUMBER: 5 OF 11		

SHEET DESCRIPTION
SYSTEM PACKAGING

CHARTED DIMENSION				
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS	
			K	L
2X2	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT	72.78	28.50
		LENGTHENED	77.21	28.00
2X3	STANDARD	W/O CLIPSLOT	72.78	28.00
		W/ CLIPSLOT		30.50
	LENGTHENED	W/O CLIPSLOT	74.79	28.00
		W/ CLIPSLOT		30.50
2X4	STANDARD	W/O CLIPSLOT	72.78	29.50
		W/ CLIPSLOT		31.50
2X6	STANDARD	W/O CLIPSLOT	72.79	35.58
		W/ CLIPSLOT		
2X8	STANDARD	W/O CLIPSLOT	72.67	42.25
		W/ CLIPSLOT		
2X10	STANDARD	STANDARD	72.78	49.05









SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	DIMENSION UNITS	SCALE	CURRENT REV DESC:						
	mm	4:1	EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16							
	GENERAL TOLERANCES (UNLESS SPECIFIED)				INITIAL REVISION:			PRODUCT CUSTOMER DRAWING		
	ANGULAR TOL ± 1.0°				DRWN: APROFFITT 2014/04/28			DOCUMENT NUMBER		
	4 PLACES ±				APPR: VKOSHY 2014/05/14			DOC TYPE DOC PART REVISION		
	3 PLACES ±				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SD-33482-0001 PSD 001 E2		
	2 PLACES ± 0.1				THIRD ANGLE PROJECTION			MATERIAL NUMBER		
	1 PLACE ± 0.2				DRAWING			CUSTOMER		
	0 PLACES ±				A1-SIZE			SHEET NUMBER		
	0 PLACES ±				SERIES			GENERAL MARKET		
				33482			6 OF 11			

SHEET DESCRIPTION
BACKSHELL NOTES


BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:
a. APPLICATION SPECIFICATION SEE: AS-34951-001
-DESIGNED TO MATE WITH BLADE SEALED ASSEMBLY SPECIFIED IN MOLEX DRAWING SD-33482-0001.
-SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm.
-COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY.
-DESIGN IS OWNED BY SCHLEMMER FOR SCHLEMMER BACKSHELL.
-DESIGN IS OWNED BY MOLEX FOR MOLEX BACKSHELL.
-90° ADAPTOR DESIGN IS OWNED BY MOLEX.
-FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34950-0001.









BACKSHELL CUSTOMER MODEL NUMBER LEGEND

- 34950-XXXX
- CUSTOMER MODEL COMPONENTS
 - 0 - SCHLEMMER BACKSHELL ONLY
 - 1 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
 - 2 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
 - 3 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
 - 4 - SCHLEMMER BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
 - 5 - MOLEX BACKSHELL ONLY
 - 6 - MOLEX BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
 - 7 - MOLEX BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
 - 8 - MOLEX BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
 - 9 - MOLEX BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
- BACKSHELL FEATURES
 - 1 - WITH RIBS
 - 2 - WITHOUT RIBS
 - 3 - 90° ADAPTOR
- MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20









SYMBOLS = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION DIMENSION UNITS: mm SCALE: 1.5:1		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16		 MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL		
	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 1.0° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.1 1 PLACE ± 0.2 0 PLACES ±		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING: A1-SIZE SERIES: 33482		MATERIAL NUMBER: CUSTOMER: GENERAL MARKET SHEET NUMBER: 7 OF 11	



SECTION A-A

SYMBOLS ∇ = 0 ∇ = 0 ∇ = 0 ∇ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ⊠ = 0 ⊠ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DIMENSION UNITS mm		SCALE 3.5:1	CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16				<div style="text-align: center;">molex</div> MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL													
	GENERAL TOLERANCES (UNLESS SPECIFIED)		ANGULAR TOL ± 1.0°		4 PLACES ±		3 PLACES ±		2 PLACES ± 0.1		1 PLACE ± 0.2		0 PLACES ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING A1-SIZE	SERIES 33482	INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14		PRODUCT CUSTOMER DRAWING	
DOCUMENT STATUS P1 RELEASE DATE 2018/02/16 22:02:26				DOCUMENT NUMBER SD-33482-0001			DOC TYPE DOC PART REVISION PSD 001 E2		MATERIAL NUMBER CUSTOMER GENERAL MARKET		SHEET NUMBER 8 OF 11												


SHEET DESCRIPTION
MOLEX BACKSHELL





SECTION B-B

SYMBOLS = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0 = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SCALE 3:1		CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16		 MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL			
	DIMENSION UNITS mm		GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 1.0°		INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14					DOCUMENT NUMBER SD-33482-0001
	4 PLACES ± 3 PLACES ± 2 PLACES ± 0.1 1 PLACE ± 0.2 0 PLACES ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION 	DRAWING A1-SIZE	SERIES 33482	MATERIAL NUMBER GENERAL MARKET	CUSTOMER GENERAL MARKET	SHEET NUMBER 9 OF 11
	DOCUMENT STATUS P1	RELEASE DATE 2018/02/16 22:02:26	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	SCALE 3:1	CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16	INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14	DOCUMENT NUMBER SD-33482-0001	DOC TYPE PSD	DOC PART 001	REVISION E2



SHEET DESCRIPTION
MOLEX BACKSHELL CONFIGURATIONS





OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL





OVERALL MATED SYSTEM WITH BLADE BACKSHELL




OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL



BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL



ADD THE VALUE OF 'Y' TO THE TOTAL DIMENSION WHENEVER ADAPTOR IS USED




CHARTED DIMENSIONS

CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS									
			U	V	W	X	Y	AA	AB	AC	AD	AE
2X4	STANDARD	STANDARD	115.24	94.36	93.93	75.62	32.10	32.93	32.54	32.85	31.76	56.81
2X8	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18
2X10	STANDARD	STANDARD	132.49	102.81	102.73	84.07	36.10	45.44	45.44	42.65	45.44	68.18

SYMBOLS ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0 ▽ = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION DIMENSION UNITS: mm SCALE: 1:1 GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 1.0° 4 PLACES ± 3 PLACES ± 2 PLACES ± 0.1 1 PLACE ± 0.2 0 PLACES ± DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	CURRENT REV DESC: EC NO: 171650 DRWN: PMANJUNATHAC 2018/01/03 CHK'D: MVANSLAMBROU 2018/02/16 APPR: MVANSLAMBROU 2018/02/16 INITIAL REVISION: DRWN: APROFFITT 2014/04/28 APPR: VKOSHY 2014/05/14	 MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL PRODUCT CUSTOMER DRAWING	
	DOCUMENT NUMBER: SD-33482-0001 DOC TYPE: PSD DOC PART: 001 REVISION: E2		MATERIAL NUMBER: 33482 CUSTOMER: GENERAL MARKET SHEET NUMBER: 11 OF 11	

**MX150 2X2 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET**




ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (OPEN)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4												
KEY A, BLACK	33482-4001	A-BLK	GCO	PLR	M														SALEABLE		
KEY B, LIGHT GRAY	33482-4002	B-LG	GCO	PLR	M														SALEABLE		
KEY C, BROWN	33482-4003	C-BR	GCO	PLR	M														NOT RECOMMENDED	SEE 33482-4103	
KEY D, GREEN	33482-4004	D-GR	GCO	PLR	M														NOT RECOMMENDED	SEE 33482-4104	
KEY A, BLACK	33482-4006	A-BLK	GCP	PLR	M		2												SALEABLE		
KEY B, LIGHT GRAY	33482-4007	B-LG	GCP	PLR	M		2												SALEABLE		
KEY C, BROWN	33482-4008	C-BR	GCP	PLR	M		2												NOT RECOMMENDED	SEE 33482-4105	
KEY D, GREEN	33482-4009	D-GR	GCP	PLR	M		2												NOT RECOMMENDED	SEE 33482-4106	
KEY A, BLACK	33482-4011	A-BLK	GCP	PLR	M		2	3											SALEABLE		
KEY B, LIGHT GRAY	33482-4012	B-LG	GCP	PLR	M		2	3											SALEABLE		
KEY C, BROWN	33482-4013	C-BR	GCP	PLR	M		2	3											NOT RECOMMENDED	SEE 33482-4107	
KEY D, GREEN	33482-4014	D-GR	GCP	PLR	M		2	3											NOT RECOMMENDED	SEE 33482-4108	
KEY A, BLACK	33482-4016	A-BLK	GCP	PLR	M	1	2	3	4										SALEABLE		
KEY B, LIGHT GRAY	33482-4017	B-LG	GCP	PLR	M	1	2	3	4										SALEABLE		
KEY C, BROWN	33482-4018	C-BR	GCP	PLR	M	1	2	3	4										NOT RECOMMENDED	SEE 33482-4109	
KEY D, GREEN	33482-4019	D-GR	GCP	PLR	M	1	2	3	4										NOT RECOMMENDED	SEE 33482-4110	
KEY A, BLACK	33482-4021	A-BLK	GCP	PLR	M	1	2	3											SALEABLE		
KEY A, BLACK	33482-4022	A-BLK	GCP	PLR	M				4										SALEABLE		
KEY A, BLACK	33482-4023	A-BLK	GCP	PLR	M			3	4										SALEABLE		
KEY A, BLACK	33482-4024	A-BLK	GCP	PLR	M			3											SALEABLE		
KEY A, BLACK	33482-4025	A-BLK	GCP	PLR	M	1	2												SALEABLE		
KEY C, DARK GRAY	33482-4103	C-DG	GCO	PLR	M														SALEABLE		
KEY D, STONE GRAY	33482-4104	D-SG	GCO	PLR	M														SALEABLE		
KEY C, DARK GRAY	33482-4105	C-DG	GCP	PLR	M		2												SALEABLE		
KEY D, STONE GRAY	33482-4106	D-SG	GCP	PLR	M		2												SALEABLE		
KEY C, DARK GRAY	33482-4107	C-DG	GCP	PLR	M		2	3											SALEABLE		
KEY D, STONE GRAY	33482-4108	D-SG	GCP	PLR	M		2	3											SALEABLE		
KEY C, DARK GRAY	33482-4109	C-DG	GCP	PLR	M	1	2	3	4										SALEABLE		
KEY D, STONE GRAY	33482-4110	D-SG	GCP	PLR	M	1	2	3	4										SALEABLE		
KEY A, BLACK	33482-4111	A-BLK	GCP	PLR	M		2		4										SALEABLE		
KEY A, YELLOW	33482-4112	A-YW	GCO	PLR	M														SALEABLE		
KEY B, LIGHT GRAY	33482-4113	B-LG	GCP	PLR	M	1													SALEABLE		
KEY A, BLACK	33482-4115	A-BLK	GCP	PLR	M	1		3											SALEABLE		
KEY C, DARK GRAY	33482-4116	C-DG	GCP	PLR	M		2		4										SALEABLE		
KEY B, LIGHT GRAY	33482-4117	B-LG	GCP	PLR	M		2		4										SALEABLE		
KEY B, LIGHT GRAY	33482-4118	B-LG	GCP	PLR	M				4										SALEABLE		
KEY A, BLACK	33482-4119	A-BLK	GCP	PLR	M	1			4										SALEABLE		

**MX150 2X3 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET**



ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GC	GROMMET CAP (STANDARD)	BLACK	SPS/NYLON GF20
GCL	GROMMET CAP (LENGTHENED)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001


ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS											STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION													BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS		
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6											
KEY A, BLACK	33482-3601	A-BLK	GC	PLR	M														SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3602	B-LG	GC	PLR	M														SALEABLE		34950-0610	34950-0620
KEY C, BROWN	33482-3603	C-BR	GC	PLR	M														NOT RECOMMENDED	SEE 33482-3628	34950-0610	34950-0620
KEY D, GREEN	33482-3604	D-GR	GC	PLR	M														NOT RECOMMENDED	SEE 33482-3629	34950-0610	34950-0620
VOID KEY	33482-3605																					
KEY A, BLACK	33482-3606	A-BLK	GC	PLR	M			3											SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3607	B-LG	GC	PLR	M			3											SALEABLE		34950-0610	34950-0620
KEY C, BROWN	33482-3608	C-BR	GC	PLR	M			3											NOT RECOMMENDED	SEE 33482-3638	34950-0610	34950-0620
KEY D, GREEN	33482-3609	D-GR	GC	PLR	M			3											NOT RECOMMENDED	SEE 33482-3641	34950-0610	34950-0620
VOID KEY	33482-3610																					
KEY A, BLACK	33482-3611	A-BLK	GC	PLR	M			3	4										SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3612	B-LG	GC	PLR	M			3	4										SALEABLE		34950-0610	34950-0620
KEY C, BROWN	33482-3613	C-BR	GC	PLR	M			3	4										NOT RECOMMENDED	SEE 33482-3642	34950-0610	34950-0620
KEY D, GREEN	33482-3614	D-GR	GC	PLR	M			3	4										NOT RECOMMENDED	SEE 33482-3643	34950-0610	34950-0620
VOID KEY	33482-3615																					
KEY A, BLACK	33482-3616	A-BLK	GC	PLR	M			3											SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3617	A-BLK	GC	PLR	M		2												SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3618	A-BLK	GC	PLR	M							5	6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3619	A-BLK	GC	PLR	M			2	3	4	5								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3620	A-BLK	GC	PLR	M		1	2	3	4	5	6							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3621	A-BLK	GC	PLR	M		1			4	5								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3622	A-BLK	GC	PLR	M					4	5	6							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3623	A-BLK	GC	PLR	M						5								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3624	A-BLK	GC	PLR	M								6						SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3625	B-LG	GC	PLR	M		1					5							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3626	A-BLK	GC	PLR	M		1	2	3	4									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3627	A-BLK	GC	PLR	M			2	3			5	6						SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3628	C-DG	GC	PLR	M														SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3629	D-SG	GC	PLR	M														SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3630	A-BLK	GC	PLR	M				3					6					SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3631	A-BLK	GCL	PLR	M														SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3632	B-LG	GCL	PLR	M														SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3633	C-DG	GCL	PLR	M														SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3634	D-SG	GCL	PLR	M														SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3635	C-DG	GCL	PLR	M				3										SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3636	A-BLK	GCL	PLR	M					3									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3637	A-BLK	GC	PLR	M			2						6					SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3638	C-DG	GC	PLR	M					3									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3639	A-BLK	GCL	PLR	M		1	2	3	4	5	6							SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3640	A-BLK	GC	PLR	M														SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3641	D-SG	GC	PLR	M					3									SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3642	C-DG	GC	PLR	M					3	4								SALEABLE		34950-0610	34950-0620
KEY D, STONE GRAY	33482-3643	D-SG	GC	PLR	M					3	4								SALEABLE		34950-0610	34950-0620
KEY A, YELLOW	33482-3644	A-YW	GC	PLR	M														SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3645	A-BLK	GC	PLR	M					3	4	5	6						SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3646	A-BLK	GC	PLR	M			2	3										SALEABLE		34950-0610	34950-0620

**MX150 2X3 BLADE SEALED ASSEMBLY MAT SEAL
BOM AND PIN OUT SHEET**

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS										STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY				
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION												BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS			
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6											
KEY B, LIGHT GRAY	33482-3647	B-LG	GC	PLR	M		2	3											SALEABLE		34950-0610	34950-0620
KEY C, DARK GRAY	33482-3648	C-DG	GC	PLR	M						6								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3649	A-BLK	GC	PLR	M				4		6								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3650	A-BLK	GC	PLR	M	1		3		5									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3651	A-BLK	GC	PLR	M		2		4		6								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3652	A-BLK	GC	PLR	M	1					6								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3653	A-BLK	GC	PLR	M		2			5									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3654	A-BLK	GC	PLR	M	1		3	4										SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3655	A-BLK	GC	PLR	M	1	2	3		5	6								SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3656	A-BLK	GC	PLR	M	1	2	3											SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3657	A-BLK	GC	PLR	M				4	5									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3658	A-BLK	GC	PLR	M	1													SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3659	B-LG	GC	PLR	M	1													SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3660	B-LG	GC	PLR	M					5									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3661	A-BLK	GC	PLR	M	1				5									SALEABLE		34950-0610	34950-0620
KEY A, BLACK	33482-3662	A-BLK	GC	PLR	M			3	4		6								SALEABLE		34950-0610	34950-0620
KEY B, LIGHT GRAY	33482-3663	B-LG	GC	PLR	M					5	6								SALEABLE		34950-0610	34950-0620

MX150 2X4 BLADE SEALED ASSEMBLY MAT SEAL

BOM AND PIN OUT SHEET




ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (OPEN)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS								STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY					
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.						CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION								BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS		
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8								
KEY A, BLACK	33482-0801	A-BLK	GCO	PLR	M-R											PLANNED OBSOLESCENCE	SEE 33482-4801	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0802	B-LG	GCO	PLR	M-R											PLANNED OBSOLESCENCE	SEE 33482-4802	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, BROWN	33482-0803	C-BR	GCO	PLR	M-R											PLANNED OBSOLESCENCE	SEE 33482-4803	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, GREEN	33482-0804	D-GR	GCO	PLR	M-R											PLANNED OBSOLESCENCE	SEE 33482-4804	34950-0811	34950-0821	34951-0831	34951-0841
VOID KEY	33482-0805																				
KEY A, BLACK	33482-0806	A-BLK	GCP	PLR	M-R				4							PLANNED OBSOLESCENCE	SEE 33482-4806	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0807	B-LG	GCP	PLR	M-R				4							PLANNED OBSOLESCENCE	SEE 33482-4807	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, BROWN	33482-0808	C-BR	GCP	PLR	M-R				4							PLANNED OBSOLESCENCE	SEE 33482-4808	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, GREEN	33482-0809	D-GR	GCP	PLR	M-R				4							PLANNED OBSOLESCENCE	SEE 33482-4809	34950-0811	34950-0821	34951-0831	34951-0841
VOID KEY	33482-0810																				
KEY A, BLACK	33482-0811	A-BLK	GCP	PLR	M-R				4	5						PLANNED OBSOLESCENCE	SEE 33482-4811	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0812	B-LG	GCP	PLR	M-R				4	5						PLANNED OBSOLESCENCE	SEE 33482-4812	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, BROWN	33482-0813	C-BR	GCP	PLR	M-R				4	5						PLANNED OBSOLESCENCE	SEE 33482-4813	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, GREEN	33482-0814	D-GR	GCP	PLR	M-R				4	5						PLANNED OBSOLESCENCE	SEE 33482-4814	34950-0811	34950-0821	34951-0831	34951-0841
VOID KEY	33482-0815																				
KEY A, BLACK	33482-0816	A-BLK	GCP	PLR	M-R	1			4	5						PLANNED OBSOLESCENCE	SEE 33482-4816	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0817	B-LG	GCP	PLR	M-R	1			4	5						PLANNED OBSOLESCENCE	SEE 33482-4817	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, BROWN	33482-0818	C-BR	GCP	PLR	M-R	1			4	5						PLANNED OBSOLESCENCE	SEE 33482-4818	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, GREEN	33482-0819	D-GR	GCP	PLR	M-R	1			4	5						PLANNED OBSOLESCENCE	SEE 33482-4819	34950-0811	34950-0821	34951-0831	34951-0841
VOID KEY	33482-0820																				
KEY A, BLACK	33482-0821	A-BLK	GCP	PLR	M-R	1			4	5			8			PLANNED OBSOLESCENCE	SEE 33482-4821	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0822	B-LG	GCP	PLR	M-R	1			4	5			8			PLANNED OBSOLESCENCE	SEE 33482-4822	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, BROWN	33482-0823	C-BR	GCP	PLR	M-R	1			4	5			8			PLANNED OBSOLESCENCE	SEE 33482-4823	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, GREEN	33482-0824	D-GR	GCP	PLR	M-R	1			4	5			8			PLANNED OBSOLESCENCE	SEE 33482-4824	34950-0811	34950-0821	34951-0831	34951-0841
VOID KEY	33482-0825																				
KEY A, BLACK	33482-0826	A-BLK	GCP	PLR	M-R	1	2	3			6	7	8			PLANNED OBSOLESCENCE	SEE 33482-4826	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0827	A-BLK	GCP	PLR	M-R								8			PLANNED OBSOLESCENCE	SEE 33482-4827	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0828	A-BLK	GCP	PLR	M-R			3		5						PLANNED OBSOLESCENCE	SEE 33482-4828	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0829	A-BLK	GCP	PLR	M-R		2	3	4	5	6	7				PLANNED OBSOLESCENCE	SEE 33482-4829	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0830	A-BLK	GCP	PLR	M-R						6					PLANNED OBSOLESCENCE	SEE 33482-4830	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0831	A-BLK	GCP	PLR	M-R			3		5	6					PLANNED OBSOLESCENCE	SEE 33482-4831	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0832	A-BLK	GCP	PLR	M-R					5	6		8			PLANNED OBSOLESCENCE	SEE 33482-4832	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0833	A-BLK	GCP	PLR	M-R	1			3	5						PLANNED OBSOLESCENCE	SEE 33482-4833	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0834	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8			PLANNED OBSOLESCENCE	SEE 33482-4834	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0835	A-BLK	GCP	PLR	M-R							7	8			PLANNED OBSOLESCENCE	SEE 33482-4835	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0836	A-BLK	GCP	PLR	M-R			2	3		6	7	8			PLANNED OBSOLESCENCE	SEE 33482-4836	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0837	A-BLK	GCP	PLR	M-R	1			4							PLANNED OBSOLESCENCE	SEE 33482-4837	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0838	A-BLK	GCP	PLR	M-R		2	3		5	6	7	8			PLANNED OBSOLESCENCE	SEE 33482-4838	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0839	B-LG	GCP	PLR	M-R								8			PLANNED OBSOLESCENCE	SEE 33482-4839	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0840	A-BLK	GCP	PLR	M-R		2	3		5	6		8			PLANNED OBSOLESCENCE	SEE 33482-4840	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0841	A-BLK	GCP	PLR	M-R						6	7				PLANNED OBSOLESCENCE	SEE 33482-4841	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0842	A-BLK	GCP	PLR	M-R							7				PLANNED OBSOLESCENCE	SEE 33482-4842	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0843	A-BLK	GCP	PLR	M-R				4			7				PLANNED OBSOLESCENCE	SEE 33482-4843	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0844	A-BLK	GCP	PLR	M-R				3		6					PLANNED OBSOLESCENCE	SEE 33482-4844	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0845	A-BLK	GCP	PLR	M-R		2	3	4	5	6					PLANNED OBSOLESCENCE	SEE 33482-4845	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0846	A-BLK	GCP	PLR	M-R				4	5		7	8			PLANNED OBSOLESCENCE	SEE 33482-4846	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0847	B-LG	GCP	PLR	M-R	1	2	3	4	5	6	7	8			PLANNED OBSOLESCENCE	SEE 33482-4847	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-0848	A-BLK	GCP	PLR	M-R	1				5						PLANNED OBSOLESCENCE	SEE 33482-4848	34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-0849	B-LG	GCP	PLR	M-R	1					6					PLANNED OBSOLESCENCE	SEE 33482-4849	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, YELLOW	33482-0850	A-YW	GCP	PLR	M-R	1			4							PLANNED OBSOLESCENCE	SEE 33482-4850	34950-0811	34950-0821	34951-0831	34951-0841
KEY A, YELLOW	33482-0851	A-YW	GCO	PLR	M-R											PLANNED OBSOLESCENCE	SEE 33482-4851	34950-0811	34950-0821	34951-0831	34951-0841
KEY C, DARK GRAY	33482-0852	C-DG	GCO	PLR	M-R											PLANNED OBSOLESCENCE	SEE 33482-4852	34950-0811	34950-0821	34951-0831	34951-0841
KEY D, STONE GRAY	33482-0853	D-SG	GCO	PLR	M-R											PLANNED OBSOLESCENCE	SEE 33482-4853	34950-0811	34950-0821	34951-0831	34951-0841

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS										STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION												BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8								
KEY A, BLACK	33482-4836	A-BLK	GCP	PLR	M-B		2	3		6	7	8				SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4837	A-BLK	GCP	PLR	M-B	1			4							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4838	A-BLK	GCP	PLR	M-B		2	3		5	6	7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4839	B-LG	GCP	PLR	M-B								8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4840	A-BLK	GCP	PLR	M-B		2	3		5	6		8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4841	A-BLK	GCP	PLR	M-B					6	7					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4842	A-BLK	GCP	PLR	M-B							7				SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4843	A-BLK	GCP	PLR	M-B				4							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4844	A-BLK	GCP	PLR	M-B				3			6				SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4845	A-BLK	GCP	PLR	M-B		2	3	4	5	6					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4846	A-BLK	GCP	PLR	M-B				4	5		7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4847	B-LG	GCP	PLR	M-B	1	2	3	4	5	6	7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4848	A-BLK	GCP	PLR	M-B	1				5						SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4849	B-LG	GCP	PLR	M-B	1					6					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, YELLOW	33482-4850	A-YW	GCP	PLR	M-B	1			4							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, YELLOW	33482-4851	A-YW	GCO	PLR	M-B											SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY C, DARK GRAY	33482-4852	C-DG	GCO	PLR	M-B											SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY D, STONE GRAY	33482-4853	D-SG	GCO	PLR	M-B											SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4854	A-BLK	GCP	PLR	M-B	1	2	3	4							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4855	A-BLK	GCP	PLR	M-B	1	2			5	6	7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4856	A-BLK	GCP	PLR	M-B	1	2									SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4857	A-BLK	GCP	PLR	M-B	1	2	3		5						SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4858	A-BLK	GCP	PLR	M-B	1	2	3	4	5			8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4859	A-BLK	GCP	PLR	M-B	1			3	5	6	7				SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4860	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4861	A-BLK	GCP	PLR	M-B	1	2	3			6					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4862	A-BLK	GCP	PLR	M-B	1					6					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4863	A-BLK	GCP	PLR	M-B	1					6	7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4864	A-BLK	GCP	PLR	M-B				3	4	5	6	7	8		SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4865	A-BLK	GCP	PLR	M-B				4			7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4866	A-BLK	GCP	PLR	M-B				4	5	6	7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4867	A-BLK	GCP	PLR	M-B		2	3	4		6	7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4868	A-BLK	GCP	PLR	M-B					5	6	7				SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4869	A-BLK	GCP	PLR	M-B				3	4						SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4870	A-BLK	GCP	PLR	M-B						6	7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4871	B-LG	GCP	PLR	M-B							7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4872	A-BLK	GCP	PLR	M-B	1							8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4873	A-BLK	GCP	PLR	M-B						6		8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4874	A-BLK	GCP	PLR	M-B					5						SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4875	A-BLK	GCP	PLR	M-B		2			5						SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4876	B-LG	GCP	PLR	M-B	1			3				8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4877	B-LG	GCP	PLR	M-B				3				8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY B, LIGHT GRAY	33482-4878	B-LG	GCP	PLR	M-B	1										SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4879	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7				SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4880	A-BLK	GCP	PLR	M-B	1										SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4881	A-BLK	GCP	PLR	M-B					5			8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4882	A-BLK	GCP	PLR	M-B				4		6					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4883	A-BLK	GCP	PLR	M-B	1							7			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4884	A-BLK	GCP	PLR	M-B	1	2	3	4			7				SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4885	A-BLK	GCP	PLR	M-B	1	2			5	6		8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4886	A-BLK	GCP	PLR	M-B		2	3					8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4887	A-BLK	GCP	PLR	M-B	1			3	4		7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4888	A-BLK	GCP	PLR	M-B				4	5	6					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4889	A-BLK	GCP	PLR	M-B	1	2		4	5	6		8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4890	A-BLK	GCP	PLR	M-B				4	5			8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4891	A-BLK	GCP	PLR	M-B											SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4892	A-BLK	GCP	PLR	M-B		2	3		5			8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4893	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4894	A-BLK	GCP	PLR	M-B				3	4	5					SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4895	A-BLK	GCP	PLR	M-B				3				7			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4896	A-BLK	GCP	PLR	M-B	1	2		4	5		7				SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4897	A-BLK	GCP	PLR	M-B				4	5			7			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4898	A-BLK	GCP	PLR	M-B			2								SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4899	A-BLK	GCP	PLR	M-B	1			3	4	5	6	7	8		SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4900	A-BLK	GCP	PLR	M-B					5	6	7	8			SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841
KEY A, BLACK	33482-4901	A-BLK	GCP	PLR	M-B				3							SALEABLE		34950-0811	34950-0821	34951-0831	34951-0841

MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET



ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
A-YL	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	ROYAL BLUE	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY		
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12					
KEY A, BLACK	33482-1201	A-BLK	GCP	PLR	M-R														PLANNED OBSOLESCENCE	SEE 33482-6201	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1202	B-LG	GCP	PLR	M-R														PLANNED OBSOLESCENCE	SEE 33482-6202	34950-1210	34950-1220
KEY C, BROWN	33482-1203	C-BR	GCP	PLR	M-R														PLANNED OBSOLESCENCE	SEE 33482-6203	34950-1210	34950-1220
KEY D, GREEN	33482-1204	D-GR	GCP	PLR	M-R														PLANNED OBSOLESCENCE	SEE 33482-6204	34950-1210	34950-1220
VOID KEY	33482-1205																					
KEY A, BLACK	33482-1206	A-BLK	GCP	PLR	M-R						6								PLANNED OBSOLESCENCE	SEE 33482-6206	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1207	B-LG	GCP	PLR	M-R						6								PLANNED OBSOLESCENCE	SEE 33482-6207	34950-1210	34950-1220
KEY C, BROWN	33482-1208	C-BR	GCP	PLR	M-R						6								PLANNED OBSOLESCENCE	SEE 33482-6208	34950-1210	34950-1220
KEY D, GREEN	33482-1209	D-GR	GCP	PLR	M-R						6								PLANNED OBSOLESCENCE	SEE 33482-6209	34950-1210	34950-1220
VOID KEY	33482-1210																					
KEY A, BLACK	33482-1211	A-BLK	GCP	PLR	M-R						6	7							PLANNED OBSOLESCENCE	SEE 33482-6211	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1212	B-LG	GCP	PLR	M-R						6	7							PLANNED OBSOLESCENCE	SEE 33482-6212	34950-1210	34950-1220
KEY C, BROWN	33482-1213	C-BR	GCP	PLR	M-R						6	7							PLANNED OBSOLESCENCE	SEE 33482-6213	34950-1210	34950-1220
KEY D, GREEN	33482-1214	D-GR	GCP	PLR	M-R						6	7							PLANNED OBSOLESCENCE	SEE 33482-6214	34950-1210	34950-1220
VOID KEY	33482-1215																					
KEY A, BLACK	33482-1216	A-BLK	GCP	PLR	M-R	1					6	7							PLANNED OBSOLESCENCE	SEE 33482-6216	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1217	B-LG	GCP	PLR	M-R	1					6	7							PLANNED OBSOLESCENCE	SEE 33482-6217	34950-1210	34950-1220
KEY C, BROWN	33482-1218	C-BR	GCP	PLR	M-R	1					6	7							PLANNED OBSOLESCENCE	SEE 33482-6218	34950-1210	34950-1220
KEY D, GREEN	33482-1219	D-GR	GCP	PLR	M-R	1					6	7							PLANNED OBSOLESCENCE	SEE 33482-6219	34950-1210	34950-1220
VOID KEY	33482-1220																					
KEY A, BLACK	33482-1221	A-BLK	GCP	PLR	M-R	1					6	7					12		PLANNED OBSOLESCENCE	SEE 33482-6221	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1222	B-LG	GCP	PLR	M-R	1					6	7					12		PLANNED OBSOLESCENCE	SEE 33482-6222	34950-1210	34950-1220
KEY C, BROWN	33482-1223	C-BR	GCP	PLR	M-R	1					6	7					12		PLANNED OBSOLESCENCE	SEE 33482-6223	34950-1210	34950-1220
KEY D, GREEN	33482-1224	D-GR	GCP	PLR	M-R	1					6	7					12		PLANNED OBSOLESCENCE	SEE 33482-6224	34950-1210	34950-1220
VOID KEY	33482-1225																					
KEY A, BLACK	33482-1226	A-BLK	GCP	PLR	M-R						6						12		PLANNED OBSOLESCENCE	SEE 33482-6226	34950-1210	34950-1220
KEY A, BLACK	33482-1227	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12		PLANNED OBSOLESCENCE	SEE 33482-6227	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1228	B-LG	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12		PLANNED OBSOLESCENCE	SEE 33482-6228	34950-1210	34950-1220
KEY C, BROWN	33482-1229	C-BR	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12		PLANNED OBSOLESCENCE	SEE 33482-6229	34950-1210	34950-1220
KEY D, GREEN	33482-1230	D-GR	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12		PLANNED OBSOLESCENCE	SEE 33482-6230	34950-1210	34950-1220
VOID KEY	33482-1231																					
KEY A, BLACK	33482-1232	A-BLK	GCP	PLR	M-R		2	3					8				11		PLANNED OBSOLESCENCE	SEE 33482-6232	34950-1210	34950-1220
KEY A, BLACK	33482-1233	A-BLK	GCP	PLR	M-R		2	3					8				11		PLANNED OBSOLESCENCE	SEE 33482-6233	34950-1210	34950-1220
KEY A, BLACK	33482-1234	A-BLK	GCP	PLR	M-R						6	7							PLANNED OBSOLESCENCE	SEE 33482-6234	34950-1210	34950-1220
KEY A, BLACK	33482-1235	A-BLK	GCP	PLR	M-R		2	3			6	7	8			10	11		PLANNED OBSOLESCENCE	SEE 33482-6235	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1236	B-LG	GCP	PLR	M-R	1					5	6	7	8	9	10			PLANNED OBSOLESCENCE	SEE 33482-6236	34950-1210	34950-1220
KEY A, BLACK	33482-1237	A-BLK	GCP	PLR	M-R			2											PLANNED OBSOLESCENCE	SEE 33482-6237	34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1238	B-LG	GCP	PLR	M-R		2								9	10			PLANNED OBSOLESCENCE	SEE 33482-6238	34950-1210	34950-1220
KEY A, BLACK	33482-1239	A-BLK	GCP	PLR	M-R	1													PLANNED OBSOLESCENCE	SEE 33482-6239	34950-1210	34950-1220
KEY A, BLACK	33482-1240	A-BLK	GCP	PLR	M-R			3					8	9	10		11		PLANNED OBSOLESCENCE	SEE 33482-6240	34950-1210	34950-1220
KEY A, BLACK	33482-1241	A-BLK	GCP	PLR	M-R							7	8	9	10	11			PLANNED OBSOLESCENCE	SEE 33482-6241	34950-1210	34950-1220
KEY A, BLACK	33482-1242	A-BLK	GCP	PLR	M-R							7	8						PLANNED OBSOLESCENCE	SEE 33482-6242	34950-1210	34950-1220
KEY A, BLACK	33482-1243	A-BLK	GCP	PLR	M-R		2							9	10				PLANNED OBSOLESCENCE	SEE 33482-6243	34950-1210	34950-1220
KEY A, BLACK	33482-1244	A-BLK	GCP	PLR	M-R		2			4									PLANNED OBSOLESCENCE	SEE 33482-6244	34950-1210	34950-1220
KEY A, BLACK	33482-1245	A-BLK	GCP	PLR	M-R									9	10		11	12	PLANNED OBSOLESCENCE	SEE 33482-6245	34950-1210	34950-1220
KEY A, BLACK	33482-1246	A-BLK	GCP	PLR	M-R												11		PLANNED OBSOLESCENCE	SEE 33482-6246	34950-1210	34950-1220
KEY A, BLACK	33482-1247	A-BLK	GCP	PLR	M-R		2	3	4			7	8						PLANNED OBSOLESCENCE	SEE 33482-6247	34950-1210	34950-1220
KEY A, BLACK	33482-1248	A-BLK	GCP	PLR	M-R	1		3	4	5	6	7	8						PLANNED OBSOLESCENCE	SEE 33482-6248	34950-1210	34950-1220
KEY A, BLACK	33482-1249	A-BLK	GCP	PLR	M-R										10	11	12		PLANNED OBSOLESCENCE	SEE 33482-6249	34950-1210	34950-1220

**MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET**

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY		
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12					
KEY A, BLACK	33482-1250	A-BLK	GCP	PLR	M-R				4	5	6	7	8	9			PLANNED OBSOLESCENCE	SEE 33482-6250	34950-1210	34950-1220		
KEY A, BLACK	33482-1251	A-BLK	GCP	PLR	M-R		2		4	5			8		10	11	PLANNED OBSOLESCENCE	SEE 33482-6251	34950-1210	34950-1220		
KEY A, BLACK	33482-1252	A-BLK	GCP	PLR	M-R							7					PLANNED OBSOLESCENCE	SEE 33482-6252	34950-1210	34950-1220		
KEY A, BLACK	33482-1253	A-BLK	GCP	PLR	M-R		2	3	4	5	6	7	8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6253	34950-1210	34950-1220	
KEY A, BLACK	33482-1254	A-BLK	GCP	PLR	M-R		2	3	4	5					10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6254	34950-1210	34950-1220	
KEY A, BLACK	33482-1255	A-BLK	GCP	PLR	M-R		2	3	4	5	6	7			10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6255	34950-1210	34950-1220	
KEY A, BLACK	33482-1256	A-BLK	GCP	PLR	M-R	1					6	7		9			PLANNED OBSOLESCENCE	SEE 33482-6256	34950-1210	34950-1220		
KEY A, BLACK	33482-1257	A-BLK	GCP	PLR	M-R								9	10		12	PLANNED OBSOLESCENCE	SEE 33482-6257	34950-1210	34950-1220		
KEY A, BLACK	33482-1258	A-BLK	GCP	PLR	M-R		2	3							11		PLANNED OBSOLESCENCE	SEE 33482-6258	34950-1210	34950-1220		
KEY A, BLACK	33482-1259	A-BLK	GCP	PLR	M-R	1	2	3	4	5			9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6259	34950-1210	34950-1220		
KEY A, BLACK	33482-1260	A-BLK	GCP	PLR	M-R										11	12	PLANNED OBSOLESCENCE	SEE 33482-6260	34950-1210	34950-1220		
KEY C, DARK GRAY	33482-1261	C-DG	GCP	PLR	M-R												PLANNED OBSOLESCENCE	SEE 33482-6261	34950-1210	34950-1220		
KEY D, STONE GRAY	33482-1262	D-SG	GCP	PLR	M-R												PLANNED OBSOLESCENCE	SEE 33482-6262	34950-1210	34950-1220		
KEY C, DARK GRAY	33482-1263	C-DG	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6263	34950-1210	34950-1220	
KEY D, STONE GRAY	33482-1264	D-SG	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6264	34950-1210	34950-1220	
KEY A, BLACK	33482-1265	A-BLK	GCP	PLR	M-R						6	7	8	9	10	11	PLANNED OBSOLESCENCE	SEE 33482-6265	34950-1210	34950-1220		
KEY A, BLACK	33482-1266	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7				12	PLANNED OBSOLESCENCE	SEE 33482-6266	34950-1210	34950-1220		
KEY A, BLACK	33482-1267	A-BLK	GCP	PLR	M-R			3	4	5	6	7					PLANNED OBSOLESCENCE	SEE 33482-6267	34950-1210	34950-1220		
KEY A, BLACK	33482-1268	A-BLK	GCP	PLR	M-R			3	4	5	6	7	8	9	10	11	PLANNED OBSOLESCENCE	SEE 33482-6268	34950-1210	34950-1220		
KEY A, BLACK	33482-1269	A-BLK	GCP	PLR	M-R	1	2	3	4	5			8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6269	34950-1210	34950-1220	
KEY A, BLACK	33482-1270	A-BLK	GCP	PLR	M-R		2		4			7	8	9	10		PLANNED OBSOLESCENCE	SEE 33482-6270	34950-1210	34950-1220		
KEY A, BLACK	33482-1271	A-BLK	GCP	PLR	M-R		2					7	8	9			PLANNED OBSOLESCENCE	SEE 33482-6271	34950-1210	34950-1220		
KEY A, BLACK	33482-1272	A-BLK	GCP	PLR	M-R		2					7	8	9	10		PLANNED OBSOLESCENCE	SEE 33482-6272	34950-1210	34950-1220		
KEY A, BLACK	33482-1273	A-BLK	GCP	PLR	M-R								8				PLANNED OBSOLESCENCE	SEE 33482-6273	34950-1210	34950-1220		
KEY A, BLACK	33482-1274	A-BLK	GCP	PLR	M-R	1		3	4	5	6		8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6274	34950-1210	34950-1220	
KEY A, BLACK	33482-1275	A-BLK	GCP	PLR	M-R				4				8		10		PLANNED OBSOLESCENCE	SEE 33482-6275	34950-1210	34950-1220		
KEY A, BLACK	33482-1276	A-BLK	GCP	PLR	M-R	1	2	3	4		6				10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6276	34950-1210	34950-1220	
KEY A, BLACK	33482-1277	A-BLK	GCP	PLR	M-R	1	2	3								11	12	PLANNED OBSOLESCENCE	SEE 33482-6277	34950-1210	34950-1220	
KEY A, BLACK	33482-1278	A-BLK	GCP	PLR	M-R						6					12	PLANNED OBSOLESCENCE	SEE 33482-6278	34950-1210	34950-1220		
KEY A, BLACK	33482-1279	A-BLK	GCP	PLR	M-R	1	2	3	4	5		7	8		9	10	11	PLANNED OBSOLESCENCE	SEE 33482-6279	34950-1210	34950-1220	
KEY A, BLACK	33482-1280	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6			9			PLANNED OBSOLESCENCE	SEE 33482-6280	34950-1210	34950-1220		
KEY A, BLACK	33482-1281	A-BLK	GCP	PLR	M-R		2		4				8		10	11	PLANNED OBSOLESCENCE	SEE 33482-6281	34950-1210	34950-1220		
KEY A, BLACK	33482-1282	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6			9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6282	34950-1210	34950-1220	
KEY A, BLACK	33482-1283	A-BLK	GCP	PLR	M-R						6				9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6283	34950-1210	34950-1220
KEY A, BLACK	33482-1284	A-BLK	GCP	PLR	M-R	1		3	4	5	6	7	8		10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6284	34950-1210	34950-1220	
KEY D, STONE GRAY	33482-1285	D-SG	GCP	PLR	M-R	1					6	7					PLANNED OBSOLESCENCE	SEE 33482-6285	34950-1210	34950-1220		
KEY A, BLACK	33482-1286	A-BLK	GCP	PLR	M-R		2	3					8	9			PLANNED OBSOLESCENCE	SEE 33482-6286	34950-1210	34950-1220		
KEY A, BLACK	33482-1287	A-BLK	GCP	PLR	M-R	1						7					PLANNED OBSOLESCENCE	SEE 33482-6287	34950-1210	34950-1220		
KEY A, BLACK	33482-1288	A-BLK	GCP	PLR	M-R	1					6						PLANNED OBSOLESCENCE	SEE 33482-6288	34950-1210	34950-1220		
KEY A, BLACK	33482-1289	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6		8				PLANNED OBSOLESCENCE	SEE 33482-6289	34950-1210	34950-1220		
KEY A, BLACK	33482-1290	A-BLK	GCP	PLR	M-R	1						7				12	PLANNED OBSOLESCENCE	SEE 33482-6290	34950-1210	34950-1220		
KEY A, BLACK	33482-1291	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8			12	PLANNED OBSOLESCENCE	SEE 33482-6291	34950-1210	34950-1220		
KEY A, BLACK	33482-1292	A-BLK	GCP	PLR	M-R									9			PLANNED OBSOLESCENCE	SEE 33482-6292	34950-1210	34950-1220		
KEY A, BLACK	33482-1293	A-BLK	GCP	PLR	M-R			3	4					9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6293	34950-1210	34950-1220	
KEY A, BLACK	33482-1294	A-BLK	GCP	PLR	M-R	1	2			5	6	7	8				PLANNED OBSOLESCENCE	SEE 33482-6294	34950-1210	34950-1220		
KEY A, BLACK	33482-1295	A-BLK	GCP	PLR	M-R	1	2			5	6	7	8		11	12	PLANNED OBSOLESCENCE	SEE 33482-6295	34950-1210	34950-1220		
KEY A, BLACK	33482-1296	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8		10		PLANNED OBSOLESCENCE	SEE 33482-6296	34950-1210	34950-1220		
KEY A, BLACK	33482-1297	A-BLK	GCP	PLR	M-R				4						10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6297	34950-1210	34950-1220	
KEY A, BLACK	33482-1298	A-BLK	GCP	PLR	M-R						6					11	12	PLANNED OBSOLESCENCE	SEE 33482-6298	34950-1210	34950-1220	
KEY A, BLACK	33482-1299	A-BLK	GCP	PLR	M-R	1	2					7	8				PLANNED OBSOLESCENCE	SEE 33482-6299	34950-1210	34950-1220		
KEY A, BLACK	33482-1300	A-BLK	GCP	PLR	M-R	1	2	3							10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6300	34950-1210	34950-1220	
KEY A, BLACK	33482-1301	A-BLK	GCP	PLR	M-R	1	2					7	8				PLANNED OBSOLESCENCE	SEE 33482-6301	34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-1302	B-LG	GCP	PLR	M-R										10	11	PLANNED OBSOLESCENCE	SEE 33482-6302	34950-1210	34950-1220		
KEY A, BLACK	33482-1303	A-BLK	GCP	PLR	M-R	1	2	3	4			7	8	9	10	12	PLANNED OBSOLESCENCE	SEE 33482-6303	34950-1210	34950-1220		
KEY A, BLACK	33482-1304	A-BLK	GCP	PLR	M-R	1	2	3	4			7	8	9	10		PLANNED OBSOLESCENCE	SEE 33482-6304	34950-1210	34950-1220		
KEY B, LIGHT GRAY	33482-1305	B-LG	GCP	PLR	M-R										10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6305	34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-1306	B-LG	GCP	PLR	M-R	1	2	3	4	5	6	7			10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6306	34950-1210	34950-1220	
KEY A, BLACK	33482-1307	A-BLK	GCP	PLR	M-R	1	2	3	4	5		7	8				PLANNED OBSOLESCENCE	SEE 33482-6307	34950-1210	34950-1220		
KEY A, BLACK	33482-1308	A-BLK	GCP	PLR	M-R							7	8	9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6308	34950-1210	34950-1220	
KEY A, BLACK	33482-1309	A-BLK	GCP	PLR	M-R	1							8		10	11	PLANNED OBSOLESCENCE	SEE 33482-6309	34950-1210	34950-1220		
KEY A, BLACK	33482-1310	A-BLK	GCP	PLR	M-R	1			4							11	PLANNED OBSOLESCENCE	SEE 33482-6310	34950-1210	34950-1220		
KEY A, BLACK	33482-1311	A-BLK	GCP	PLR	M-R	1	2		4	5	6	7		9	10	11	12	PLANNED OBSOLESCENCE	SEE 33482-6311	34950-1210	34950-1220	
KEY A, BLACK	33482-1312	A-BLK	GCP	PLR	M-R								8	9			PLANNED OBSOLESCENCE	SEE 33482-6312	34950-1210	34950-1220		
KEY A, BLACK	33482-1313	A-BLK	GCP	PLR	M-R			3	4	5	6		8	9	10	11	PLANNED OBSOLESCENCE	SEE 33482-6313	34950-1210	34950-1220		
KEY A, BLACK	33482-1314	A-BLK	GCP	PLR	M-R			3			6	7	8	9	10		PLANNED OBSOLESCENCE	SEE 33482-6314	34950-1210	34950-1220		
KEY A, BLACK	33482-1315	A-BLK	GCP	PLR	M-R						6	7	8	9			PLANNED OBSOLESCENCE	SEE 33482-6315	34950-1210	34950-1220		
KEY A, BLACK	33482-1316	A-BLK	GCP	PLR	M-R					5	6	7	8			11	PLANNED OBSOLESCENCE	SEE 33482-6316	34950-1210	34950-1220		
KEY A, BLACK	33482-1317	A-BLK	GCP	PLR	M-R	1	2										PLANNED OBSOLESCENCE	SEE 33482-6317	34950-1210	34950-1220		
KEY A, BLACK	33482-1318	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8				PLANNED OBSOLESCENCE	SEE 3348				

MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

Table with columns: ASSEMBLY DESCRIPTION, ASSEMBLY PART NUMBER, COMPONENT (HOUSING KEY/COLOR, GROMMET CAP, PLR, MAT SEAL), BLOCKED TERMINALS (1-12), STATUS, COMMENTS, and OPTIONAL ATTACHMENTS SOLD SEPERATELY (BACKSHELL WITH RIBS, BACKSHELL WITHOUT RIBS). Rows list various part numbers and their configurations.



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

Table with columns: ASSEMBLY DESCRIPTION, ASSEMBLY PART NUMBER, COMPONENT (HOUSING KEY/COLOR, GROMMET CAP, PLR, MAT SEAL), BLOCKED TERMINALS (1-12), STATUS, COMMENTS, and OPTIONAL ATTACHMENTS SOLD SEPARATELY (BACKSHELL WITH RIBS, BACKSHELL WITHOUT RIBS). Rows list various part numbers and their corresponding terminal configurations and statuses.

**MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET**

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY		
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12					
KEY A, BLACK	33482-6239	A-BLK	GCP	PLR	M-B	1				5	6	7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6240	A-BLK	GCP	PLR	M-B		2	3					8	9	10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6241	A-BLK	GCP	PLR	M-B							7	8	9	10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6242	A-BLK	GCP	PLR	M-B							7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6243	A-BLK	GCP	PLR	M-B		2							9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6244	A-BLK	GCP	PLR	M-B		2		4									SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6245	A-BLK	GCP	PLR	M-B									9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6246	A-BLK	GCP	PLR	M-B										11			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6247	A-BLK	GCP	PLR	M-B		2	3	4			7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6248	A-BLK	GCP	PLR	M-B	1		3	4	5	6	7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6249	A-BLK	GCP	PLR	M-B				4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6250	A-BLK	GCP	PLR	M-B				4	5	6	7	8	9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6251	A-BLK	GCP	PLR	M-B		2		4	5			8		10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6252	A-BLK	GCP	PLR	M-B							7						SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6253	A-BLK	GCP	PLR	M-B		2	3	4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6254	A-BLK	GCP	PLR	M-B		2	3	4	5				10	11	12		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6255	A-BLK	GCP	PLR	M-B		2	3	4	5	6	7		10	11	12		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6256	A-BLK	GCP	PLR	M-B	1					6	7		9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6257	A-BLK	GCP	PLR	M-B									9	10		12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6258	A-BLK	GCP	PLR	M-B		2	3								11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6259	A-BLK	GCP	PLR	M-B	1	2	3	4	5				9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6260	A-BLK	GCP	PLR	M-B											11	12	SALEABLE		34950-1210	34950-1220	
KEY C, DARK GRAY	33482-6261	C-DG	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220	
KEY D, STONE GRAY	33482-6262	D-SG	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220	
KEY C, DARK GRAY	33482-6263	C-DG	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY D, STONE GRAY	33482-6264	D-SG	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6265	A-BLK	GCP	PLR	M-B						6	7	8	9	10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6266	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7					12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6267	A-BLK	GCP	PLR	M-B			3	4	5	6	7						SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6268	A-BLK	GCP	PLR	M-B			3	4	5	6	7	8	9	10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6269	A-BLK	GCP	PLR	M-B	1	2	3	4	5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6270	A-BLK	GCP	PLR	M-B		2		4				7	8	9	10		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6271	A-BLK	GCP	PLR	M-B		2						7	8	9			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6272	A-BLK	GCP	PLR	M-B		2					7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6273	A-BLK	GCP	PLR	M-B								8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6274	A-BLK	GCP	PLR	M-B	1		3	4	5	6		8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6275	A-BLK	GCP	PLR	M-B				4				8		10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6276	A-BLK	GCP	PLR	M-B	1	2	3	4		6		8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6277	A-BLK	GCP	PLR	M-B	1	2	3								11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6278	A-BLK	GCP	PLR	M-B						6						12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6279	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7	8	9	10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6280	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6			9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6281	A-BLK	GCP	PLR	M-B		2		4		6		8		10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6282	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6			9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6283	A-BLK	GCP	PLR	M-B						6			9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6284	A-BLK	GCP	PLR	M-B	1		3	4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY D, STONE GRAY	33482-6285	D-SG	GCP	PLR	M-B	1					6	7						SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6286	A-BLK	GCP	PLR	M-B		2	3					8	9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6287	A-BLK	GCP	PLR	M-B	1						7						SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6288	A-BLK	GCP	PLR	M-B	1					6							SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6289	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6		8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6290	A-BLK	GCP	PLR	M-B	1						7					12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6291	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6292	A-BLK	GCP	PLR	M-B									9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6293	A-BLK	GCP	PLR	M-B			3	4					9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6294	A-BLK	GCP	PLR	M-B	1	2			5	6	7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6295	A-BLK	GCP	PLR	M-B	1	2			5	6	7	8			11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6296	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6297	A-BLK	GCP	PLR	M-B				4		6				10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6298	A-BLK	GCP	PLR	M-B					6						11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6299	A-BLK	GCP	PLR	M-B	1	2					7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6300	A-BLK	GCP	PLR	M-B	1	2	3							10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6301	A-BLK	GCP	PLR	M-B	1	2						7	8			12	SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6302	B-LG	GCP	PLR	M-B										10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6303	A-BLK	GCP	PLR	M-B	1	2	3	4			7	8	9	10		12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6304	A-BLK	GCP	PLR	M-B	1	2	3	4			7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6305	B-LG	GCP	PLR	M-B										10	11	12	SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6306	B-LG	GCP	PLR	M-B	1	2	3	4	5	6	7			10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6307	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6308	A-BLK	GCP	PLR	M-B								7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6309	A-BLK	GCP	PLR	M-B	1							8		10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6310	A-BLK	GCP	PLR	M-B	1			4							11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6311	A-BLK	GCP	PLR	M-B	1	2		4	5	6	7		9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6312	A-BLK	GCP	PLR	M-B								8	9				SALEABLE		34950-1210	34950-1220	

MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

Table with columns: ASSEMBLY DESCRIPTION, ASSEMBLY PART NUMBER, COMPONENT (HOUSING KEY/COLOR, GROMMET CAP, PLR, MAT SEAL), BLOCKED TERMINALS (1-12), STATUS, COMMENTS, and OPTIONAL ATTACHMENTS SOLD SEPERATELY (BACKSHELL WITH RIBS, BACKSHELL WITHOUT RIBS).



MX150 2X6 BLADE SEALED ASSY MAT SEAL BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY		
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12					
KEY A, BLACK	33482-6387	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6388	A-BLK	GCP	PLR	M-B	1	2	3								10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6389	A-BLK	GCP	PLR	M-B	1	2	3			6					11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6390	A-BLK	GCP	PLR	M-B	1		3	4							11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6391	A-BLK	GCP	PLR	M-B	1	2	3			6					10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-6392	A-BLK	GCP	PLR	M-B	1		3	4							11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6393	A-BLK	GCP	PLR	M-B				4	5		7				11	12	SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6394	B-LG	GCP	PLR	M-B	1	2	3	4				8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6395	B-LG	GCP	PLR	M-B	1	2	3	4				8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6396	A-BLK	GCP	PLR	M-B	1					6	7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6397	A-BLK	GCP	PLR	M-B				4		6		8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6398	A-BLK	GCP	PLR	M-B				4	5	6	7				11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6399	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8			11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6400	A-BLK	GCP	PLR	M-B	1	2	3				7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6401	A-BLK	GCP	PLR	M-B	1	2	3				7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6402	A-BLK	GCP	PLR	M-B				4	5	6		8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6403	A-BLK	GCP	PLR	M-B					5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6404	A-BLK	GCP	PLR	M-B					5	6	7	8				12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6405	A-BLK	GCP	PLR	M-B							7	8				12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6406	A-BLK	GCP	PLR	M-B		2	3		5	6	7		9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6407	A-BLK	GCP	PLR	M-B			3							10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6408	A-BLK	GCP	PLR	M-B				4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6409	A-BLK	GCP	PLR	M-B			3	4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6410	A-BLK	GCP	PLR	M-B	1	2	3	4				8	9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6411	A-BLK	GCP	PLR	M-B		2	3						9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6412	A-BLK	GCP	PLR	M-B								8		10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6413	A-BLK	GCP	PLR	M-B	1		3		5						11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6414	A-BLK	GCP	PLR	M-B	1		3		5			8		10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6415	A-BLK	GCP	PLR	M-B		2	3		5	6	7		9		11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6416	A-BLK	GCP	PLR	M-B	1			4	5	6		8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6417	A-BLK	GCP	PLR	M-B	1			4	5			8		10		12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6418	A-BLK	GCP	PLR	M-B	1	2	3	4	5			8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6419	A-BLK	GCP	PLR	M-B		2	3		5	6	7		9	10	11	12	SALEABLE	SEE 33482-6406	34950-1210	34950-1220	
KEY A, BLACK	33482-6420	A-BLK	GCP	PLR	M-B	1	2	3	4				8	9				SALEABLE	SEE 33482-6410	34950-1210	34950-1220	
KEY A, BLACK	33482-6421	A-BLK	GCP	PLR	M-B		2	3						9				SALEABLE	SEE 33482-6411	34950-1210	34950-1220	
KEY A, BLACK	33482-6422	A-BLK	GCP	PLR	M-B								8		10	11		SALEABLE	SEE 33482-6412	34950-1210	34950-1220	
KEY A, BLACK	33482-6423	A-BLK	GCP	PLR	M-B	1		3		5						11		SALEABLE	SEE 33482-6413	34950-1210	34950-1220	
KEY A, BLACK	33482-6424	A-BLK	GCP	PLR	M-B	1		3		5			8		10	11		SALEABLE	SEE 33482-6414	34950-1210	34950-1220	
KEY A, BLACK	33482-6425	A-BLK	GCP	PLR	M-B		2		4		6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6426	A-BLK	GCP	PLR	M-B				3	4						11	12	SALEABLE	SEE 33482-6385	34950-1210	34950-1220	
KEY A, BLACK	33482-6427	A-BLK	GCP	PLR	M-B				3	4					9	10	11	12	SALEABLE	SEE 33482-6293	34950-1210	34950-1220
KEY A, BLACK	33482-6428	A-BLK	GCP	PLR	M-B	1	2				5	6	7	8	9	10		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6429	A-BLK	GCP	PLR	M-B									9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6430	A-BLK	GCP	PLR	M-B			3	4	5	6		8	9				SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6431	B-LG	GCP	PLR	M-B	1	2	3	4				8			11	12	SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6432	B-LG	GCP	PLR	M-B	1	2	3	4				8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6433	A-BLK	GCP	PLR	M-B										10	11	12	SALEABLE	SEE 33482-6249	34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6434	B-LG	GCP	PLR	M-B							7	8	9			12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6435	A-BLK	GCP	PLR	M-B													SALEABLE	SEE 33482-6308	34950-1210	34950-1220	
KEY A, BLACK	33482-6436	A-BLK	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6437	A-BLK	GCP	PLR	M-B		2						8	9				SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6438	B-LG	GCP	PLR	M-B	1	2	3	4				8			11	12	NOT RECOMMENDED	SEE 33482-6431	34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6439	B-LG	GCP	PLR	M-B	1	2	3	4					8				NOT RECOMMENDED	SEE 33482-6432	34950-1210	34950-1220	
KEY A, BLACK	33482-6440	A-BLK	GCP	PLR	M-B	1	2				6			9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6441	A-BLK	GCP	PLR	M-B	1	2	3			6	7				10	11	12	SALEABLE	SEE 33482-6370	34950-1210	34950-1220
KEY A, BLACK	33482-6442	A-BLK	GCP	PLR	M-B		2		4		6		8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6443	A-BLK	GCP	PLR	M-B		2		4		6							SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6444	A-BLK	GCP	PLR	M-B			3	4		6		8	9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6445	A-BLK	GCP	PLR	M-B				4			7		9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY C, DARK GRAY	33482-6446	C-DG	GCP	PLR	M-B				3	4								SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6447	A-BLK	GCP	PLR	M-B	1	2	3			6		8			11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6448	A-BLK	GCP	PLR	M-B					5	6	7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-6449	B-LG	GCP	PLR	M-B							7			10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6450	A-BLK	GCP	PLR	M-B		2	3		5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6451	A-BLK	GCP	PLR	M-B													SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6452	A-BLK	GCP	PLR	M-B				3	4			8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6453	A-BLK	GCP	PLR	M-B	1	2	3	4				8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6454	A-BLK	GCP	PLR	M-B				3	4			7	8	9			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6455	A-BLK	GCP	PLR	M-B	1			4				7	8			12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6456	A-BLK	GCP	PLR	M-B	1	2		4	5	6					11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6457	A-BLK	GCP	PLR	M-B		2		4	5	6	7					12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6458	A-BLK	GCP	PLR	M-B						6							SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6459	A-BLK	GCP	PLR	M-B								7	8	9			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-6460	A-BLK	GCP	PLR	M-B	1											12	SALEABLE		34950-1210	34950-1220	

MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

Table with columns: ASSEMBLY DESCRIPTION, ASSEMBLY PART NUMBER, COMPONENT (HOUSING KEY/COLOR, GROMMET CAP, PLR, MAT SEAL), BLOCKED TERMINALS (1-12), STATUS, COMMENTS, and OPTIONAL ATTACHMENTS SOLD SEPERATELY (BACKSHELL WITH RIBS, BACKSHELL WITHOUT RIBS).

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

Table with columns: ASSEMBLY DESCRIPTION, ASSEMBLY PART NUMBER, COMPONENT (HOUSING KEY/COLOR, GROMMET CAP, PLR, MAT SEAL), BLOCKED TERMINALS (1-16), STATUS, COMMENTS, and OPTIONAL ATTACHMENTS SOLD SEPARATELY (BACKSHELL WITH RIBS, BACKSHELL WITHOUT RIBS, 90° ADAPTOR WITH RIBS, 90° ADAPTOR WITHOUT RIBS).

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

Table with columns: ASSEMBLY DESCRIPTION, ASSEMBLY PART NUMBER, COMPONENT (HOUSING KEY/COLOR, GROMMET CAP, PLR, MAT SEAL), BLOCKED TERMINALS (1-16), STATUS, COMMENTS, and OPTIONAL ATTACHMENTS SOLD SEPARATELY (BACKSHELL WITH RIBS, BACKSHELL WITHOUT RIBS, 90° ADAPTOR WITH RIBS, 90° ADAPTOR WITHOUT RIBS).

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16						
KEY A, BLACK	33482-1857	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8857	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1858	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8858	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1859	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8859	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-1860	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	PLANNED OBSOLESCENCE	SEE 33482-8860	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8639	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPARATELY							
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS				
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16										
KEY A, BLACK	33482-8640	A-BLK	GCP	PLR	M-B					5															16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8641	A-BLK	GCP	PLR	M-B					5																	SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8642	B-LG	GCP	PLR	M-B						4															12	SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8643	A-BLK	GCP	PLR	M-B																					15	SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8644	B-LG	GCP	PLR	M-B						4																SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8645	B-LG	GCP	PLR	M-B						4																SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8646	A-BLK	GCP	PLR	M-B							4															SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8647	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8648	A-BLK	GCP	PLR	M-B							4														12	SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8649	B-LG	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8650	B-LG	GCP	PLR	M-B							4															SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8651	B-LG	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8652	B-LG	GCP	PLR	M-B									6													SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8653	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8654	A-BLK	GCP	PLR	M-B							4															SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8655	B-LG	GCP	PLR	M-B							4															SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8656	B-LG	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8657	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8658	B-LG	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8659	B-LG	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8660	B-LG	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8661	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-8662	B-LG	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8663	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8664	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8665	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8666	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8667	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8668	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8669	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8670	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8671	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8672	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8673	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8674	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8675	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8676	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8677	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8678	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8679	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8680	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8681	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8682	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8683	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8684	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8685	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8686	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8687	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8688	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8689	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8690	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8691	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8692	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8693	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8694	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8695	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8700	A-BLK	GCP	PLR	M-B																						SALEABLE	34950-1611	34950-1621	3495	


MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY									
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS						
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16												
KEY A, BLACK	33482-8736	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6					13	14					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641						
KEY A, BLACK	33482-8737	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6							10	11	12	13	14	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8738	A-BLK	GCP	PLR	M-B	1	2						7	8									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8739	A-BLK	GCP	PLR	M-B			3	4														SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8740	A-BLK	GCP	PLR	M-B								9										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8741	A-BLK	GCP	PLR	M-B			3	4				9	10	11	12	13	14	15	16			SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8742	A-BLK	GCP	PLR	M-B										11	12	13	14					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8743	A-BLK	GCP	PLR	M-B										11				14				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8744	A-BLK	GCP	PLR	M-B		2					7		9									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8745	A-BLK	GCP	PLR	M-B		2							9									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8746	A-BLK	GCP	PLR	M-B		2							9									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8747	A-BLK	GCP	PLR	M-B											12	13	14					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8748	A-BLK	GCP	PLR	M-B			2					9										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8749	A-BLK	GCP	PLR	M-B		1							10	11	12	13	14					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8750	A-BLK	GCP	PLR	M-B	1	2						9	10	11	12	13	14					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY C, DARK GRAY	33482-8751	C-DG	GCP	PLR	M-B							8											SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY D, STONE GRAY	33482-8752	D-SG	GCP	PLR	M-B							8											SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY C, DARK GRAY	33482-8753	C-DG	GCP	PLR	M-B							8	9										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY D, STONE GRAY	33482-8754	D-SG	GCP	PLR	M-B							8	9										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY C, DARK GRAY	33482-8755	C-DG	GCP	PLR	M-B	1						8	9										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY D, STONE GRAY	33482-8756	D-SG	GCP	PLR	M-B	1						8	9										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY C, DARK GRAY	33482-8757	C-DG	GCP	PLR	M-B	1						8	9										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY D, STONE GRAY	33482-8758	D-SG	GCP	PLR	M-B	1						8	9										SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8759	A-BLK	GCP	PLR	M-B	1	2	3	4	5			9	10	11	12	13	14					SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8760	A-BLK	GCP	PLR	M-B		2						7		9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8761	A-BLK	GCP	PLR	M-B		2					5			9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641					
KEY A, BLACK	33482-8762	A-BLK	GCP	PLR	M-B	1	2					5			7			9	10	11	12	13	14	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8763	A-BLK	GCP	PLR	M-B							7											16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8764	A-BLK	GCP	PLR	M-B							5	6	7		9							16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8765	A-BLK	GCP	PLR	M-B		2					5			7								16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8766	A-BLK	GCP	PLR	M-B							5	6	7		9	10	11	12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8767	A-BLK	GCP	PLR	M-B							5	6	7		9							16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8768	A-BLK	GCP	PLR	M-B							5	6	7		9	10						16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8769	A-BLK	GCP	PLR	M-B	1			4	5	6				8				12	13	14		16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8770	A-BLK	GCP	PLR	M-B	1	2		4	5	6				8	9	10			12	13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8771	A-BLK	GCP	PLR	M-B	1			4	5	6	7			8		10					13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641		
KEY A, BLACK	33482-8772	A-BLK	GCP	PLR	M-B											10							16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8773	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6												16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8774	A-BLK	GCP	PLR	M-B												10						15	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8775	A-BLK	GCP	PLR	M-B										9	10							15	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8776	A-BLK	GCP	PLR	M-B			3	4						9	10							15	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, YELLOW	33482-8777	A-YW	GCP	PLR	M-B																				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8778	A-BLK	GCP	PLR	M-B						5						8								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8779	A-BLK	GCP	PLR	M-B						5	6	7		8	9	10	11	12						SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8780	A-BLK	GCP	PLR	M-B			3	4	5	6									13	14				SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8781	A-BLK	GCP	PLR	M-B	1			4	5	6	7		8	9	10							15	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8782	A-BLK	GCP	PLR	M-B	1			4	5	6	7		8	9	10							15	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8783	A-BLK	GCP	PLR	M-B											11	12						15	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8784	A-BLK	GCP	PLR	M-B			3																	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8785	A-BLK	GCP	PLR	M-B	1						5				7									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8786	A-BLK	GCP	PLR	M-B		2					5				7									SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8787	A-BLK	GCP	PLR	M-B	1	2					5					9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8788	A-BLK	GCP	PLR	M-B	1	2										9								SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641			
KEY A, BLACK	33482-8789	A-BLK	GCP	PLR	M-B	1	2					5				9							15	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8790	A-BLK	GCP	PLR	M-B	1	2					5				9							16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641				
KEY A, BLACK	33482-8791	A-BLK	GCP	PLR	M-B	1	2	3													10	11	12	13	14	15	16	SALEABLE		34950-1611	34950-1621	34951-1631	34951-1641
KEY A, BLACK	33482-8792	A-BLK	GCP	PLR	M-B							5	</																				

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

Table with columns: ASSEMBLY DESCRIPTION, ASSEMBLY PART NUMBER, COMPONENT (HOUSING KEY/COLOR, GROMMET CAP, PLR, MAT SEAL), BLOCKED TERMINALS (1-16), STATUS, COMMENTS, and OPTIONAL ATTACHMENTS SOLD SEPARATELY (BACKSHELL WITH RIBS, BACKSHELL WITHOUT RIBS, 90° ADAPTOR WITH RIBS, 90° ADAPTOR WITHOUT RIBS).

MX150 2X10 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET



FOR ADDITIONAL INFORMATION SEE 5D-33482-0001

Table with 4 columns: ABBREVIATION, DESCRIPTION, COLOR, MATERIAL. Lists various housing keys (A-Blk, B-Lg, C-Br, D-Gr, A-Yl, C-Dg, D-Sg), grommet caps (GCP, GCO), and mat seals (PLR, M-R, M-B) with their respective colors and materials.

Main BOM and Pin Out table with columns: ASSEMBLY DESCRIPTION, ASSEMBLY PART NUMBER, COMPONENT (Housing Key/Color, Grommet Cap, PLR, Mat Seal), CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION (1-20), STATUS, COMMENTS, and OPTIONAL ATTACHMENTS SOLD SEPERATELY (Backshell with/without ribs, 90° Adaptor with/without ribs). Rows list various assembly configurations from 33482-2001 to 33482-2081.

MX150 2X10 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																				STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY														
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																						BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS											
						1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20																	
KEY A, BLACK	33482-2082	A-BLK	GCP	PLR	M-R	1		3	4						8	9	10	11					13	14					18	19	20	OBSOLETE	SEE 33482-2182	34950-2011	34950-2021	34951-1631	34951-1641					
KEY A, BLACK	33482-2083	A-BLK	GCP	PLR	M-R	1									8	9	10	11															OBSOLETE	SEE 33482-2183	34950-2011	34950-2021	34951-1631	34951-1641				
KEY A, BLACK	33482-2084	A-BLK	GCP	PLR	M-R	1																											OBSOLETE	SEE 33482-2184	34950-2011	34950-2021	34951-1631	34951-1641				
KEY A, BLACK	33482-2085	A-BLK	GCP	PLR	M-R	1																												OBSOLETE	SEE 33482-2185	34950-2011	34950-2021	34951-1631	34951-1641			
KEY A, BLACK	33482-2086	A-BLK	GCP	PLR	M-R				2	3																									OBSOLETE	SEE 33482-2186	34950-2011	34950-2021	34951-1631	34951-1641		
KEY A, BLACK	33482-2087	A-BLK	GCP	PLR	M-R	1																													OBSOLETE	SEE 33482-2187	34950-2011	34950-2021	34951-1631	34951-1641		
KEY A, BLACK	33482-2088	A-BLK	GCP	PLR	M-R	1										5	6	7	8																OBSOLETE	SEE 33482-2188	34950-2011	34950-2021	34951-1631	34951-1641		
KEY A, BLACK	33482-2089	A-BLK	GCP	PLR	M-R	1			2	3	4	5	6	7	8	9																				OBSOLETE	SEE 33482-2189	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2090	A-BLK	GCP	PLR	M-R	1			2	3	4	5	6	7	8	9	10	11	12	13	14	15	16														OBSOLETE	SEE 33482-2190	34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2101	A-BLK	GCO	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-2102	B-LG	GCO	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY C, BROWN	33482-2103	C-BR	GCO	PLR	M-B																															NOT RECOMMENDED	SEE 33482-2154	34950-2011	34950-2021	34951-1631	34951-1641	
KEY D, GREEN	33482-2104	D-GR	GCO	PLR	M-B																															NOT RECOMMENDED	SEE 33482-2155	34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2106	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2107	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2108	A-BLK	GCP	PLR	M-B					4	5	6																								SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2109	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2110	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2111	A-BLK	GCP	PLR	M-B		1	2																												SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2112	A-BLK	GCP	PLR	M-B		1	2																												SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2113	A-BLK	GCP	PLR	M-B		1	2																												SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2114	A-BLK	GCP	PLR	M-B					3	4	5																								SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2115	A-BLK	GCP	PLR	M-B					3	4	5																								SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2116	A-BLK	GCP	PLR	M-B				2																											SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2117	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2118	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2119	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2120	A-BLK	GCP	PLR	M-B					3	4	5																								SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2121	A-BLK	GCP	PLR	M-B		1	2	3	4	5																									SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2122	A-BLK	GCP	PLR	M-B					3	4	5																								SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2123	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2124	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2125	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2126	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2127	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2128	A-BLK	GCP	PLR	M-B		1			3	4	5	6	7	8	9	10	11																		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2129	A-BLK	GCP	PLR	M-B					3	4	5	6	7	8	9	10	11																		SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2130	A-BLK	GCP	PLR	M-B					3	4	5																								SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2131	A-BLK	GCP	PLR	M-B					3	4	5																								SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2132	A-BLK	GCP	PLR	M-B					3	4	5																								SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2133	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2134	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2135	A-BLK	GCP	PLR	M-B																															SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2136	A-BLK	GCP	PLR	M-B										7	9																				SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2137	A-BLK	GCP	PLR	M-B										7	9																				SALEABLE		34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2138	A-BLK	GCP	PLR	M-B		1	2	3	4	5	6	7	8	9	10																				SALEABLE		34950-2011	34950-2021	34951-1631		

MX150 2X10 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																				STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY							
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																						BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	90° ADAPTOR WITH RIBS	90° ADAPTOR WITHOUT RIBS				
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20										
KEY A, BLACK	33482-2198	A-BLK	GCP	PLR	M-B	1	2	3			7	8	9							16			19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641		
KEY A, BLACK	33482-2199	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7	8	9				13	14	15	16			19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2200	A-BLK	GCP	PLR	M-B	1	2	3	4	5												17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2201	A-BLK	GCP	PLR	M-B	1	2	3					9	10	11	12					15			19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2202	A-BLK	GCP	PLR	M-B	1	2	3	4	5			8	9										19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2203	A-BLK	GCP	PLR	M-B	1	2	3					9											19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2204	A-BLK	GCP	PLR	M-B				4	5	6					12				15	16	17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY B, LIGHT GRAY	33482-2205	B-LG	GCP	PLR	M-B				3	4	5	6							14					19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2206	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6												17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2207	B-LG	GCP	PLR	M-B				4	5	6																SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2208	B-LG	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2209	B-LG	GCP	PLR	M-B				4	5	6	7															SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2210	A-BLK	GCP	PLR	M-B	1																					SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2211	A-BLK	GCP	PLR	M-B	1	2					7															SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2213	A-BLK	GCP	PLR	M-B													13									SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2214	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2215	A-BLK	GCP	PLR	M-B		2																				SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2216	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2217	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2218	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7															SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2219	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2220	A-BLK	GCP	PLR	M-B	1																					SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2221	A-BLK	GCP	PLR	M-B		2																				SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2222	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13									SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2223	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2224	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2225	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13									SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2226	B-LG	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2227	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2228	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2229	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2230	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2231	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13	14								SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2232	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2233	B-LG	GCP	PLR	M-B	1	2	3	4	5	6	7	8														SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2234	B-LG	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY B, LIGHT GRAY	33482-2235	B-LG	GCP	PLR	M-B		2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2236	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2237	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2238	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2239	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2240	A-BLK	GCP	PLR	M-B																						SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641
KEY A, BLACK	33482-2241	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2242	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2243	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2244	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2245	A-BLK	GCP	PLR	M-B		2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2246	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2247	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	
KEY A, BLACK	33482-2248	A-BLK	GCP	PLR	M-B		2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	SALEABLE					34950-2011	34950-2021	34951-1631	34951-1641	

