



(1)

NOTES:

MATERIAL: HOUSING: DIALLYL PTHYHALATE, UL94V-0 CONTACT MATERIAL: COPPER ALLOY CONTACT PLATING: GOLD PLATING OVER NICKEL INSERTION FORCE: 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT WITHDRAWAL FORCE: 6 TO 16 Oz (0.56 TO 4.45N) PER CONTACT

OPERATING TEMPERATURE: -65°C ~ 125°C

CURRENT RATING: **10A PER CONTACT** CONTACT RESISTANCE:  $10m\Omega$  MAX. INSULATOR RESISTANCE: 5000MΩ min. DIELECTRIC WITHSTANDING VOLTAGE: 2000V AC rms AT SEA LEVEL

CONTACT TYPE: 000 - No Contacts Assembled

	415 & 438 SERIES CARD EDGE		SW REFERENCE NO.: 415 ASSEMBLY		
			DRAWN: W.T	DATE: AUG. 01/2	018
			CHECKED:	DATE:	
MS TO	EDAC INC	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC INCAND	SCALE: 1:1	SHEET 1 OF	1
CTIVES IANCY.		SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWING NUMBER: 415-029-000-212		ISSUE
			PART NUMBER: 415-029	-000-212	1



THIS SERIES FULLY CONFORMS THE EUROPEAN UNION DIRECT 2011/65/EU FOR RoHS COMPLIA