

SPECIFICATIONS

Current Rating:	1.5 Amps
Insulation Resistance:	1000MΩ Min
Contact Resistance:	20mΩ Max
Withstanding Voltage:	AC 500V
Operation Temperature:	-40° to+105°
Contact Material:	Brass
Standard:	PA6T
Insrlator Material:	Polyester
Contact Plating:	Gold Flash
Max.Processing Temp:	240° C for30-60seconds (260° C for5seconds)







RECOMMEND P.C.B LAYOUT

PCB TOLERANCE:±0.05 (TOP VIEW)

深圳市虹成电子有限公司

UNLESS OTHEWIXE SPECIFIED TOLERANCE		DRAWM NAME:	排针2.0PH H2.0 2x10Pin SMT PC6.5 PA4.0 PB2.5 L8.2 6T		
X :±0.30	X° :±5°	SIZE A4	SCALE N:1	PROUCT NO.	HC-PZ200-2x10-8.2LS
X.X :±0.25	X.X° :±1°	REV A	UNIT mm	PROJECT	PAGE 1/1
X.XX:±0.20	X.XX° :±0.5°				
CHECKED: 陈超凡 2022/04/24		CHECKED: / /		APPROVED: / /	

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.00	11	20.00	22.00	21	40.00	42.00	31	60.00	62.00
2	2.00	4.00	12	22.00	24.00	22	42.00	44.00	32	62.00	64.00
3	4.00	6.00	13	24.00	26.00	23	44.00	46.00	33	64.00	66.00
4	6.00	8.00	14	26.00	28.00	24	46.00	48.00	34	66.00	68.00
5	8.00	10.00	15	28.00	30.00	25	48.00	50.00	35	68.00	70.00
6	10.00	12.00	16	30.00	32.00	26	50.00	52.00	36	70.00	72.00
7	12.00	14.00	17	32.00	34.00	27	52.00	54.00	37	72.00	74.00
8	14.00	16.00	18	34.00	36.00	28	54.00	56.00	38	74.00	76.00
9	16.00	18.00	19	36.00	38.00	29	56.00	58.00	39	76.00	78.00
10	18.00	20.00	20	38.00	40.00	30	58.00	60.00	40	78.00	80.00