

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION JUL, 2016.
 © COPYRIGHT 2016 By Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F6	REVISED	ECR-18-008351	31MAY2018	TS HY

プリント基板取付寸法図
 (MOUNTING DIMENSIONS FOR P.C. BOARD)

1. 板厚, 1.6±0.15
 (P.C.B. THICKNESS, 1.6±0.15)
 2. 公差, ±0.1
 (TOLERANCE, ±0.1)

注記:
 △ 相手ハウジングと所定の機能を満たしてかん合できること。
 △ フードの反りは0.2以内。
 3 推奨取付けねじ: JIS B 1115 又は, 1122 タッピンねじ
 なべ1種、呼び径φ3を使用し締め付け後半田付けする。
 (締め付けトルク: 0.4N-m 以下)
 4 適用製品規格: 108-5093
 △ [A]面より2mmの範囲で測定のこと。
 6 相手ハウジングとのかん合力は、29.4N以下
 但し、リセパタクルコンタクトは含まない。

NOTES;
 △ IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES
 FUNCTION
 △ WARPAGE 0.2 MAX.
 3 RECOMMENDED MOUNTING SCREW; 3mm DIA,
 PAN HEAD, CLASS 1 TAPPING SCREW SPECIFIED IN JIS
 B1115, B1122 (TORQUE; 0.4N-m MAX.)
 4 SPEC. No. 108-5093
 △ TO BE MEASURED WITHIN 2mm FROM [A]
 6 IN COUPLING WITH THE PLUG HOUSING MATING FORCE
 29.4N MAX. WITHOUT REC CONTACTS.

SEE CUSTOMER DRAWING 6-172035-1						6-172035-1
26.3	4	4	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38 μm MIN.)	NATURAL	2-5172035-1
26.3	4	4	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.76 μm MIN.)	NATURAL	1-5172035-1
48.1	25.8	13.8	PRE-TIN		NATURAL	5-172035-1
30.9	8.6	8.6	PRE-TIN		NATURAL	4-172035-1
26.3	4	4	TIN-LEAD	SELECTIVE GOLD (0.76 μm MIN.)	NATURAL	1-172035-1
26.3	4	4	PRE-TIN		YELLOW	172035-7
26.3	4	4	PRE-TIN		BROWN	172035-3
26.3	4	4	PRE-TIN		BLACK	172035-2
26.3	4	4	PRE-TIN		NATURAL	172035-1
L3	L2	L1	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
CONTACT FINISH コンタクト仕上						

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 31AUG07	TE Connectivity Ltd.	
DIMENSIONS: 単位: 概 mm		CHK K.BETSUI 31AUG07	NAME 名称 9P VERTICAL TYPE CAP HOUSING ASS'Y MULTI-INTERLOCK CONN. (WIRE TO P.C.B.)	
TOLERANCES UNLESS OTHERWISE SPECIFIED. 一般公差		APVD K.BETSUI 31AUG07	DRAWING NO 番号 A2 00779 C=172035	
0 <= x <= 10 : ±0.2 10 <= x <= 30 : ±0.25 30 <= x <= 100 : ±0.3 ANGLE : ±3° 角度		PRODUCT SPEC 製品規格 SEE NOTE 4	RESTRICTED TO —	
MATERIAL 材料 HSG: 66 NYLON CONTACT: BRASS		APPLICATION SPEC 取付適用規格 —	SCALE 尺度 2:1	
FINISH 仕上 SEE TABLE		WEIGHT —	SHEET 1 of 1	
		CUSTOMER DRAWING		REV F6

1471-9 (1/15)

172035