Note: This datasheet may be out of date.

Please download the latest datasheet of HEAWS-100M# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=HEAWS-100M%23

## "#" indicates a package specification code.





HEAWS-100M#














< List of part numbers with package codes > HEAWS-100M=P3



# Appearance & Shape





## References

Packaging	Specifications	Standard Packing Quantity
=P3	330Embossed Tape	250

Mass (typ.)	
1 piece	3.8g



## **Notices**

Rated current (Isat) is specified when the decrease of the initial inductance value at 25%. Rated current (Itemp) is specified when temperature of inductor the is raised 40°C by DC current.

1 of 3

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



# HEAWS-100M#

Note: This datasheet may be out of date.

Please download the latest datasheet of HEAWS-100M# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=HEAWS-100M%23

"#" indicates a package specification code.



# **Specifications**

10.7±0.3mm
10.4±0.3mm
10.0mm
4241 (107104)
10μH±20%
0.1MHz
5000mA
2800mA
0.025Ω
-40°C to 125°C
Ferrite Core
HEAWS

2 of 3

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



## Product Search Data Sheet

Please download the latest datasheet of HEAWS-100M# from the official website of Murata

Note: This datasheet may be out of date.

Manufacturing Co., Ltd.


http://www.murata.com/en/products/productdetail?partno=HEAWS-100M%23


"#" indicates a package specification code.





# Characteristic Data





Impedance - Current Characteristics

Temperature Increase Characteristic

3 of 3

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

