


Fuse - SI FORM C 25 A DIN 72581 - 0913757

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Flat-type plug-in fuse, type C, color code: white, nominal current: 25 A

Your advantages

- ✓ With snap-in foot for secure pre-assembly on the PCB
- ✓ Fuse holder for flat-type fuses with a maximum nominal voltage of 32 V



Key Commercial Data

Packing unit	50 pc
GTIN	 4 017918 104016
GTIN	4017918104016

Technical data

General

Color	white
Flammability rating according to UL 94	V0
Fuse	C
Nominal current I_N	25 A
Nominal voltage U_N	24 V

Dimensions

Width	5 mm
Length	19 mm

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Fuse - SI FORM C 25 A DIN 72581 - 0913757

Classifications

eCl@ss

eCl@ss 10.0.1	27142008
eCl@ss 11.0	27142008
eCl@ss 4.0	27142000
eCl@ss 4.1	27142000
eCl@ss 5.0	27142000
eCl@ss 5.1	27142000
eCl@ss 6.0	27142000
eCl@ss 7.0	27142008
eCl@ss 8.0	27142008
eCl@ss 9.0	27142008

ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC002298
ETIM 4.0	EC002298
ETIM 5.0	EC002298
ETIM 6.0	EC002298
ETIM 7.0	EC002298

UNSPSC

UNSPSC 6.01	30211813
UNSPSC 7.0901	39121410
UNSPSC 11	39121412
UNSPSC 12.01	39121412
UNSPSC 13.2	39121622
UNSPSC 18.0	39121622
UNSPSC 19.0	39121622
UNSPSC 20.0	39121622
UNSPSC 21.0	39121622

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Fuse - SI FORM C 25 A DIN 72581 - 0913757

Approvals

EAC



RU C-
DE.BL08.B.00724

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>