

Wi-Fi®/ Bluetooth® Modules

Wi-Fi® modules

Type 1FX

PN: LBWA1KL1FX-875

CYW43364 Chipset

6.95 x 5.15 x 1.1mm

FCC/IC/CE*/Japan Certified



Wi-Fi® + Bluetooth® modules




Type 1DX

PN: LBEE5KL1DX-883

CYW4343W Chipset

6.95 x 5.15 x 1.1 mm

FCC/IC/CE*/Japan Certified





Type 1LV

PN: LBEE59B1LV-278

CYW43012 Chipset

10.0 x 7.2 x 1.4 mm

FCC/IC/CE*/Japan Certified




Type 1MW

PN: LBEE5HY1MW-230

CYW43455 Chipset

7.9 x 7.3 x 1.1 mm

FCC/IC/CE*/Japan Certified




Type 1CX

PN: LBEH5UL1CX-887

CYW4356 Chipset

11.5 x 8.8 x 1.0 mm



Type 1VA

PN: LBEE5XV1VA-495

CYW88359 Chipset

11.4 x 8.9 x 1.4 mm

FCC/IC/CE*/Japan Certified




*Conducted results for CE Marking Conformity Assessment Procedures are available

Wi-Fi® MCU Modules

ElectricImp modules

electric imp


 **Type 1GC/Imp005**
PN: LBWA1UZ1GC-958
PN: LBWA1UZ1GC-901 (Imp005)
CYW43907 Chipset
10.0 x 10.0 x 1.3 mm




WICED, ElectricImp
FCC/IC/CE* Reference Certified



802.11 a/b/g/n
+ Ethernet + ARM Cortex-R4


 **Type 1MD/Imp004m**
PN: LBEE5ZZ1MD-011
CYW43438+STM Chipset
21.0 x 17.5 x 2.3 mm




ElectricImp
FCC/IC/CE*/Japan Certified



802.11 b/g/n + Bluetooth® 4.1
+ ARM Cortex-M4

 **Type 1CD/Imp003**
PN: LBWA1ZV1CD-716
CYW43362+STM Chipset
10.0 x 7.9 x 1.25 mm





ElectricImp
FCC/IC/CE* Reference Certified



802.11 b/g/n
+ ARM Cortex-M4

Ayla modules


 **Type 1LD**
PN: LBEE5PA1LD-005
PN: LBEE5PA1LD-222 (Ayla)
CYW43438+STM Chipset
8.9 x 7.8 x 1.2 mm



WICED, Ayla
FCC/IC/CE*/Japan Certified



802.11 b/g/n + Bluetooth® 4.2
+ ARM Cortex-M4

 **Type 1AD**
PN: LBWA1CS1AD-806
CYW4390 Chipset
9.4 x 8.9 x 1.2 mm



Ayla
FCC/IC/CE* Reference Certified



802.11 b/g/n + ARM Cortex-M3


 **Ayla Networks**

Wi-Fi MCU modules



Type 1PS

PN: LBWA1UZ1PS-241
CYW54907 Chipset
10.0 x 10.0 x 1.3 mm



WICED
FCC/IC/CE*/Japan Certified



802.11 a/b/g/n/ac + Bluetooth®



Wi-Fi/BT MCU modules

Type 1QP

PN: LBEE5WQ1QP-276
CYW43907+CYW20707 Chipset
11.0 x 11.0 x 1.2 mm



WICED



802.11 a/b/g/n + Bluetooth® 5.0
+ ARM Cortex- R4

Type 1QX

PN: LBEE5WQ1QX-277
CYW54907+CYW20707 Chipset
11.0 x 11.0 x 1.2 mm



WICED




802.11 a/b/g/n + Bluetooth® 5.0
+ ARM Cortex- R4

Bluetooth®/ BLE Modules



Type 1PA

PN: LBCA1KU1PA-245
CYW20719 Chipset
5.9 x 5.1 x 1.17mm




Bluetooth/BLE
WICED Studio

Bluetooth® 5.0

Type 1WA

PN: LBCA1KU1WA
CYW20721 Chipset
5.9 x 5.1 x 1.17mm



Bluetooth/BLE
WICED Studio

Bluetooth® 5.0

Type 1GR

PN: LBCA1ZZ1GR-084
CYW20736 chipset
9.0 x 7.0 x 1.2mm



BLE
WICED Studio
FCC/IC/CE*/Japan Certified

Bluetooth® 4.1



*Conducted results for CE Marking Conformity Assessment Procedures are available