

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0334722061](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: [MX150 Mat-Sealed Female Connector Assembly, Dual Row, 20 Circuits, Keying Option D, without Connector Position Assurance, Stone Gray](#)

Documents:

Drawing (PDF)	Application Specification AS-33611-001-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31300-903-001 (PDF)
3D Model	Test Summary TS-33472-0001-001 (PDF)
Product Specification PS-33472-000-001 (PDF)	Datasheet (PDF)
Application Specification AS-33472-100-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33472-100-CH-001 (PDF)	

General

Product Family	Crimp Housings
Series	33472
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications -Partnership
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	884982301979

Physical

Circuits (maximum)	20
Color - Resin	Stone Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	21.495/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +150°C


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100-001, AS-33472-100-CH-001, AS-33611-001-001
Packaging Specification	PK-31300-903-001
Product Specification	PS-33472-000-001
Sales Drawing	334722002-001, SD-33472-0001-001
Test Summary	TS-33472-0001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)10043-DC (17
Jan 2022)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant

Not Contained

Search Parts in this Series

[33472 Series](#)

Mates With

MX150 Male Sealed Connector [33482](#) .
MX150 Right-Angle Header [348302004](#)

Use With

MX150 Female Terminal [33012](#) ,
[33001](#)
MX150 Sealed Cavity
PlugLink:343450001

This document was generated on 04/14/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION