

PRODUCT-DETAILS

C3SS4-10R-11

C3SS4-10R-11



General Information

Extended Product Type	C3SS4-10R-11
Product ID	1SFA619213R1071
EAN	7320500555651
Catalog Description	C3SS4-10R-11
Long Description	C3SS4-10R-11

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	8536501999

Popular Downloads

Data Sheet, Technical Information	1SFC151007C02_
Instructions and Manuals	1SFC151011M0201

Dimensions

Product Net Width	0.029 m
Product Net Height	0.04 m
Product Net Depth /	0.073 m

Length

Product Net Weight	0.02 kg
--------------------	---------

Technical

Ambient Air Temperature	Operation -25 ... +70 °C Storage -40 ... +85 °C
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	1
Degree of Protection	Front IP66 Front IP67 Front IP69K Terminals IP20
Enclosure Type NEMA	Type1 Type12 Type13 Type3R Type4 Type4X
Pollution Degree	3
Rated Insulation Voltage (U _i)	300 V
Rated Impulse Withstand Voltage (U _{imp})	6 kV
Rated Frequency (f)	50 / 60 Hz
Rated Operational Voltage	Maximum 300 V
Power Loss	Maximum 5 W
Connecting Capacity	Flexible with Ferrule 1 x 0.5...1.5 mm ² Flexible with Ferrule 2 x 0.5...1.5 mm ² Flexible with Insulated Ferrule 1 x 0.5...1.5 mm ² Flexible with Insulated Ferrule 2 x 0.5...1.5 mm ² Flexible 1 x 0.5 ...1.5 mm ² Flexible 2 x 0.5 ...1.5 mm ² Solid 1 x 0.5...1.5 mm ² Solid 2 x 0.5...1.5 mm ²
Terminal Type	Screw Terminals
Tightening Torque	0.8 N·m
Wire Stripping Length	6 mm

Technical UL/CSA

Connecting Capacity UL/CSA	1x 22...14 AWG 2x 22...14 AWG
----------------------------	----------------------------------

Environmental

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Information	2CMT2015-005451
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business

Certificates and Declarations (Document Number)

CB Certificate	CQC_CN_CN50749
CCC Certificate	2003010305054693_
CQC Certificate	CQC2003010305054693
cURus Certificate	UL_E496500-20171020

Declaration of Conformity - CCC	2020980305001187
Declaration of Conformity - CE	2CMT2015-005451
DNV GL Certificate	9AKK107046A3749
EAC Certificate	RU C-CN.ME77.B.00587/20
Environmental Information	1SAC200022H0002
Instructions and Manuals	1SFC151011M0201
RoHS Information	2CMT2015-005451

Container Information

Package Level 1 Units	bag 10 piece
Package Level 1 EAN	7320500473450

Classifications

ETIM 6	EC001029 - Selector switch, complete
ETIM 7	EC001029 - Selector switch, complete
ETIM 8	EC001029 - Selector switch, complete
eClass	V11.0 : 27371243
UNSPSC	39121500

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Compact Range

