



VIEW A (SCALE:1:1)

△6	△4	178306-5
△6	△3	178306-3
△6	△2	178306-2
(FINISH)		製品番号 (PART NO.)

NOTES

- MATERIAL: HOUSING: GLASS FILED THERMO PLASTIC, POLYESTER  
CONTACT: COPPER ALLOY  
RETENTION LEG: COPPER ALLOY
- FINISH (CONTACT AREA): 0.38 μm MIN GOLD PLATING OVER Ni PLATING
- FINISH (CONTACT AREA): 0.76 μm MIN GOLD PLATING OVER Ni PLATING
- FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL
- FINISH (RETENTION LEG): TIN-LEAD PLATED (CONTACT TAIL) OVER NICKEL
- FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

注記

- 材料: ハウジング: ガラス入り熱可塑性ポリエステル樹脂  
コンタクト: 銅合金  
リテンションレグ: 銅合金
- めっき: コンタクト: 全面Ni下地  
接触部: 0.38 μm MIN金めっき
- めっき: コンタクト: 全面Ni下地  
接触部: 0.76 μm MIN金めっき
- めっき: コンタクト: 全面Ni下地  
接触部: 2.0 μm MINスズめっき
- めっき: リテンションレグとコンタクト半田付部  
: ニッケル下地の上に半田めっき
- めっき: リテンションレグとコンタクト半田付部  
: ニッケル下地の上にスズめっき

PRINT DIST DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

NUMBER 178306 METRIC 3rd ANGLE PROJECTION

				Copyright © 1995 AMP(Japan) LTD. ALL RIGHTS RESERVED.		Tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan	
				WIRE RANGE	INSULATION DIA	NAME	
				SEE NOTE	SEE NOTE	12 POS DOUBLE ROW HORIZONTAL HDR ASS'Y FOR DYNAMIC 3100	
				DR. 23 JUN 95 N. Matsubara	DE. 23 JUN 95 N. Matsubara	一般公差 (GENERAL TOLERANCE)	
				CHK. Y. ISHIKAWA	APP. S. MANABE	SIZE A3	LOC J
						NUMBER C-178306	REV. B1
						SCALE 2-1	SHEET 1 OF 1