


NUMBER C-175778
METRIC
3-1/2 ANGLE PROJECTION




- 注:
 1. 材料: 66ナイロン (UL94V-0)
 2. 適用製品規格: 108-5297
 3. 取付適用規格: 114-5140

- NOTES:
 1. MATERIAL: 66 NYLON (UL94V-0)
 2. PRODUCT SPEC.: 108-5297
 3. APPLICATION SPEC.: 114-5140

IMP 27.91

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT



	7-175778-5	5-175778-5	3-175778-5	1-175778-5	15	28.0	30.8	32.0
	7- 4	5- 4	3- 4	1- 4	14	26.0	28.8	30.0
	7- 3	5- 3	3- 3	1- 3	13	24.0	26.8	28.0
	7- 2	5- 2	3- 2	1- 2	12	22.0	24.8	26.0
	7- 1	5- 1	3- 1	1- 1	11	20.0	22.8	24.0
	7- 0	5- 0	3- 0	1- 0	10	18.0	20.8	22.0
	6- 9	4- 9	2- 9		9	16.0	18.8	20.0
	6- 8	4- 8	2- 8		8	14.0	16.8	18.0
	6- 7	4- 7	2- 7		7	12.0	14.8	16.0
	6- 6	4- 6	2- 6		6	10.0	12.8	14.0
	6- 5	4- 5	2- 5		5	8.0	10.8	12.0
	6- 4	4- 4	2- 4		4	6.0	8.8	10.0
	6- 3	4- 3	2- 3		3	4.0	6.8	8.0
	6-175778-2	4-175778-2	2-175778-2	175778-2	2	2.0	4.8	6.0
	BLACK	YELLOW	BLUE	NATURAL	Pos.	A	B	C
	品名	品名	品名	品名	位置			

STE TE Connectivity

名称 圧着タイプ リセハウジング
CRIMP TYPE RECEPTACLE HOUSING
 (AMP CT CONNECTOR 2mm PITCH)

WIRE RANGE: 0.5 - 1.0mm (AWG 30 - 18)
 INSULATION DIA: 0.5 - 1.0mm
 MATERIAL NOTE: 66 NYLON
 FINISH: 未指定

GENERAL TOLERANCE: 0.1mm
 SIZE LOC NUMBER: A3 J C-175778
 SCALE: 5-1 REV. D2 SHEET 1 OF 1

D2	ECO-11-005294	RK	DR	DA	DR. T. NAKAMURA	4/6 '80 DE.
LTR	REVISION RECORD	DR	CHK	DA	CHK. S. KIKUCHI	4/8 '80 APP. S. Kikuchi

CUSTOMER DRAWING