# 3M<sup>™</sup> Mini-Clamp Plug

Designed for Wiring Supplied from Japan and Asia, 2 mm, IDC, Wiremount



• Designed to accommodate typical wiring specifications per Japanese and Asian suppliers

371 Series

- No special wire preparation
- Integrated cable retention
- Design accepts multiple wire size diameters
- Easy, quick, and reliable IDC termination using a standard pliers
- Debris free wire termination
- Mating latches provide a reliable interconnection in demanding applications
- High number of mating cycles
- Compact design saves board space
- Helps reduce maintenance work by providing higher connection reliability
- See Regulatory Information Appendix (RIA) for chemical compliance information

Date Modified: December7, 2017	TS-2092-D Sheet 1 of 3
--------------------------------	---------------------------

### **Physical**

Insu	lati	٥n
IIISU	lau	on.

Insulation.	
Material:	Glass reinforced thermoplastic body & lower cover, transparent thermoplastic cover
Flammability:	UL 94V-0
Color:	Black body, cover-white & color (see Table 1)
Contact:	
Material:	Copper Alloy
Plating:	
Underplating:	2.54 μm [100 μ"] minimum Nickel
Wiping Area::	0.2 µm [8 µ"] minimum Gold with Lubricant
IDC:	Nickel
Accommodation:	Annealed Copper, high-strength Copper, or Copper Alloy. Bare, tinned, or tin overcoated, 20~26 AWG [ 0.14~0.5 ] stranded
Wire Insulation:	Flexible vinyl, semi-rigid vinyl, x -linked polyethylene, or ETFE (see Table 1)
Marking:	3M Logo, Position Indicator, Wire Gauge, Insulator Material

## Electrical

## Environmental

UL File No.: E68080


#### ЗМ

Electronics Materials Solutions Division Interconnect Solutions http://www.3Mconnectors.com

## 3M<sup>™</sup> Mini-Clamp Plug

Designed for Wiring Supplied from Japan and Asia, 2 mm, IDC, Wiremount

371 Series




ЗМ

Electronics Materials Solutions Division Interconnect Solutions http://www.3Mconnectors.com

# 3M<sup>™</sup> Mini-Clamp Plug

Designed for Wiring Supplied from Japan and Asia, 2 mm, IDC, Wiremount



#### ЗМ

Electronics Materials Solutions Division Interconnect Solutions http://www.3Mconnectors.com 3M is a trademark of 3M Company. For technical, sales or ordering information call **800-225-5373**  Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE.

If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M Electronics Materials Solutions Division 6801 River Place Blvd. Austin, TX 78726-9000 1-800-225-5373 www.3M.com/interconnect



Electronics Materials Solutions Division Interconnect Solutions http://www.3Mconnectors.com

Please recycle. Printed in USA. © 3M 2008. All rights reserved. RIA-2217B-D