



1932847-3 Product Details

[Share](#) [Print](#) [Email](#)


1932847-3

Universal Serial Bus (USB) Connectors

Not reviewed for RoHS Compliance

Product Highlights:

- USB 3.0 Industry Standard
- Size = Standard
- A Series
- Receptacle
- Without Locking Feature

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 1932847-3

Active

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Size = Standard
- Gender = Receptacle
- Orientation = Right Angle
- LED = Without
- PCB Mount Retention Type = Boardlock(s)

Mechanical Attachment:

- Mount Location = Top Edge

Termination Features:

- Contact Termination Type = Through Hole
- Termination Method = Solder

Dimensions:

- PCB Thickness, Recommended (mm [in]) = 1.20 [0.048]
- Tail Length (mm [in]) = 1.5 [0.059]

Body Features:

- Locking Feature = Without
- Shell Plating = Matte Tin

Contact Features:

- [Contact Plating](#), [Mating Area](#), [Material](#) = Gold
- [Contact Plating](#), [Mating Area](#), [Thickness](#) (µm [µin]) = 0.127 [5]

Housing Features:

- [Housing Color](#) = Black
- [Housing Material](#) = Thermoplastic

Configuration Features:

- [Number of Ports](#) = 1
- [Number of Positions](#) = 4

Industry Standards:

- [Industry Standard](#) = USB 3.0
- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- [USB-IF Test ID Number \(TID\)](#) = Not Submitted For Testing

Conditions for Usage:

- [Applies To](#) = Printed Circuit Board

Packaging Features:

- [Packaging Method](#) = Tape & Reel
- [Packaging Quantity](#) = 300

Other:

- [Series](#) = A
- [Brand](#) = TE Connectivity

Feedback

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [AODA Accessibility Policy](#)
- [AODA Multi-Year Accessibility Plan](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed



