

PRODUCT-DETAILS

CA5X-01

CA5X-01 Auxiliary contact block



General Information

Extended Product Type	CA5X-01
Product ID	1SBN019010R1001
EAN	3471522387912
Catalog Description	CA5X-01 Auxiliary contact block
Long Description	CA5X-01 is a 1-pole front mounted auxiliary contact block equipped with screw terminals and can be fitted on AX06...150 contactors and NX contactor relays. CA5X-01 is available with 1 N.C. instantaneous contacts for standard industrial environments.

Ordering

Minimum Order Quantity	10 piece
Customs Tariff Number	85030099
Product Main Type	Accessories for Block Contactors

Popular Downloads

Instructions and Manuals	1SBB910513D4501
CAD Dimensional Drawing	2CDC001079B0201

Dimensions

Product Net Width	10 mm
Product Net Depth / Length	47 mm
Product Net Height	36 mm
Product Net Weight	0.014 kg

Technical

Maximum Electrical Switching Frequency	(AC-15) 1200 cycles per hour (DC-13) 900 cycles per hour
Maximum Mechanical Switching Frequency	3600 cycles per hour
Number of Auxiliary Contacts NC	1
Number of Auxiliary Contacts NO	0
Rated Insulation Voltage (U_i)	acc. to IEC 60947-5-1 and VDE 0110 (Gr. C) 690 V
Rated Operational Current AC-15 (I_a)	(690 V) 2 A (24 / 127 V) 6 A (220 / 240 V) 4 A (380 / 400 V) 3 A
Rated Operational Current DC-13 (I_a)	(24 V) 6 A / 144 W (110 V) 0.55 A / 60 W (125 V) 0.55 A / 69 W (220 V) 0.30 A / 66 W (250 V) 0.30 A / 75 W (400 V) 2.8 A / 134 W (500 V) 1 A / 72 W
Rated Operational Voltage	Auxiliary Circuit 690 V Main Circuit 690 V
Rated Short-time Withstand Current Low Voltage (I_{cw})	for 0.1 s 140 A for 1 s 100 A
Suitable For	AX06 AX09 AX12 AX18 AX25 AX32 AX40 AX50 AX65 AX80 AX95 AX115 AX150 NX
Terminal Type	Screw Terminals

Environmental

Conventional Free-air Thermal Current (I_{th})	acc. to IEC 60947-5-1, $\Theta = 40\text{ °C}$ 16 A
RoHS Information	2CMT2021-006277
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Certificates and Declarations

CB Certificate	CB_CN28662
----------------	------------

CCC Certificate	CCC_2013010304656838
CCS Certificate	CCS_GZ13T00025
CQC Certificate	CQC2013010304656838
cUL Certificate	UL-CA-L252354-45-61406102-5
Declaration of Conformity - CCC	2020980304001061
Declaration of Conformity - CE	1SBD250013U1000
EAC Certificate	EAC_RU C-DE ME77 B03562
UL Certificate	UL-US-L252354-15-61406102-5

Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	65 mm
Package Level 1 Depth / Length	130 mm
Package Level 1 Height	40 mm
Package Level 1 Gross Weight	0.14 kg
Package Level 1 EAN	3471522387912
Package Level 2 Units	600 piece
Package Level 2 Width	220 mm
Package Level 2 Depth / Length	380 mm
Package Level 2 Height	300 mm
Package Level 2 Gross Weight	8.4 kg

Classifications

eClass	V11.0 : 27371302
E-Number (Finland)	3708078
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
ETIM 8	EC000041 - Auxiliary contact block
ETIM 9	EC000041 - Auxiliary contact block
IDEA Granular Category Code (IGCC)	4743 >> Auxiliary contact block
Object Classification Code	K
UNSPSC	39121522

Categories

Low Voltage Products and Systems → Control Products → Contactors → Block Contactors Accessories

