

PRODUCT-DETAILS

# SJ203-C63

## SJ203-C63 Miniature Circuit Breaker - 3P - C - 63 A



### General Information

Extended Product Type	SJ203-C63
Product ID	2TAZ141300R0634
EAN	6957625328757
Catalog Description	SJ203-C63 Miniature Circuit Breaker - 3P - C - 63 A
Long Description	Miniature Circuit Breaker - SJ200 - 3P - C - 63 A

### Technical

Standards	IEC/EN 60898-1 GB 10963
Tripping Characteristic	C
Rated Voltage ( $U_r$ )	400 V
Rated Operational Voltage	400 V AC
Rated Insulation Voltage ( $U_i$ )	440 V
Rated Impulse Withstand Voltage ( $U_{imp}$ )	4 kV
Input Voltage Type	AC
Rated Current ( $I_n$ )	63 A
Rated Short-Circuit Capacity	(400 V) 6 kA
Rated Conditional Short-Circuit Current ( $I_{nc}$ )	(400 V) 6 kA
Frequency (f)	50...60 Hz
Rated Frequency (f)	50-60 Hz

Energy Limiting Class	3
Number of Poles	3
Number of Protected Poles	3
Overtoltage Category	III
Release Type	C
Accessories Available	No
Connecting Capacity	Rigid 0 ... 25 mm <sup>2</sup> Flexible 0 ... 25 mm <sup>2</sup>

## Environmental

Ambient Temperature	-25...55 °C
Ambient Air Temperature	Operation -25...55 °C
Degree of Protection	IP20
Pollution Degree	2
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Information	9AKK108467A0533
REACH Declaration	CNIIIB22EDMCB0928
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363

## Dimensions

Width in Number of Modular Spacings	3
Product Net Width	0.053 m
Product Net Height	0.088 m
Product Net Depth / Length	0.044 m
Product Net Weight	0.322 kg
Built-In Depth (t <sub>2</sub> )	69 mm

## Ordering

Minimum Order Quantity	1 piece
------------------------	---------

## Certificates and Declarations

Declaration of Conformity - CE	No declaration needed
--------------------------------	-----------------------

## Installation

Instructions and Manuals	No document needed
--------------------------	--------------------

## Popular Downloads

Data Sheet, Technical Information	1SX400005C2013
-----------------------------------	----------------

## Classifications

ETIM 8	EC000042 - Miniature circuit breaker (MCB)
ETIM 9	EC000042 - Miniature circuit breaker (MCB)

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85362010
eClass	V11.0 : 27141901

---

## Categories

---

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs → Miniature Circuit Breakers MCBs

