



This document is the property of Metek Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used in whole or in part, for manufacture or sale by anyone other than Metek Corporation without the prior written consent of Metek Corporation. The marking on this product doesn't contain environmental hazardous materials. The marking on Material Specification or per directive 2002/95/EC for RoHS is compliant.

序号	成品长度 (单位MM)	线缆长度 (单位MM)	扎带	线材	捆扎数量	纸箱尺寸	样品名称	料号
1	L1=300±15MM	L1=290±5MM	白色 扎带 50MM	透明PE袋自封口120×180 MM	700PCS	450×300×300	USB3.0 AM-AM 蓝色 0.3米	306551-0301102
2	L2=500±25MM	L2=480±10MM	白色 扎带 50MM	透明PE袋自封口120×180 MM	500PCS	450×300×300	USB3.0 AM-AM 蓝色 0.5米	306551-0501102
3	L3=1000±30MM	L3=980±15MM	白色 扎带 50MM	透明PE袋自封口120×180 MM	300PCS	450×300×300	USB3.0 AM-AM 蓝色 1米	306551-1001102
4	L4=1500±40MM	L4=1480±20MM	白色 扎带 80MM	透明PE袋自封口150×200 MM	250PCS	450×300×300	USB3.0 AM-AM 蓝色 1.5米	306551-1501102
5	L5=1800±50MM	L5=1780±25MM	白色 扎带 80MM	透明PE袋自封口150×200 MM	200PCS	450×300×300	USB3.0 AM-AM 蓝色 1.8米	306551-1801102
6	L6=3000±75MM	L6=2960±30MM	白色 扎带 120MM	透明PE袋自封口150×200 MM	110PCS	450×300×300	USB3.0 AM-AM 蓝色 3米	306551-3001102
7	L7=5000±90MM	L7=4950±40MM	白色 扎带 150MM	透明PE袋自封口150×200 MM	70PCS	450×300×300	USB3.0 AM-AM 蓝色 5米	306551-5001102



**PIN ASSIGNMENT**



**CABLE SPECIFICATION**

QTY.	DESCRIPTION	PART NUMBER	DETAIL
4	PE胶料	J4-1111105	白色PE胶料
3	PVC胶料	J2-451102	PVC 45P BLUE U94V-0
2	USB公头	2Pos C3-110112	USB A (M) 4.4IU
1	Cable	依附录 X3-550612	UI-20276 (#30*1P+D+AL+M)*2+#30*1P+#26*2C+ABD OD: 5.5mm Blue
0	DESCRIPTION		

TOLERANCE		APPROVALS		DATE	DRAWING	
X	±0.50	DATE	DATE	26/03/2018	SCALE	1:1
XX	±0.30	APPROVED	DATE		SIZE	A4
XXX	±0.20	ENG DWG	DATE		SHEET	1 OF 1
XXXX	±0.10	PHD	DATE			
ANGULAR	±1°					
UNLESS OTHERWISE SPECIFIED						

**Electrical character:**

- 100% open & short testing.
- Withstanding voltage: DC 300V 0.01Sec.
- Insulation resistance: 5M Ohm(Min).
- Conductive resistance: 3 Ohm(Max).



东莞市讯联电子有限公司

306551-XXX1102

01