



Product: [83006](#)

Lead Wire, #22 Str SPC, TFE Ins, AWM 1213

Request Sample

Product Description

High Temp Plastic Lead Wire, 22AWG (19x34) Silver Plated Copper, TFE Insulation, AWM 1213 105C TYPE E MIL-W-16878/4 600V 200C

Technical Specifications

Product Overview

Suitable Applications:	high temperature, inter-connection circuits, internal wiring of computer and electronic equipments, (Type E) MIL-W-16878/4 applications
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	22 AWG	19x34	SC - Silvered Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PTFE - Polytetrafluoroethylene	0.009 in (0.23 mm)	0.050 in (1.3 mm)

Overall Cable Diameter (Nominal):	0.05 in (1.3 mm)
-----------------------------------	------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
15.75 Ohm/1000ft	Mil-Std-975M Table 3.16 (single wire): 4.5 amps

Voltage

UL Voltage Rating
600 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
200°C	-70°C To +200°C

Bend Radius

Stationary Min.	Installation Min.
0.56 in (14 mm)	0.56 in (14 mm)

Max. Pull Tension:	8 lbs (3.6 kg)
Bulk Cable Weight:	3 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	VW-1
AWM Compliance:	AWM 1213

NEMA Compliance:	HP3
Military Compliance:	MIL-W-16878/4
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.481 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
83006 010100	Black	Reel	100 ft		E
83006 010500	Black	Reel	500 ft		E S
83006 0101000	Black	Reel	1,000 ft	612825378365	
83006 006500	Blue, Light				E S
83006 006100	Blue, Light	Reel	100 ft		E
83006 0061000	Blue, Light	Reel	1,000 ft	612825399346	E S
83006 001100	Brown	Reel	100 ft		E
83006 001500	Brown	Reel	500 ft		E S
83006 0011000	Brown	Reel	1,000 ft		E S
83006 008100	Gray	Reel	100 ft		E
83006 0081000	Gray	Reel	1,000 ft	612825399360	E S
83006 005100	Green, Dark	Reel	100 ft	612825354437	E
83006 005500	Green, Dark	Reel	500 ft		E S
83006 0051000	Green, Dark	Reel	1,000 ft	612825399339	E S
83006 0031000	Orange				E S
83006 003100	Orange	Reel	100 ft		E
83006 002100	Red	Reel	100 ft	612825354420	E
83006 002500	Red	Reel	500 ft		E S
83006 0021000	Red	Reel	1,000 ft	612825378358	
83006 007100	Violet				E
83006 0071000	Violet	Reel	1,000 ft	612825399353	E S
83006 009100	White	Reel	100 ft		E
83006 009500	White	Reel	500 ft		E S
83006 0091000	White	Reel	1,000 ft	612825354048	
83006 004100	Yellow	Reel	100 ft		E
83006 004500	Yellow	Reel	500 ft		E S
83006 0041000	Yellow	Reel	1,000 ft	612825399322	E S

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.