

## **Specification Sheet**

Part Number: 184-44002

Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.

Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.



High Density Slotted Wall Wiring Duct, 4" x 4", Non-Adhesive, PVC, Gray, 120ft/Carton

Article Number 184-44002

Type SLHD4X4

Color Gray (GY)

Quantity Per carton

Product Description HellermannTyton High-Density Slotted Wall Wiring Duct features

narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and

components are more easily accommodated.

Short Description High Density Slotted Wall Wiring Duct, 4" x 4", Non-Adhesive, PVC,

Gray, 120ft/Carton

	_	
Global	Dart	Nama
Giuuai	ган	INAILIE

SLHD4X4-PVC-GY

Length L (Imperial)

6.0

Length L (Metric)

1.83

**Fixation Method** 

Non-Adhesive

Width W (Imperial)

4.0

Width W (Metric)

101.6

Height H (Imperial)

4.07

Height H (Metric)

103.4

Mounting Hole Centers (Imperial)

2.0

Material

Polyvinylchloride (PVC)

**Material Shortcut** 

PVC

Halogen Free

No

UV Resistant (Yes/No)

No

**Operating Temperature** 

+122°F (+50°C)

Reach Compliant (Article 33)

No

ROHS Compliant	Yes
Certification/Specification	EN 50085-1:2005 + A1:2013 CSA EN 50085-2-3_1A UL
UL Recognized (US)	Yes
Package Quantity (Imperial)	120.0
Package Quantity (Metric)	36.58
Customs Number	3925900000

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

Contact Us RoHS/WEEE Compliance Disclaimer Terms and Conditions