



Cable Length (L)	Cable Color	Cat. 5e STP AWG24 Solid Cable	Cat. 5e UTP AWG24 Solid Cable					
		Black	Black	Blue	Red	Green	Yellow	White
0.25m ± 0.01m		17-130464	17-130474	17-130484	17-130494	17-130504	17-130514	17-130524
0.30m ± 0.01m			17-132844					
0.50m ± 0.01m		17-130534	17-130544	17-130554	17-130564	17-130574	17-130584	17-130594
0.60m ± 0.01m			17-132214					
0.75m ± 0.01m		17-130684	17-130694	17-130704	17-130714	17-130724	17-130734	17-130744
1m ± 0.02m		17-103294	17-103304	17-103314	17-103324	17-103334	17-103344	17-103354
1.5m ± 0.02m		17-132544						
2m ± 0.02m		17-101324	17-100654	17-100684	17-100714	17-100744	17-100774	17-100804
3m ± 0.03m		17-130364	17-130374	17-130384	17-130394	17-130404	17-130414	17-130424
4m ± 0.03m		17-101334	17-100664	17-100694	17-100724	17-100754	17-100784	17-100814
5m ± 0.05m		17-101344	17-100674	17-100704	17-100734	17-100764	17-100794	17-100824
10m ± 0.1m		17-103574	17-103584	17-103594	17-103604	17-103614	17-103624	17-103634
15m ± 0.2m		17-130834	17-130844	17-130854	17-130864	17-130874	17-130884	17-130894
20m ± 0.2m		17-130904	17-130914	17-130924	17-130934	17-130944	17-130954	17-130964

Notes: - Special cable lengths are available please contact factory; STP: Shielded Twisted Pair, UTP: Unshielded Twisted Pair

**Notes:**

- Electrical:
  - Meets EIA/TIA-568-B.2 Cat.5e Specification
  - RJ45 Plug Operating Temperature: -40° C to +85° C
- Materials and Finish:
  - RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
  - RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-2
  - RJ45 Plug Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel
  - RJ45 Modular Boot: PVC, Color: See P/N Table
  - Cable: See Above Part Number Table

RoHS Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF CONEC CORPORATION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified			Scale: NTS	Dim. in Meter
	Name		Title	Approval Date	Dimensional: Angles		Material: See Notes	
	k	1 x k	Jul/24/2017	Vincent Ke	2008	Date	Name	Title: RJ45 Cat. 5e Ethernet Patch Cord Standard to Standard
	j	1 x j	Apr/13/2016	Vincent ke	Draw.	Feb. 20	Vincent Ke	
	i	1 x i	Oct/10/2013	Vincent Ke	Appd.	Feb. 20	J. Chaudry	
	h	1 x h	Apr/03/2013	Vincent ke	Norm			
	g	1 x g	Nov/05/2012	Vincent ke	D-old			
	f	1 x f	Sep/05/2012	Vincent ke				
	a	original					Drawing No.: 39K1A375	DIN A3
	Rev.	Changes	Date	Name			Part No.: SEE PART NUMBER ABOVE	Sheet 1/1