

Computer Cable, 10-ft. AB Parallel Gold Cable Cen36M to DB25M

MODEL NUMBER: P606-010-R



Description

Tripp Lite's 10-ft. A-B gold parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Centronics 36 female parallel port. Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing. The cable features gold plated DB25 male/Cent36 male connectors and gold plated copper contacts for superior conductivity. It is manufactured from superior molded cable with integral strain relief and double shielding for maximum EMI/RFI protection. It contains low-capacitance, impedance matched, twisted-pair conductors that protect against cross-talk and other transmission problems. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. Clamshell retail package.

Features

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing
- Length: 10-ft. Connectors: DB25 male/Cent36 male
- Gold plated connectors and gold plated copper contacts offer superior conductivity
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- · Molded ends with easy-grip textured overmold
- Tripp Lite warrants this product to be free from defects in materials and workmanship for life

Specifications

OVERVIEW	
UPC Code	037332013552

Highlights

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bidirectional printing.
- Superior molded cables with integral strain relief and foilshielding for maximum EMI/RFI protection
- Printer cables' gold-plated connectors provide superior conductivity and support highspeed bi-directional printing
- Retail packaging

System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with high-speed Bi-Directional communication (although not essential).

Package Includes

 10-ft. AB Parallel Gold Cable DB25M to Cen36M



Technology	Parallel
PHYSICAL	
PHISICAL	
Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	7.50 x 7.25 x 3.00
Shipping Dimensions (hwd / cm)	19.05 x 18.42 x 7.62
Shipping Weight (lbs.)	1.10
Shipping Weight (kg)	0.50
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
CONNECTIONS	
Side A - Connector 1	DB25 (MALE)
Side B - Connector 1	CENTRONICS 36 (MALE)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.