

## **Specification Sheet**

Part Number: 181-00253

Narrow fingers reduce fanning of the wires to the terminal blocks, presenting a neater appearance.

Each finger is provided with a double restriction to hold wires in the bottom portion of the duct, allowing for easier installation.

Mounting holes are uniform in size and are offered every 2 inches to accommodate compact designs and ease installation.

Optional covers snap on and off easily, and are provided with a non-slip lining that insures the covers remain in place during vibration.



High Density Slotted Wall Wiring Duct, 2" x 5", Non-Adhesive, PVC, Gray, 30ft/Box

Article Number	181-00253
AITIGIC INGILIDO	101-00233

Type SLHD2X5

Color Gray (GY)

Quantity Per box

Product Description HellermannTyton High-Density Slotted Wall Wiring Duct features

narrow fingers equaling a 2-to-1 finger ratio compared to standard slotted wiring duct. With the narrow fingers, compact designs and

components are more easily accommodated.

Short Description High Density Slotted Wall Wiring Duct, 2" x 5", Non-Adhesive, PVC,

Gray, 30ft/Box

	_	
Global	Dart	Nama
เวเบเลเ	ran	ıvaııı <del>∈</del>

SLHD2X5-PVC-GY

Length L (Imperial)

6.0

Length L (Metric)

1.83

Width W (Imperial)

2.0

Width W (Metric)

50.8

Height H (Imperial)

5.07

Height H (Metric)

128.8

Mounting Hole Centers (Imperial)

2.0

Material

Polyvinylchloride (PVC)

**Material Shortcut** 

PVC

Halogen Free

No

UV Resistant (Yes/No)

No

**Operating Temperature** 

+122°F (+50°C)

Reach Compliant (Article 33)

No

**ROHS Compliant** 

Yes

Certification/Specification EN 50085-1:2005 + A1:2013 EN 50085-2-3\_1A UL CSA

UL Recognized (US)

Yes

Package Quantity (Imperial)

30.0

Package Quantity (Metric)

9.14

3925900000

## About HellermannTyton

**Customs Number** 

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (<a href="https://www.hellermann.tyton.com">www.hellermann.tyton.com</a>).

© 2023 HellermannTyton. All Rights Reserved.

Contact Us RoHS/WEEE Compliance Disclaimer Terms and Conditions