

## AB Parallel Printer Cable (DB25 to Cen36 M/M), 3-ft.

MODEL NUMBER: P606-003



### Description

Tripp Lite's 3-ft. A-B parallel printer cable connects computers with a DB25 female parallel port to parallel printers with a Centronics 36 female parallel port. Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing. The cable features nickel plated DB25 male/Cent36 male connectors and gold plated copper contacts for superior conductivity. It is manufactured from superior molded cable with integral strain relief and double shielding for maximum EMI/RFI protection. It contains low-capacitance, impedance matched, twisted-pair conductors that protect against cross-talk and other transmission problems.

### Features

- Built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing
- Length: 3-ft. Connectors: DB25 male/Cent36 male
- Nickel plated connectors and gold plated copper contacts offer superior conductivity
- Superior molded cable with integral strain relief and double shielding (foil and braid) for maximum EMI/RFI protection
- Low-capacitance impedance matched twisted-pair conductors protect against cross-talk and other transmission problems
- Bi-directional communication allows your printer to broadcast printer error messages back to network computers
- Molded ends with easy-grip textured overmold

## Specifications

| OVERVIEW   |              |
|------------|--------------|
| UPC Code   | 037332013514 |
| Technology | Parallel     |

### Highlights

- Superior molded cables with integral strain relief and foil-shielding for maximum EMI/RFI protection
- Printer Cable built to the IEEE 1284 standard to provide superior conductivity and support high-speed bi-directional printing

### System Requirements

- Computers with a DB25 Female parallel port
- Parallel printers with a Centronics 36 Female parallel port with high-speed Bi-Directional communication (although not essential).

### Package Includes

- 3ft AB Parallel Printer Cable Cen36M to DB25M

| <b>PHYSICAL</b>                     |                           |
|-------------------------------------|---------------------------|
| Color                               | Black                     |
| Cable Length (ft.)                  | 3                         |
| Cable Length (m)                    | 0.91                      |
| Shipping Dimensions (hwd / in.)     | 0.50 x 4.30 x 9.00        |
| Shipping Dimensions (hwd / cm)      | 1.27 x 10.92 x 22.86      |
| Shipping Weight (lbs.)              | 0.40                      |
| Shipping Weight (kg)                | 0.18                      |
| Unit Dimensions (hwd / in.)         | 0.000 x 0.000 x 0.000     |
| <b>CONNECTIONS</b>                  |                           |
| Side A - Connector 1                | DB25 (MALE)               |
| Side B - Connector 1                | CENTRONICS 36 (MALE)      |
| <b>WARRANTY &amp; SUPPORT</b>       |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |