


PROPRIETARY INFORMATION:
 PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK, INC.

REVISION			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE, RFS. 20710, EM	04/11/11	BS




GENERAL SPECIFICATIONS:

RATING: 10A / 125V AC
 CABLE TYPE / SIZE: SVT, 18 AWG X 3
 TEMPERATURE RATING: 105° C
 CONDUCTOR COLORS: BLACK / WHITE / GREEN
 CABLE JACKET COLOR: PMS 11C, COOL GRAY
 OVERALL LENGTH (L): 2150 ± 50 mm
 CABLE OUTER DIAMETER: 6.3 ± 0.1 mm
 END 'A' TERMINATION: NEMA 5-15P, COLOR PMS 11C, COOL GRAY
 END 'B' TERMINATION: IEC 320 / C13, COLOR PMS 11C, COOL GRAY
 APPROVALS PLUG: UL, CSA or cUL
 APPROVALS CABLE: UL, CSA or cUL
 APPROVALS CONNECTOR: UL, CSA or cUL

PACKING:


HANKING
 L = 230 ± 10 mm
 MAXIMUM SHIPPING CARTON WEIGHT IS 30 KG.



NOTES:

1. CORD, PLUG AND CONNECTOR MUST BE MARKED WITH APPROVAL SYMBOLS OR FILE NUMBER(S).





DASH NO.	PART NO	REV.	DESCRIPTION	NOTES
TABULATION BLOCK				
		TOLERANCES: DECIMALS ANGULAR .xx +/- 0.1 +/- 1° .xxx +/- .005		 GlobTek, Inc. www.globtek.com 186 Veterans Dr. Northvale, NJ 07647 Tel. 201-784-1000 Fax 201.784.0111
		MILLIMETERS ANGULAR .xx +/- 0.3 +/- 1° .xxx +/- .013		
INIT.BY: EM	DATE: 04/11/11	DWG TITLE: NORTH AMERICAN DETACHABLE CORDSET, 7 FEET, NEMA5-15P TO IEC320/C13		
DRAWN: NF	DATE: 04/11/11	FSCN No.: G, CC	SIZE A	MODEL: N / A
APRVD: HM	DATE: 04/11/11	SCALE: NONE	PART NO: 3021457F701T-GGY(R)	
				REV. A
				SHEET 1/2

Foot Note:
 Globtek Inc. will not be liable for the safety and performance of these power product if unauthorized access and repair occurs. End user should consult the applicable UL, CSA or EN Standards for proper installation instruction.


Limitation of Use:
 Globtek product are not authorized for use as mission critical components in life support, hazardous environment, nuclear or aircraft applications without prior written approval from the CEO of Globtek Inc.

Contents of this document are subject to change without prior notice

PROPRIETARY INFORMATION:
 PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR
 USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY
 PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK,INC.



5PCS PACK PRICK




Waterproof Bag

Outer Box


- NOTE:
1. 100PCS/CTN, 5PCS PACK PRICK.
 2. 1PC Waterproof Bag/CTN
 SIZE: 80cmX80cmX0.05mm
 3. Outer Box SIZE: (40X30X23)cm

FRONT MARK:
 **GlobTek, Inc.**
 PART: 3021457F701(R)
 C/NO.:
 DATE:

MADE IN CHINA
 E-63-0005 Rev.A



SIDE MARK:
 LR#:
 PART#: 3021457F701(R)
 MODEL: POWER CORD
 Q'TY: 100 PCS
 N.W.: 17.0 KGS
 G.W.: 17.7 KGS
 Recycle Mark

 GlobTek, Inc. www.globtek.com		186 Veterans Dr. Northvale, NJ 07647 Tel. 201-784-1000 Fax 201.784.0111
DWG TITLE: NORTH AMERICAN DETACHABLE CORDSET, 7 FEET, NEMA5-15P TO IEC320/C13		
MODEL: N / A	REV. A	
PART NO: 3021457F701T-GGY(R)	SHEET 2/2	