PROPRIETARY INFORMATION:					REVISION				
	PROPRIETARY OF GLOBTEK, INC. ANY REPRODUCTION, DISCLOSURE OR USE OF THIS DRAWING, IN WHOLE OR IN PART, IS HEREBY			ICL V		DESCRIPTION	DATE	APPROVED	
	PROHIBITED EXCEPT AS SPECIFIED IN WRITING BY GLOBTEK, INC.			A		INITIAL RELEASE, RFS. 26645, MK	02/07/17	MK	
CONN.1:USB A/M COLOR WHITE			1			CONN.2:Micro USB 5P COLOR WHITE 3(4)5(6) 5 1 1			
12.0		12	00±30			5.7			
WIRING TABLE CONN.1 CONN.2 COL 1 1 RE 2 2 WH 3 3 GRI 4 5 BL/ Shell Shell BR/ Shield attached to Black wire bo		120±			 1. 1009 2. Insul 3. Cond 4. USB Micro 5. Curr BENDING 1. Angle 2. Bend 3. Load 4. Sam 	ICAL TEST: % OPEN,SHORT AND MISS WIRE TEST lation Resistance: D300V 5Mohm min. ductor Resistance: 2ohm Max. AM: Insertion force<=35N, Pullout force bUSB AM: Insertion force<=35N,Pullout for ent rating: 5V/2Amp G TEST REQUIREMENTS: e: +60° and -60° in opposite directions ding frequency: 10~11 cycles/min ding position: 30cm from where cable i uple loading: 200g est regulation performance USB connector s	orce>=8N. s securec		
Image: Second system Image: Second system Image: Second				1.2 m	attach	ned to GND in user system. RELEASED By N.Frost at 4:16 pm, Feb 07, 2017	And the second s	IS	
		DASH NO.	PART NO	REV.		DESCRIPTION		NOTES	
DECIN xx + xxx +				•	TABULATION BLOCK				
				TOLER DECIMALS .xx +/- 0.1 .xxx +/005 MILLIMETERS	-0.1 +/- I* .005 www.globtek.com Tel. 201-784-1000 Fax 201.784.0111				
Foot Note: Globtek Inc. will not be liable for the safety and performance of these power	Limitation of Use: Globtek product are not authorized for use as mission critical components in life support,	INIT.BY: NF DATE:		MILLIMETERS .xx +/- 0.3 .xxx +/013	$_{0.3}^{\text{HARM}}$ +/- 1° DWG TITLE: USB A/M TO MICRO 5P L=1200 mm(2A), WHITE				
Contents of this document are subject to change without prior notice product if unauthorized access and repair occurs. End user should consult the applica- ble UL,CSA or EN Standards for proper	aircraft applications without prior written approval from the CEO of Globtek Inc.		DATE: 02/07/17	FSCN No.: G, YL	SIZE A			REV. A	
installation instruction.		APRVD: MK	: MK DATE: SCA 02/07/17		NONE	PART NO: USBA1M2MICROB20W(R)		SHEET 1/1	