

VS-04-C-SDA/PH/0,3 - USB cable



1405552

<https://www.phoenixcontact.com/us/products/1405552>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

USB cable, with USB connectors at one end, assembled connector type: A, single post connector, length: 0.3 m



Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 1405552 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB14 |
| Product key | ABNDBA |
| Catalog page | Page 453 (C-2-2019) |
| GTIN | 4046356460576 |
| Weight per piece (including packing) | 20.7 g |
| Weight per piece (excluding packing) | 18.5 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

VS-04-C-SDA/PH/0,3 - USB cable



1405552

<https://www.phoenixcontact.com/us/products/1405552>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Sensor type | USB 2.0 |
| Number of positions | 4 |

Electrical properties

| | |
|---|----------|
| Transmission medium | Copper |
| Transmission characteristics (category) | USB 2.0 |
| Transmission speed | 480 Mbps |

Material specifications

| | |
|------------------------|-----|
| Outer sheath, material | PVC |
|------------------------|-----|

Connector

Connection 1

| | |
|---------------------|--------------------------|
| Type | Plug straight USB type A |
| Number of positions | 4 |

Connection 2

| | |
|---------------------|---------------------|
| Type | Individual pin plug |
| Number of positions | 4 |

Cable/line

| | |
|------------------------|-------------------|
| Cable structure | 2xAWG28 + 2xAWG24 |
| Outer sheath, material | PVC |
| External sheath, color | gray |

VS-04-C-SDA/PH/0,3 - USB cable



1405552

<https://www.phoenixcontact.com/us/products/1405552>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1405552>



EAC

Approval ID: 19060508

VS-04-C-SDA/PH/0,3 - USB cable



1405552

<https://www.phoenixcontact.com/us/products/1405552>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27060308 |
| ECLASS-12.0 | 27060308 |
| ECLASS-13.0 | 27060308 |

ETIM

| | |
|----------|----------|
| ETIM 8.0 | EC002599 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

VS-04-C-SDA/PH/0,3 - USB cable

1405552

<https://www.phoenixcontact.com/us/products/1405552>




Accessories

VS-04-BUA-FK-F/IP67 - USB female insert

1653854

<https://www.phoenixcontact.com/us/products/1653854>




USB socket insert, 4-pos., socket USB type A on flat-ribbon cable terminal strip, pitch 2.54, for the Freenet system in the panel mounting frame, IP20 terminal outlet, 19" patch panel and service interface

VS-04-BUB-FK-F/IP67 - USB female insert

1653867

<https://www.phoenixcontact.com/us/products/1653867>



USB socket insert, 4-pos., socket USB type B on flat-ribbon cable terminal strip, pitch 2.54, for the Freenet system in the panel mounting frame, IP20 terminal outlet, 19" patch panel and service interface

VS-04-C-SDA/PH/0,3 - USB cable

1405552

<https://www.phoenixcontact.com/us/products/1405552>



VS-A-F-IP67 - Panel mounting frames

1653744

<https://www.phoenixcontact.com/us/products/1653744>



Panel mounting frame, IP67, for Freenet system, for round panel cutout, with grommet, without mounting screws, color: gray

VS-08-SD-F - Protective cover

1652606

<https://www.phoenixcontact.com/us/products/1652606>



Protective cover, IP67, flat design, to cover the contact insert in the panel mounting frame, color: gray

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com