

## Specification Sheet

Part Number: 151-00378



Clips can be connected to each other to create a chain of cable harnesses. Secures firmly to surfaces to eliminate moisture and corrosion.

Quick and easy installation ideal for the production environment.

Automatic Harness Clip, Connectable, 1.1" Bundle Max, PA66HIRHS, Black, 500/pkg

Article Number 151-00378

Type IAHC3AH

Color Black (BK)

Quantity Per carton

Product Description Automatic Harness Clips offer a simple and secure method of attaching cables to panels and other surfaces. When the cable is pushed inside, it automatically activates the locking features which causes it to close. These are also connectable which allows for multiple cables to be positioned next to each other. These come in various sizes to fit different bundle diameters.

Short Description Automatic Harness Clip, Connectable, 1.1" Bundle Max, PA66HIRHS, Black, 500/pkg

Global Part Name IAHC3AH-PA66HIRHS-BK

Length L (Imperial) 1.6

Length L (Metric) 40.0

Width W (Imperial) 0.4

Width W (Metric) 13.5

Bundle Diameter Min (Metric) 19.0

Bundle Diameter Max (Metric) 28.0

Height H (Imperial) 2.5

Height H (Metric) 64.5

Panel Thickness Min (Imperial) 0.04

Panel Thickness Max (Imperial) 0.03

Panel Thickness Min (Metric) 0.7

Panel Thickness Max (Metric) 2.7

Mounting Hole Diameter D (Imperial) 0.24 - 0.26

Mounting Hole Diameter D (Metric) 6.2 - 6.7 mm

Mounting Hole Diameter D Max (Metric) 6.7

Disc Diameter (Metric)	24.0
Disc Diameter (Imperial)	0.94
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach

to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)