




Cable entry grommets Type KDT/X FDA



PRODUCT INFORMATION

1-piece cable entry grommet for pre-assembled cables combined with the cable entry system KDL/H-VA FDA made of FDA compliant material for the food industry.

- Pre-assembled cables can be easily inserted or fed through e.g. in control

cabinets.

- Grommets are retrofitted around the cable.
- Made of FDA compliant material especially for the food industry

SPECIFICATIONS

| | |
|---|-------------|
|  | TPE |
|  | -40 – 80 °C |
|  | |
|  | |
|  | |

| Type | Order No. | Colour | for Ø mm | For opening Small / medium / large | No. of openings | VPE qty. |
|------------------------|-----------|--------|----------|---------------------------------------|-----------------|----------|
| Grommet, small | | | | | | |
| KDT/X-FDA 02, 02-03 | 87141710 | Blue | 2 – 3 | • / - / - | 1 | 12 |
| KDT/X-FDA 03, 03-04 | 87141712 | Blue | 3 – 4 | • / - / - | 1 | 12 |
| KDT/X-FDA 04, 04-05 | 87141714 | Blue | 4 – 5 | • / - / - | 1 | 12 |
| KDT/X-FDA 05, 05-06 | 87141716 | Blue | 5 – 6 | • / - / - | 1 | 12 |
| KDT/X-FDA 06, 06-07 | 87141718 | Blue | 6 – 7 | • / - / - | 1 | 12 |
| KDT/X-FDA 07, 07-08 | 87141720 | Blue | 7 – 8 | • / - / - | 1 | 12 |
| KDT/X-FDA 08, 08-09 | 87141722 | Blue | 8 – 9 | • / - / - | 1 | 12 |
| KDT/X-FDA 09, 09-10 | 87141724 | Blue | 9 – 10 | • / - / - | 1 | 12 |
| KDT/X-FDA 10, 10-11 | 87141726 | Blue | 10 – 11 | • / - / - | 1 | 12 |
| KDT/X-FDA 11, 11-12 | 87141728 | Blue | 11 – 12 | • / - / - | 1 | 12 |
| Grommet, medium | | | | | | |
| KDT/X-FDA 12, 12-13 | 87141730 | Blue | 12 – 13 | - / • / - | 1 | 4 |
| KDT/X-FDA 13, 13-14 | 87141732 | Blue | 13 – 14 | - / • / - | 1 | 4 |
| KDT/X-FDA 14, 14-15 | 87141734 | Blue | 14 – 15 | - / • / - | 1 | 4 |
| KDT/X-FDA 15, 15-16 | 87141736 | Blue | 15 – 16 | - / • / - | 1 | 4 |
| KDT/X-FDA 16, 16-17 | 87141738 | Blue | 16 – 17 | - / • / - | 1 | 4 |
| KDT/X-FDA 17, 17-18 | 87141740 | Blue | 17 – 18 | - / • / - | 1 | 4 |
| KDT/X-FDA 18, 18-19 | 87141742 | Blue | 18 – 19 | - / • / - | 1 | 4 |
| KDT/X-FDA 19, 19-20 | 87141744 | Blue | 19 – 20 | - / • / - | 1 | 4 |
| KDT/X-FDA 20, 20-21 | 87141746 | Blue | 20 – 21 | - / • / - | 1 | 4 |
| KDT/X-FDA 21, 21-22 | 87141748 | Blue | 21 – 22 | - / • / - | 1 | 4 |
| Grommet, large | | | | | | |
| KDT/X-FDA 23, 23-24 | 87141752 | Blue | 23 – 24 | - / - / • | 1 | 4 |

Cable entry grommets Type KDT/X FDA

DIMENSION TABLE

| Type | Order No. |
|------------------------|-----------|
| Grommet, small | |
| KDT/X-FDA 02, 02-03 | 87141710 |
| KDT/X-FDA 03, 03-04 | 87141712 |
| KDT/X-FDA 04, 04-05 | 87141714 |
| KDT/X-FDA 05, 05-06 | 87141716 |
| KDT/X-FDA 06, 06-07 | 87141718 |
| KDT/X-FDA 07, 07-08 | 87141720 |
| KDT/X-FDA 08, 08-09 | 87141722 |
| KDT/X-FDA 09, 09-10 | 87141724 |
| KDT/X-FDA 10, 10-11 | 87141726 |
| KDT/X-FDA 11, 11-12 | 87141728 |
| Grommet, medium | |
| KDT/X-FDA 12, 12-13 | 87141730 |
| KDT/X-FDA 13, 13-14 | 87141732 |
| KDT/X-FDA 14, 14-15 | 87141734 |
| KDT/X-FDA 15, 15-16 | 87141736 |
| KDT/X-FDA 16, 16-17 | 87141738 |
| KDT/X-FDA 17, 17-18 | 87141740 |
| KDT/X-FDA 18, 18-19 | 87141742 |
| KDT/X-FDA 19, 19-20 | 87141744 |
| KDT/X-FDA 20, 20-21 | 87141746 |
| KDT/X-FDA 21, 21-22 | 87141748 |
| Grommet, large | |
| KDT/X-FDA 23, 23-24 | 87141752 |



TPE



Temperature / temperature range
-40 – 80 °C

Cable entry grommets Type KDT/X FDA



According to EN -2-1



RoHS (EC Directive 2011/65/EU)



Made in Germany

All details given in our sales brochures and catalogues, as well as the information available online, are based on our current knowledge of the products described.

The electronic data and files made available by Murrplastik, particularly CAD files are based on our current knowledge of the product described.

A legally binding assurance of certain properties or the suitability for a certain purpose can not be determined from this information.

All information with respect to the chemical and physical properties of Murrplastik products, as well as application advice given verbally, in writing or by tests, is given to the best of our knowledge.

They do not release the buyer from the obligation to carry out his own tests and trials in order to determine the concrete suitability of the products for the intended purpose.

Murrplastik accepts no responsibility for the available information being up-to-date, correct or complete. Neither do we accept responsibility for the quality of this information.

Murrplastik accepts no liability for damage caused as a result of using our products.

Murrplastik reserves the right to make technical changes and improvements through constant further development of products and services.

Our General Terms and Conditions apply.

© Murrplastik Systemtechnik GmbH • proID_134216~20200228~890287~kdh_kdt_x_fda