

# USB-A to USB-C Cable, Right-Angle USB-C, USB 2.0, (M/M), 3 ft. (0.91 m)

## MODEL NUMBER: U038-003-CRA











USB-A to C cable connects a smartphone or other USB-C device to the USB-A port on your computer, wall charger or car charger.

#### **Features**

**USB Type-A to USB Type-C Cable Connects a USB-C Mobile Device to Your Computer**This three-foot right-angle USB-C cable allows you to connect a device with a USB-C or Thunderbolt 3 port to a USB-enabled computer, charger, hard drive, hub or other peripheral for the purpose of charging, powering, syncing or transferring data. It is compatible with any device with a USB-C or Thunderbolt 3 port, including tablets, smartphones, MacBooks, Ultrabooks and Chromebooks.

**Transfers Data and Charges Devices at USB 2.0 Speeds**The USB-A to C cable supports USB 2.0 data transfer speeds up to 480 Mbps. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

Reversible USB-C Connector Attaches in Either DirectionUnlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

**Right-Angle USB-C Plug Makes Connecting in Tight Spaces Easier**The space-saving right-angle USB-C plug is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

#### **Highlights**

- Right-angle USB-C plug permits easier connection in confined or hard-to-reach spaces
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- USB-A to USB-C cable compatible with all USB-A, USB-C and Thunderbolt 3 devices

#### **Applications**

- Charge and sync a USB-C mobile device from a USB-A wall charger up to 3 ft. away
- Connect a printer or scanner to a desktop computer's hard-toreach rear USB-C port
- Transfer data between an external hard drive or flash drive and your computer or laptop

#### **System Requirements**

- Device with a USB-C or Thunderbolt 3 port
- · Device with a USB-A port

### **Package Includes**

 U038-003-CRA USB Type-A to Type-C Cable, M/M, 3 ft.

# **Specifications**

OVERVIEW	
UPC Code	037332214119
Technology	USB 2.0 (High Speed)
Cable Type	Passive



PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.0 mm
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB C (MALE) - RIGHT ANGLE
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Angled
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty







© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.