



NOTE
 1.適合ターミナル: 2011956000
 APPLICABLE TERMINAL : 2011956000
 2.適合ハウジング: 201196,201200シリーズ
 APPLICABLE HOUSING : 201196 201200 SERIES
 3.材料: ポリエステル UL94V-0
 色: グレー
 MATERIAL: POLYESTER UL94 V-0
 COLOR: GRAY
 4. 偶数極に適用
 APPLY EVEN CIRCUIT PRODUCTS.

7.5	9.3	38	44.5	201196 4200	20
7.5	9.3	36	42.5	201196 4190	19
7.5	9.3	34	40.5	201196 4180	18
7.5	9.3	32	38.5	201196 4170	17
7.5	9.3	30	36.5	201196 4160	16
7.5	9.3	28	34.5	201196 4150	15
7.5	9.3	26	32.5	201196 4140	14
7.5	9.3	24	30.5	201196 4130	13
7.5	9.3	22	28.5	201196 4120	12
7.5	9.3	20	26.5	201196 4110	11
7.5	9.3	18	24.5	201196 4100	10
7.5	9.3	16	22.5	201196 4090	9
7.5	9.3	14	20.5	201196 4080	8
7.5	9.3	12	18.5	201196 4070	7
7.5	9.3	10	16.5	201196 4060	6
-	-	8	14.5	201196 4050	5
-	-	6	13.5	201196 4040	4
-	-	4	11.5	201196 4030	3
-	-	2	9.5	201196 4020	2
D	C	B	A	ポリ袋 POLYBAG PKG オーダー番号 ORDER No.	極数 CKT NO.

QUALITY SYMBOLS A = 0 E = 0 F = 0 G = 0 H = 0 I = 0 J = 0 K = 0 L = 0 M = 0 N = 0 O = 0 P = 0 Q = 0 R = 0 S = 0 T = 0 U = 0 V = 0 W = 0 X = 0 Y = 0 Z = 0	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				DIMENSION UNITS: MM SCALE: 5:1						
	EC NO: 114815 DRWN: SNAKAMURA08 CHK'D: KOMURAKAMI APPR: TKANEKO	2016/11/30 2017/03/23 2017/03/24	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 3.0 °		DRWN BY	DATE					SPOT-ON 2.0 RETAINER
			4 PLACES ± 0.2	3 PLACES ± 0.2	SNAKAMURA08	2016/11/30					
			2 PLACES ± 0.2	1 PLACE ± 0.2	0 PLACES ± 0.2	CHK'D BY	DATE	PRODUCT CUSTOMER DRAWING			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			KOMURAKAMI	2017/03/23	SERIES	MATERIAL NUMBER	CUSTOMER				
			TKANEKO	2017/03/24	201196	SEE CHART					
			DRAWING SIZE: A3		THIRD ANGLE PROJECTION		DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER
							2011964150		PSD	000	1 OF 1