

4

3

2

1

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESEINTE AMP

RELEASED FOR PUBLICATION .19

© COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.
TOUS DROITS RESERVES.

REVISIONS						
P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.	
	A	MISE A JOUR	18-SEP-97	SI	-	
	B	RENFORT DU PION DE DETROMPAGE	26-JUN-00	JLQ	-	

RECOMMANDATION DECOUPE PANNEAU
RECOMMENDED PANEL CUTOUT

VUE DE DESSUS / VIEW FROM TOP

Dimensions: 13.3 ± 0.1, 14 ± 0.1, 12.75 ± 0.1, 10.8 ± 0.2, 16.2 ± 0.2, +0.2, +0.1

Dimensions: 17, +0.1, 16 ± 0.3, 11 ± 0.15, 12.6 ± 0.1, 13.2 ± 0.1, 11.4 ± 0.1, 8.6 ± 0.1, +0.4, +0.3, 21.5 ± 0.1, (40.4), (5X2.54), (2.54)

Dimensions: 4 ± 0.2, 16.2, 3.4 ± 0.4, 20.3 ± 0.2, 2.5 ± 0.1, +0.2, 13.1 ± 0.15, +0.05, 14.15 ± 0.1, 14.85 ± 0.1, +0.2, 13.8 ± 0.15, +0.05, 6 ± 0.2, 1.5 ± 0.2, 4 ± 0.2, +0.2

Dimensions: (10.35), (11.05), R3.1, (6.55), 12.3 ± 0.1, 0.8, 11.6 ± 0.1, 6

☒ COTE POUR CAPABILITE
DIMENSION FOR CAPABILITY

Callouts: 1, 5, 4, (∅2.2)

NOTES:

- DATE CODE
- LOGO D'AMP
- REFERENCE DU PRODUIT ASSEMBLE
- REVISION DU MOULE
- N° D'EMPREINTE DU MOULE
- MATIERE
- CONTRE-PARTIE :
CONNECTEURS REF 185341 ET 185343

NOTES:

- DATE CODE
- AMP LOGO
- ASSY PART NUMBER
- REVISION STATUS
- CAVITY MARKING
- MATERIAL REFERENCE
- MATING PART :
CONNECTORS PN 185341 AND 185343

RECOMMANDATION IMPLANTATION CI
RECOMMENDED PCB DETAILS

VUE DE DESSUS / VIEW FROM TOP

Dimensions: 6.5, 6.5, 1.6 ± 0.15, 12.7, 6.55, 11.05, 1.27, 2.54, 10.35, 2.54, 12.7, 11.05, 1.27, 10.35

Labels: BOITIER BLEU BLUE HOUSING, BOITIER MARRON BROWN HOUSING, BOITIER NOIR BLACK HOUSING

Specs: 3X ∅1.8 ± 0.075, ∅0.15 M, 12X ∅1.1 ± 0.075, ∅0.15 M, 2X ∅2.7 ± 0.075, ∅0.15 M

REF / ASSY PN	REV	QTY	MATERIAL	DESIGNATION / NAME	COULEUR / COLOR	REP.
953130-1	-	12	CuSn6	CONTACT MQS 0.63X0.63	POST ETAME / POST TIN	④
953130-2	-	1	PBT GF20	BOITIER / HOUSING	MARRON / BROWN	③
953130-3	-	1	PBT GF20	BOITIER / HOUSING	BLEU / BLUE	②
		1	PBT GF20	BOITIER / HOUSING	NOIR / BLACK	①

DETROMPAGES / CODINGS

Options: NOIR BLACK (953130-1), BLEU BLUE (953130-2), MARRON BROWN (953130-3)

Dimensions: 13.2 ± 0.1, 1.6 ± 0.15, 1.8 ± 0.2, +0.2

SCALE 1:1

THIS DRAWING IS A CONTROLLED DOCUMENT.
CE PLAN EST UN DOCUMENT CONTROLE.

DIMENSIONS: mm

MATERIAL MATIERE: SEE TABLE

FINISH FINITION: SEE TABLE

WEIGHT MASSE APPROX.: 4.5 g

CUSTOMER DRAWING/PLAN CLIENT: UNIQUEMENT POUR REFERENCE

DWN/DESSINE: 23-MAY-97, Sladjan IVANOVIC

CHK/VERIFIE: 12-NOV-97, J. LAQUERBE

APVD/APPROUVE: 12-NOV-97, JJ. REVIL

NAME TITRE: AMP DE FRANCE, 95301 PONTOISE

AMP

PRODUCT SPEC: 108-15180

APPLICATION SPEC: 12W MQS STRAIGHT HEADER WITH BOARD-LOCKS

SIZE FORMAT: A2

CAGE CODE: 00779

DRAWING NO TITRE: 953130

RESTRICTED TO: B

SCALE ECHELLE: 2:1

SHEET FEUILLE: 1 OF 1

REV: B

AMP 1471-9 REV 27JUN96

27-JUL-00 16:31:23 er003237 /home/dept1302/er003237/ednmod