



NUMBER OF CIRCUITS	"A" DIM.	"B" DIM.	"C" DIM.	MATERIAL NUMBER
02	43.51 (1.713)	11.11 (1.438)	33.35 (1.313)	387403402
03	54.62 (2.151)	22.23 (1.875)	44.46 (1.751)	387403403
04	65.74 (2.588)	33.34 (1.313)	55.58 (2.188)	387403404
05	76.85 (3.026)	44.45 (1.750)	66.69 (2.626)	387403405
06	87.96 (3.463)	55.56 (2.188)	77.80 (3.063)	387403406
07	99.07 (3.901)	66.68 (2.625)	88.91 (3.501)	387403407
08	110.19 (4.338)	77.79 (3.063)	100.03 (3.938)	387403408
10	132.41 (5.213)	100.01 (3.938)	122.25 (4.813)	387403410
26	310.21 (12.213)	277.81 (10.938)	300.05 (11.813)	387403426

- NOTES:
1. MATERIAL: SEE TABLE
 2. FINISHES: SEE TABLE
 3. PRODUCT SPECIFICATION: AS REQUIRED
 4. PACKAGING: NOT REQUIRED
 5. MATES WITH: NONE

ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH
3	"XX"	SCREW #6-32 BINDING HEAD	BRASS	NICKEL
2	"XX"	TERMINAL WITH TURRET TAIL	BRASS	TIN
1	1	INSULATOR	THERMOPLASTIC	BLACK

EC NO.: RELEASED DRWING: JF 08-09-04 CHK'K: APPR:	QUALITY SYMBOLS MAJOR CRITICAL SPC	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 2:1	DESIGN UNITS <input type="checkbox"/> mm <input checked="" type="checkbox"/> INCH	THIRD ANGLE PROJECTION	DIMENSIONS: <input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH <input type="checkbox"/> mm ONLY	SHT REV	
		4 PLACES ±.0015 3 PLACES ±.038 ±.005 2 PLACES ±.13 ±.01 1 PLACE ±.3		DRAWN BY & DATE J.FARMER 08-09-04		TITLE: SR BTS TURRET TAIL MO MTG ASY.			
		ANGULAR: ±2°		CHECKED BY & DATE		MOLEX INCORPORATED			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		APPROVED BY & DATE		CAD FILENAME 742XX-49.PRT	MATERIAL NO. SEE CHART	DRAWING NO. SD-38740-001	SHEET NO. 1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.								SIZE B	