

PCA.0A.250.NTLC29

SUMMARY

Wires

Coax 1



Image is for illustrative purpose only

Series 0A

Termination type Female solder

IP rating 50

AWG wire size 0.00 - 0.00

Cable Ø 2.50 - 2.80 mm

Status Active

Matching parts FFA.0A.250.NTAC29

Download

Request a quote

Catalog

TECHNICAL DETAILS

Mechanics

Shell Style/Model PCA*: Straight receptacle with cable collet

Keying

Housing Material Brass (nickel plated [SAE AMS QQ N 290]) shell, collet nut, latch sleeve and mid pieces

Weight 8.88 g

Performance

Configuration 0A.250 : 1 Coax (50 Ohm)

Insulator

Rated Current

Specifications

Contact Type: Coaxial 50 Ohm (Solder)


Others

Endurance (Shell): 5000 mating cycles

Salt Spray Corrosion: >144 hr

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

DRAWINGS





Dimensions

	A	В	L	S1	S2	S 3
mm.	9	10	35	8	8.5	9
in.	0,35	0,39	1,38	0,31	0,33	0,35

RECOMMENDED BY LEMO

Tools

Cables

17420	PVC	Black	
17450	COPOLYMER	Black	
18700	PTFE	White	
18800	PTFE	White	
31600	PTFE	Brown	
CCX.50.RG1.74-U25N	PVC	Black	
CCX.50.RG1.74AU28N	PVC	Black	
CCX.50.RG1.74AU28N	PVC	Black	
CCX.50.RG1.74U25N	PVC	Black	
CCX.50.RG1.88AU26B	PFA	White	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

CCX.50.RG1.88AU26B	PTFE	White	
CCX.50.RG3.16BU26M	FEP	Brown	
CCX.50.RG3.16U28M	PTFE	Brown	
CCX.75.RG1.79BU26M	FEP	Brown	
CCX.75.RG1.87AU26B	PFA	White	
CCX.75.RG1.87AU27B	PTFE	White	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.